Release date: 2023-05-09 Date of issue: 2023-05-09 Filename: 199988_eng.pdf

Photoelectric slot sensor

GL20-RT/32/40a/98a



- Optimized for the detection of small parts
- High switching frequency
- Multiple device installation possible, no mutual interference (no cross-talk)
- Sensitivity adjuster and light-on/dark-on changeover switch as standard features of this series
- Visible red light
- Degree of protection IP67
- cULus approval
- Sturdy aluminum housing


Photoelectric slot sensor, aluminum housing, 20 mm slot width, red light, light/dark on, sensitivity adjuster, DC version, PNP output, 3 pin M8 plug



Function

Photoelectric slot sensors offer vast installation benefits thanks to their housing design. When it comes to operation, these new generation devices boast features such as high resolution, high repeatability, automatic signal threshold adjustment, ambient light resistance, and detection of and/or light transmission through transparent objects. Cross-talk protection enables parallel installation of devices despite extremely high switching frequency. These characteristics guarantee reliable detection of small parts, from 0.3 mm, across the entire detection range, even in very fast moving applications.

Dimensions





Technical Data General specifications LED Light source Light type modulated visible red light Tests EN 60947-5-2 Target size 0.3 mm 20 mm Slot width Slot depth 17 mm Ambient light limit 100000 Lux Functional safety related parameters 1290 a MTTF_d Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Function indicator LED red in connector Control elements Sensitivity adjuster, light/dark switch **Electrical specifications** Operating voltage U_B 10 ... 30 V DC, class 2 10 % Ripple No-load supply current I_0 ≤ 15 mA Output Switching type light/dark on Signal output 1 PNP, short-circuit protected, open collector Switching voltage max. 30 V DC Switching current max. 100 mA 0.05 mm Repeat accuracy Switching frequency 3 kHz Response time ≤ 160 µs

Approvals and	certificates
CE conformity	

CE conformity	CE
UL approval	cULus
000	000

CCC approval / marking not required for products rated ≤36 V

EN 60947-5-2

Ambient conditions

Product standard

Conformity

Ambient temperature $-20 \dots 60 \,^{\circ}\text{C} \, (-4 \dots 140 \,^{\circ}\text{F})$ Storage temperature $-20 \dots 75 \,^{\circ}\text{C} \, (-4 \dots 167 \,^{\circ}\text{F})$

Mechanical specifications


Degree of protection	IP67
Connection	M8 connector, 3-pin
Material	

Housing black anodized aluminum

Optical face glass
Mass 25 g



Connection Assignment



- O = Light on
- = Dark on


Connection Assignment




Wire colors in accordance with EN 60947-5-2

1 BN (brown) 3 BU (blue) 4 BK (black)

Assembly



- 1 Functional display red
- 2 Light-/dark switch
- 3 Sensitivity adjuster



Function Principle

Photoelectric slot sensors are photoelectric sensors that operate according to the thru-beam sensor principle. The transmitter sends signals directly to the receiver. If an object breaks the light beam, the switching element function is triggered. The special U-shaped design means the transmitter and receiver can be accommodated in one housing, which ensures high resistance to vibrations. In contrast to standard thru-beam sensors, photoelectric slot sensors have the added advantage of not requiring complex electrical installation, as only one device needs to be connected. Also, adjustment of the optical axes is not necessary.

Accessories



V3-WM-2M-PUR

Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey

Application

- Small part detection, from object size 0.3 mm
- Can also be used for systems with strong vibrations
- Detection of small needles in transparent hollow needles
- · Counting of small parts on conveyors
- · Feed and correct separation verification
- Web edge control
- Elevator car position in elevators