



Thru-beam sensor LA31/LK31/25/31/115 SET2



- Photoelectric sensor for detecting people, objects and vehicles
- Large construction with small housing
- Not sensitive to ambient light
- Version for universal voltages
- Relay output
- Version with accessories in scope of delivery

Mid-range photoelectric sensors for detecting people, objects, and vehicles










Function

Series 31 is a range of cost-effective and, most importantly, reliable photoelectric sensors for standard applications in the fields of material handling and logistics, and for monitoring industrial doors, elevators, and automatic gates. The ultrasonic-welded plastic housing provides a high degree of protection, making these sensors ideal for tasks in harsh outdoor conditions. These sensors are currently the most compact "wide range power supply sensors" that can work with any DC and AC voltage between 24 V and 240 V. In addition to the robust technology, the sensors offer numerous product details that help the user with assembly, connection and operation.

Application

- Monitoring closing edges of automatic industrial doors and elevators
- · Monitoring the swing range of automatic gates
- · Detecting and tracking objects in material handling



red


Technical Data


System components				
Emitter	LA31/115			
Receiver	LK31/25/31/115			
General specifications				
Effective detection range	0 30 m			
Threshold detection range	43 m			
Light source	LED			
Light type	modulated visible red light, 630 nm			
Alignment aid	LED yellow: 1. LED illuminates: Sufficient light signal received, emitter and receiver alignment is correct 2. LED flashes: Reaching switching point 3. LED off: Light beam is interrupted or the alignment is out			
Diameter of the light spot	approx. 800 mm at a distance of 30 m			
Opening angle	Emitter: 0.5 °, Receiver: 1.5 °			
Ambient light limit	50000 Lux			
Accessories provided	2 x Mounting bracket OMH-RL31-05 and mounting materials			
Functional safety related parameters				
MTTF _d	790 a			
Mission Time (T _M)	20 a			
Diagnostic Coverage (DC)	0 %			
Indicators/operating means				
Operation indicator	LED green: power on			
Function indicator	LED yellow: 1. LED lit constantly: signal > 2 x switching point (function reserve) 2. LED flashes: signal between 1 x switching point and 2 x switching point 3. LED off: signal < switching point			

Technical Data **Electrical specifications** Operating voltage U_B 24 ... 240 V AC 12 ... 240 V DC No-load supply current Emitter: ≤ 40 mA I_0 Receiver: ≤ 3 mA Power consumption P_0 Emitter: ≤ 1 VA Receiver: ≤ 1 VA Output light-on Switching type Signal output Relay, 1 alternator Switching voltage max. 250 V AC/DC Switching current max. 3 A Switching power DC: max. 150 W AC: max. 750 VA Switching frequency f ≤ 20 Hz Response time ≤ 25 ms Conformity Product standard EN 60947-5-2 Compliance with standards and directives Standard conformity EN 62103 Standards Approvals and certificates II , rated voltage \leq 250 V AC with pollution degree 1-2 according to IEC 60664-1 Output circuit basis insulation of input circuit according to EN 50178, rated insulation Protection class voltage 240 V AC CCC approval Certified by China Compulsory Certification (CCC) **Ambient conditions** -25 ... 55 °C (-13 ... 131 °F) Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) Mechanical specifications **IP67** Degree of protection Emitter: 2 m fixed cable , 2-wire Connection Receiver: 2 m fixed cable, 5-wire Material Housing Polycarbonate Optical face **PMMA** Mass Emitter: 116 g

Receiver: 131 g


Connection Assignment






1	Operating display	green
2	Signal display	yellow
3	Emitter or receiver	

Characteristic Curve









Kit component



OMH-RL31-05

Mounting bracket for mounting on flat surfaces with 2 M4 screws