


# Ultrasonic sensor UB1000-18GM75-E23-V15

- 2 switch outputs
- Selectable sound lobe width
- Program input
- Temperature compensation
- Very small unusable area

# Single head system



# **Dimensions**



# **Technical Data**

General specifications	
Sensing range	70 1000 mm
Adjustment range	90 1000 mm
Dead band	0 70 mm
Standard target plate	100 mm x 100 mm
Transducer frequency	approx. 255 kHz
Response delay	approx. 125 ms
Indicators/operating means	
LED yellow	indication of the switching state flashing: program function object detected

#### Technical Data LED red "Error", object uncertain in program function: No object detected **Electrical specifications** 10 ... 30 V DC , ripple 10 %SS Operating voltage $U_{\mathsf{B}}$ No-load supply current $I_0$ ≤ 50 mA Input Input type 1 program input, operating range 1: -U<sub>B</sub> ... +1 V, operating range 2: +4 V ... +U<sub>B</sub> input impedance: > 4.7 kΩ; program pulse: ≥ 1 s Output Output type 2 switch outputs PNP, NO/NC Rated operating current 2 x 100 mA, short-circuit/overload protected $I_{e}$ Voltage drop $U_{\text{d}}$ ≤3 V Repeat accuracy ≤1 % Switching frequency f max. 3 Hz Range hysteresis 1 % of the set operating distance Temperature influence ± 1.5 % of full-scale value Compliance with standards and directives Standard conformity EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 Standards Approvals and certificates **UL** approval cULus Listed, Class 2 Power Source CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** Ambient temperature -25 ... 70 °C (-13 ... 158 °F) Storage temperature -40 ... 85 °C (-40 ... 185 °F) Mechanical specifications Connector plug M12 x 1, 5-pin Connection type Housing diameter 18 mm IP67 Degree of protection Material Housing brass, nickel-plated Transducer epoxy resin/hollow glass sphere mixture; foam polyurethane, cover PBT 60 g **Factory settings** Switching point: 90 mm output function: Switch point operation mode output behavior: NO contact Output 1 Output 2 Switching point: 1000 mm output function: Switch point operation mode output behavior: NC contact Beam width wide

# Connection

# Standard symbol/Connections:

(version E23, pnp)

1 (BN) + U<sub>B</sub>
5 (GY) Teaching input
4 (BK) Switch output 1
3 (BU) Switch output 2

Core colours in accordance with EN 60947-5-2.



# **Connection Assignment**




Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)


# **Characteristic Curve**

# Characteristic response curve





# Programmed switching output function



Switch point 1 -> ∞: Switch output 1, (N.O.) Detection of object presence Switch output 2, (N.C.) Detection of object presence Switch point 2 -> ∞:

# **Accessories**

Release date: 2023-02-15 Date of issue: 2023-02-15 Filename: 204534\_eng.pdf





# BF 18 Mounting flange, 18 mm BF 18-F Plastic mounting adapter, 18 mm BF 5-30 Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm UVW90-K18 Ultrasonic -deflector M18K-VE Plastic nuts with centering ring for the vibration-free mounting of cylindrical sensors V15-G-2M-PVC Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey V15-W-2M-PVC Female cordset single-ended M12 angled A-coded, 5-pin, PVC cable grey

The sensor features two switch outputs with one programmable switch point, each. Programming the switch points is done by applying the supply voltage  $-U_B$  (switch output 1) or  $+U_B$  (switch output 2) to the Teach-In input. The supply voltage must be applied to the Teach-In input for at least 1 s. LEDs indicate whether the sensor has recognized the target during the programming procedure.

#### Note

Switching points may only be specified directly after Power on. A time lock secures the adjusted switching points against unintended modification 5 minutes after Power on. To modify the switching points later, the user may specify the desired values only after a new Power On.

#### Note:

If a programming adapter UB-PROG3 is used for the programming procedure, button A1 is assigned to -UB and button A2 is assigned to +UB.

## **Programming switch ouputs**

## Switch point for switch output 1

- 1. Place the target at the desired switch point position of switch output 1
- 2. Program the switch point by applying -U<sub>B</sub> to the Teach-In input (corresponding yellow LED flashes)
- 3. Disconnect the Teach-In input from -UB to save the switch point

## Switch point for switch output 2

- 1. Place the target at the desired switch point position of switch output 2
- 2. Program the switch point by applying  $+U_B$  to the Teach-In input (corresponding yellow LED flashes)
- 3. Disconnect the Teach-In input from +U<sub>B</sub> to save the switch point

## Programming detection of object presence

- 1. Cover the sensor face with hand or remove all objects from sensing range
- 2. Apply -UB to the Teach-In input (red LED flashes)
- 3. Disconnect the Teach-In input from -UB
- 4. Apply +UB to the Teach-In input (red LED flashes)
- 5. Disconnect the Teach-In input from +UB

**Note:** Only one switch output can be configured for detection of presence of objects. If the sensor detects an object within the maximum detection range, the switch output switches.

## Adjusting the sound cone characteristics:

The ultrasonic sensor enables two different shapes of the sound cone, a wide angle sound cone and a small angle sound cone.

## 1. Small angle sound cone

- · switch off the power supply
- connect the Teach-In input wire to -U<sub>R</sub>
- · switch on the power supply
- the red LED flashes once with a pause before the next.
- yellow LED: permanently on: indicates the presence of an object or disturbing object within the sensing range
- disconnect the Teach-In input wire from -U<sub>B</sub> and the changing is saved



# 2. Wide angle sound cone

- switch off the power supply
- connect the Teach-In input wire with +U<sub>B</sub>
- · switch on the power supply
- · the red LED double-flashes with a long pause before the next.
- yellow LED: permanently on: indicates an object or disturbing object within the sensing range
- disconnect the Teach-In input wire from +U<sub>B</sub> and the changing is saved



# **Factory Setting**

## Factory settings

See technical data.

# Indication

The sensor provides LEDs to indicate various conditions.

www.pepperl-fuchs.com

# Ultrasonic sensor

	Red LED	Yellow LED 1	Yellow LED 2
During Normal operation			
Proper operation	Off	Switching state output 1	Switching state output 2
Interference (e.g. compressed air)	On	remains in previous state	remains in previous state
Programming of output 1			
Object detected	Off	Flashes	Off
No object detected	Flashes	Off	Off
Object uncertain (programming invalid)	On	Off	Off
Programming of output 2			
Object detected	Off	Off	Flashes
No object detected	Flashes	Off	Off
Object uncertain (programming invalid)	On	Off	Off

# **Installation Conditions**

If the sensor is installed at places, where the environment temperature can fall below 0 °C, for the sensors fixation, one of the mounting flanges BF18, BF18-F or BF 5-30 must be used.

In case of direct mounting of the sensor in a through hole using the steel nuts, it has to be fixed at the middle of the housing thread. If a fixation at the front end of the threaded housing is required, plastic nuts with centering ring (accessories) must be used.