Control interface unit

IC-KP2-2HRX-2V1

- LED status indicator of bus communication and read/write heads
- Max. 2 read/write heads can be connected
- Alternatively 1 read/write head and 1 trigger sensor can be connected

Control interface unit IDENTControl Compactwith serial interface RS-232 and RS-485



Function

The RFID identification system IDENTControl Compact from Pepperl+Fuchs offers a vast number of benefits compared to other systems, thanks to its innovative design. The control interfaces IDENTControl and IDENTControl Compact make up the core of the system.


With its integrated interfaces to all commercially available fieldbus systems such as PROFIBUS, PROFINET, Ethernet, EtherCAT, CC-Link, serial connections (RS 232 or RS 485) and numerous connection options for read/write heads available for frequency ranges LF, HF and UHF, the

IDENTControl Compact control interface can be easily and flexibly adapted to your requirements.

LEDs on the front of the housing indicate bus communication, connected read/write heads and active read/write commands. Reliability of the application is further increased by using trigger sensors.

The system is equally suited for use in control cabinets and field use in IP67. The interface to the higher-level fieldbus is integrated in the housing, and all connections are designed such that they are pluggable. This enables simple installation and quick, problem-free replacement in case of device failure. The consistent EMC design, with metal housing, grounding and shielded wires, offers a high degree of reliability.

Dimensions




107

Technical Data


General specifications

Technical Data Number of read/write heads alternatively 1 read/write head and 1 trigger sensor **UL File Number** E87056 **MTBF** 80 a (Operation at +40 °C) Indicators/operating means LEDs 1, 2 Status indicator for read/write heads green: read head detected LEDs CH1, CH2 red: Configuration error green: power on red: Hardware fault LED PWR/ERR I FD TxD green: flashes in rhythm with the transmitted data LED RxD green: flashes in rhythm of receiving data Electrical specifications 20 ... 30 V DC , PELV Rated operating voltage U_{e} < 10 % at 30 V DC Ripple Current consumption ≤ 4 A incl. read/write heads Power consumption P_0 2 W Without read/write heads Galvanic isolation basic insulation acc. to DIN EN 50178, rated insulation voltage of 50 V_{eff} Interface 1 Interface type serial Physical RS-485 Protocol ASCII Transfer rate 1200; 2400; 4800; 9600; 19200; 38400 Bit/s Interface 2 Interface type serial Physical RS 232 Protocol **ASCII** Transfer rate 1200; 2400; 4800; 9600; 19200; 38400 Bit/s **Directive conformity** Electromagnetic compatibility Directive 2014/30/EU EN 61000-6-2 EN 61000-6-4 RoHS IEC/EN 63000 Directive 2011/65/EU (RoHS) Standard conformity Degree of protection IEC 60529 **Ambient conditions** Ambient temperature -25 ... 70 °C (-13 ... 158 °F) Storage temperature -40 ... 85 °C (-40 ... 185 °F) air humidity max. 96 % Salt spray resistant to EN 60068-2-52 Climatic conditions Oscillation (Sine): 5 g, 10 - 1000 Hz to EN 60068-2-6 Shock and impact resistance Shock (Half-sine): 30 g, 11 ms in accordance with EN 60068-2-27 Mechanical specifications 137 mm Housing length Housing width 62 mm Housing height 42 mm IP67 Degree of protection Read/write heads: shielded, 4-pin, M12 connector Power supply: M12 connector Protective earth: M4 earthing screw Connection RS 232: M12 plug connection RS 485: M12 connector Material powder coated aluminum Housing Installation screw fixing Mass approx. 300 g




Control interface unit IC-KP2-2HRX-2V1

Connection



Assembly



Accessories

	V1S-G-0,15M-PUR-ABG- SUBD	Adapter cable M12 plug straight A-coded 4-pin to Sub-D-plug straight 9-pin, PUR cable grey, shielded
66	V1-G-2M-PUR-ABG-V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded
66	V1-G-10M-PUR-ABG- V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded
	ICZ-MH05-SACB-8	Mounting aid for DIN rail
	V1S-G-5M-PUR-ABG- SUBD9	Adapter cable M12 plug straight A-coded 4-pin to Sub-D-socket straight 9-pin, PUR cable grey, shielded
66	V1-G-5M-PUR-ABG-V1-W	Cordset M12 socket straight to M12 plug angled A-coded, 4-pin, PUR cable grey, shielded
6 /	V1-G-5M-PUR-ABG	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey, shielded