

# Diffuse mode sensor ML100-8-1000-RT/95/103



- Miniature design
- Easy to use
- Very bright, highly visible light spot
- Full metal thread mounting
- Highly visible LEDs for Power ON and switching state
- Not sensitive to ambient light

Diffuse mode sensor, plastic housing, 1000 mm adjustable detection range, red light, light/dark on, pnp output, M8 plug 4-pin









# **Function**

The optical sensors of this series are suitable for both standard and demanding applications. The series a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

### **Dimensions**





#### Technical Data **General specifications** 0 ... 1000 mm Detection range Adjustment range 100 ... 1000 mm Reference target standard white, 100 mm x 100 mm Light source modulated visible red light Light type Polarization filter Diameter of the light spot approx. 75 mm at a distance of 1000 mm Opening angle approx. 2° Optical face frontal Ambient light limit EN 60947-5-2:2007+A1:2012 Functional safety related parameters 860 a $\mathsf{MTTF}_\mathsf{d}$ Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on Function indicator LED yellow, lights up with receiver lit Control elements sensitivity adjustment Control elements Light-on/dark-on changeover switch **Electrical specifications** Operating voltage $U_{R}$ 10 ... 30 V DC Ripple max. 10 % < 20 mA No-load supply current $I_0$ Output Switching type The switching type of the sensor is adjustable. The default setting is: light-on 1 PNP output, short-circuit protected, reverse polarity protected, open collector Signal output max. 30 V DC Switching voltage Switching current max. 100 mA, resistive load Voltage drop $U_{\text{d}}$ ≤ 1.5 V DC Switching frequency f 1000 Hz Response time 0.5 ms Conformity EN 60947-5-2 Product standard

Approvals	and	certificates

UL approval	cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclose	
CCC approval	CCC approval / marking not required for products rated ≤36 V	

**Ambient conditions** 

## Ambient temperature -30 ... 60 °C (-22 ... 140 °F)

Storage temperature -40 ... 70 °C (-40 ... 158 °F)

Mechanical specifications			
Housing width	11 mm		
Housing height	31 mm		
Housing depth	20 mm		

IP67 Degree of protection Connection plug M8 x 1, 4-pin


Material Housing PC (Polycarbonate)

**PMMA** Optical face Mass approx. 10 g

Tightening torque, fastening screws

0.6 Nm

# **Connection**




# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)

# **Assembly**




1	Light-Dark-switching	
2	2 Sensitivity adjuster	
3	Signal display yello	
4	Operating display	green

# **Characteristic Curve**



# **Characteristic Curve**



# **Accessories**

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
8	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket
*	OMH-F10-ML100	Mounting aid for ML100 series
N. A.	OMH-10	Mounting aid for ML100 series
6/	V31-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey
61	V31-GM-2M-PUR	Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey

# Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 210537\_eng.pdf

# **Accessories**



OMH-ML100-S1

Mounting bracket