


# Ultrasonic sensor UB300-18GM40A-E4-V1


- Short design, 40 mm
- Function indicators visible from all directions
- Switching output
- 5 different output functions can be set
- Program input
- Temperature compensation

## Single head system



# Dimensions






# **Technical Data**

General specifications		
Sensing range	35 300 mm	
Adjustment range	50 300 mm	
Dead band	0 35 mm	
Standard target plate	100 mm x 100 mm	
Transducer frequency	approx. 390 kHz	
Response delay	approx. 50 ms	
Indicators/operating means		
LED green	Power on	

Technical Data		
LED yellow		indication of the switching state
I ED and		flashing: program function object detected
LED red		solid red: Error red, flashing: program function, object not detected
Electrical specifications		
Operating voltage	$U_B$	10 30 V DC , ripple 10 %ss
No-load supply current	$I_0$	≤ 20 mA
Input		
Input type		1 program input operating distance 1: -U <sub>B</sub> +1 V, operating distance 2: +6 V +U <sub>B</sub> input impedance: > 4,7 k $\Omega$ program pulse: $\geq$ 1 s
Output		
Output type		1 switching output E4, NPN, NO/NC, programmable
Rated operating current	I <sub>e</sub>	200 mA , short-circuit/overload protected
Default setting		Switch point A1: 50 mm Switch point A2: 300 mm
Voltage drop	$U_{d}$	≤3 V
Repeat accuracy		≤1 %
Switching frequency	f	≤13 Hz
Range hysteresis	Н	1 % of the set operating distance
Temperature influence		± 1.5 % of full-scale value
Compliance with standards and directives		
Standard conformity		
Standards		EN IEC 60947-5-2:2020 IEC 60947-5-2:2019
Approvals and certificates		
UL approval		cULus Listed, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection type		Connector plug M12 x 1 , 4-pin
Housing diameter		18 mm
Degree of protection		IP67
Material		
Housing		brass, nickel-plated
Transducer		epoxy resin/hollow glass sphere mixture; foam polyurethane, cover PBT
Mass		25 g

## **Connection**

Standard symbol/Connections: (version E4, npn)



Core colours in accordance with EN 60947-5-2.

## **Connection Assignment**




Wire colors in accordance with EN 60947-5-2


1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

## **Characteristic Curve**

### Characteristic response curve



### Programmable output modes



5. A1 ->  $\infty$ , A2 ->  $\infty$ : Object presence detection mode Object detected: Switch output closed No object detected: Switch output open

## **Accessories**

21	UB-PROG2	Programming unit
	OMH-04	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm

# **Accessories BF 18** Mounting flange, 18 mm BF 18-F Plastic mounting adapter, 18 mm BF 5-30 Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey V1-G-2M-PVC V1-W-2M-PUR Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey UVW90-K18 Ultrasonic -deflector M18K-VE Plastic nuts with centering ring for the vibration-free mounting of cylindrical sensors

#### Adjusting the switching points

The ultrasonic sensor features a switch output with two teachable switching points. These are set by applying the supply voltage  $-U_B$  or  $+U_B$  to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. Switching point A1 is taught with  $-U_B$ , A2 with  $+U_B$ .

Five different output functions can be set

- 1. Window mode, normally-open function
- 2. Window mode, normally-closed function
- 3. one switching point, normally-open function
- 4. one switching point, normally-closed function
- 5. Detection of object presence

#### **TEACH-IN** window mode, normally-open function

- Set target to near switching point
- TEACH-IN switching point A1 with -U<sub>B</sub>
- Set target to far switching point
- TEACH-IN switching point A2 with +U<sub>B</sub>

#### **TEACH-IN** window mode, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A2 with +U<sub>B</sub>
- Set target to far switching point
- TEACH-IN switching point A1 with -U<sub>B</sub>

## TEACH-IN switching point, normally-open function

- Set target to near switching point
- TEACH-IN switching point A2 with +U<sub>B</sub>
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -U<sub>B</sub>

#### **TEACH-IN** switching point, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A1 with -U<sub>B</sub>
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A2 with +U<sub>B</sub>

#### **TEACH-IN** detection of objects presence

- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -U<sub>B</sub>
- TEACH-IN switching point A2 with +U<sub>B</sub>

### **LED Displays**

Displays in dependence on operating mode	Red LED	Yellow LED
TEACH-IN switching point:		
Object detected	off	flashes
No object detected	flashes	off
Object uncertain (TEACH-IN invalid)	On	off
Normal operation	off	Switching state
Fault	on	Previous state