



Model Number

GLP30-RT/40b/102/123/143

Photoelectric slot sensor with 4-pin, M8 x 1 connector


Features

- Plastic version •
- Clearly visible function indicators •
- External TEACH-IN •
- Degree of protection IP67


Product information

An extremely favorable price/performance ratio and an innovative display concept characterize the GLP series. The switching states are visible from all directions. The optional attachment holes or dove tail joint significantly increase installation flexibility. The external, dynamic Teach-In function allows you to teach in moving objects easily.


Dimensions



Туре	A	В	С	D	E	F	G	Number of mounting holes M4 *
GLP30-RT-	30	50	30	34	59.5	20	-	1
GLP50-RT-	50	70	50	54	79.5	20	28	2
GLP80-RT-	80	100	80	54	79.5	20	2 x 28	3
GLP120-RT-	120	140	120	54	79.5	20	3 x 28	4




Electrical connection



Pinout



Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	TEACH-IN button	
4	Emitter	
5	Receiver	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com ⁵ PEPPERL+FUCHS 1

Technical data			Accessories	
General specifications			ОМН-К03	
Light source		LED , 640 nm pulsing	dove tail mounting clamp	
Light type		modulated visible red light	•	
Object size		min. 0.3 mm	V31-WM-2M-PUR	
Slot width		30 mm	Female cordset single-ended, M8, 4-p PUR cable	
Slot depth		34 mm		
Ambient light limit		10000 Lux		
Indicators/operating means			V31-GM-2M-PUR	
Function indicator		LED yellow , lit when the light beam is interrupted LED green: ready	Female cordset single-ended, M8, 4-p PUR cable	
Control elements		Teach-In key , Sensitivity adjustment and Mode adjustment (NO/NC)	V31-GM-BK2M-PUR-U	
Electrical specifications			Female cordset single-ended, M8, 4-p	
Operating voltage U _B		10 30 V DC	PUR cable	
Ripple		10 %	T OTT Cable	
No-load supply current	I ₀	≤ 30 mA	V31-WM-BK2M-PUR-U	
Input			Female cordset single-ended, M8, 4-p PUR cable	
Function input		external Teach-In		
Output				
Switching type light/dark on		Other suitable accessories can be found		
Signal output		1 NPN short-circuit protected, reverse polarity protected, open collector	www.pepperl-fuchs.com	
Switching voltage		max. 30 V DC		
Switching current		max. 100 mA		
Voltage drop	Ud	≤2.4 V		
Switching frequency	f	2000 Hz		
Response time		0.25 ms		
Conformity				
Product standard		EN 60947-5-2		
Ambient conditions				
Ambient temperature		-20 60 °C (-4 140 °F)		
Storage temperature		-20 80 °C (-4 176 °F)		
Mechanical specifications				
Degree of protection		IP67		
Connection		M8 connector, 4-pin		
Material		···· ···· ····		
Housing		PC		
Optical face		plastic		
Mass		20 g		
Approvals and certificates				
Protection class		II		
UL approval		cULus Listed, Class 2 Power Source "For use in NFPA 79 Applications only" Adapters providing field wiring means are available from the manufacturer. Refer to manufacturers information.		

2

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

EPPPERL+FUCHS