



# Retroreflective sensor ML100-55/25/103/115b/154



- No controls
- Miniature design
- Easy to use
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- Very bright, highly visible light spot
- Full metal thread mounting
- Not sensitive to ambient light

Retroreflective sensor with polarization filter, plastic housing, 5 m detection range, red light, light on, DC version, PNP output, no controls, fixed cable with M12 plug








#### **Function**

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

#### **Dimensions**





#### Retroreflective sensor ML100-55/25/103/115b/154 Technical Data **General specifications** Effective detection range 0 ... 5 m Reflector distance 0.01 ... 5 m Threshold detection range 7 m Reference target H50 reflector LED Light source Light type modulated visible red light Polarization filter Diameter of the light spot approx. 500 mm at a distance of 7 m Opening angle approx. 4° Optical face frontal Ambient light limit EN 60947-5-2:2007+A1:2012 Functional safety related parameters $\mathsf{MTTF}_\mathsf{d}$ 860 a Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted Function indicator **Electrical specifications** Operating voltage $U_{B}$ 10 ... 30 V DC Ripple max. 10 % < 20 mA No-load supply current $I_0$ Output Switching type light-on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load Voltage drop $U_{d}$ ≤ 1.5 V DC 1000 Hz Switching frequency 0.5 ms Response time Conformity Product standard EN 60947-5-2

Αı	าตต	ova	ls	and	cert	ifica	tes
, J	Mb.	0.0					

OL approvai	output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure
CCC approval	CCC approval / marking not required for products rated ≤36 V

#### **Ambient conditions**

Ambient temperature	-30 60 °C (-22 140 °F)
Storage temperature	-40 70 °C (-40 158 °F)

#### **Mechanical specifications**

Housing width	11 mm
Housing height	31 mm
Housing depth	20 mm
Degree of protection	IP67
Begies of proteotion	11 07

Material

Housing


Connection

PC (Polycarbonate) Optical face **PMMA** 

Cable


Length 300 mm Mass approx. 20 g

0.6 Nm Tightening torque, fastening screws



300 mm fixed cable with 4-pin, M12 x 1 connector

#### **Connection**




# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)

# Indication




1	Signal display	yellow
2	Operating display	green

## **Characteristic Curve**



#### **Characteristic Curve**



### **Accessories**

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
100	OMH-F10-ML100	Mounting aid for ML100 series
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket
	OMH-10	Mounting aid for ML100 series
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole
	REF-H60-2	Reflector with mounting holes
	REF-H33	Reflector with screw fixing

Accessories			
	OFR-70-2	Reflective tape 70 mm x 70 mm	
	OMH-ML100-08	Mounting aid for ML100 series, Snap-in	
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes	
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap	
	OFR-100/100	Reflective tape 100 mm x 100 mm	