



Thru-beam sensor (pair) M100/MV100-RT/76a/103/115



- Miniature design
- Easy to use
- Very bright, highly visible light spot
- Full metal thread mounting
- Highly visible LEDs for Power ON and switching state
- Not sensitive to ambient light

Thru-beam sensor, 10 m detection range, red light, light/dark on, DC version, PNP output, sensitivity adjuster, emitter switch-off, fixed cable









Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions







www.pepperl-fuchs.com



Technical Data System components Emitter M100-RT/76a/115 MV100-RT/103/115 Receiver **General specifications** Effective detection range 0 ... 10 m Threshold detection range 15 m Light source LED modulated visible red light Light type Diameter of the light spot approx. 1 m at a distance of 15 m Opening angle approx. 2° Optical face frontal Ambient light limit EN 60947-5-2 Functional safety related parameters $MTTF_d$ 860 a 20 a Mission Time (T_M) Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on Function indicator Receiver: LED yellow, lights up when light beam is free, flashes when falling short of the operating reserve; OFF when light beam is interrupted Control elements sensitivity adjustment Control elements Light-on/dark-on changeover switch **Electrical specifications** U_{B} 10 ... 30 V DC Operating voltage Ripple max. 10 % No-load supply current I_0 Emitter: ≤ 15 mA Receiver: ≤ 8 mA Input Test input emitter deactivation at +UB Output Switching type The switching type of the sensor is adjustable. The default setting is: light-on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC max. 100 mA, resistive load Switching current ≤ 1.5 V DC Voltage drop U_d 1000 Hz Switching frequency Response time 0.5 ms Conformity EN 60947-5-2 Product standard Approvals and certificates cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** Ambient temperature -30 ... 60 °C (-22 ... 140 °F) Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Housing width 11 mm 31 mm Housing height

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Housing depth

Connection

Material Housing

Degree of protection

20 mm

2 m fixed cable


PC (Polycarbonate)


IP67

Technical Data


Optical face	PMMA
Mass	approx. 100 g (emitter and receiver)
Tightening torque, fastening screws	0.6 Nm
Cable length	2 m

Connection






Assembly




1	Light-Dark-switching	
2	Sensitivity adjuster	
3	Signal display yellow	
4	Operating display green	

Characteristic Curve



Characteristic Curve



Accessories

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
W. Harris	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket
.	OMH-F10-ML100	Mounting aid for ML100 series
14 A	OMH-10	Mounting aid for ML100 series
	OMH-ML100-S1	Mounting bracket
	OMH-ML100-S2	Mounting aid for ML100 series, mounting bracket