



# Retroreflective sensor ML100-55/103/115a



- Miniature design
- Easy to use
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- Full metal thread mounting
- Very bright, highly visible light spot
- Not sensitive to ambient light

Retroreflective sensor with polarization filter, plastic housing, 5 m detection range, red light, sensitivity adjuster, light/dark on, DC version, PNP output, fixed cable with M8 plug








### **Function**

The optical sensors of this series are suitable for both standard and demanding applications. The series a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

#### **Dimensions**






## **Technical Data**

General specifications		0 5 m
Effective detection range		
Reflector distance		0.01 5 m
Threshold detection range		7 m
Reference target		H50 reflector
Light source		LED
Light type		modulated visible red light
Polarization filter		yes
Diameter of the light spot		approx. 500 mm at a distance of 7 m
Opening angle		approx. 4 °
Optical face		frontal
Ambient light limit		EN 60947-5-2:2007+A1:2012
Functional safety related parameters		
MTTF <sub>d</sub>		860 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0 %
ndicators/operating means		
Operation indicator		LED green: power on
Function indicator		LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted
Control elements		sensitivity adjustment
Control elements		Light-on/dark-on changeover switch
Electrical specifications		
Operating voltage	U <sub>B</sub>	10 30 V DC
Ripple		max. 10 %
No-load supply current	I <sub>O</sub>	<20 mA
Output		
Switching type		The switching type of the sensor is adjustable. The default setting is: light-on
Signal output		1 PNP output, short-circuit protected, reverse polarity protected, open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA , resistive load
Voltage drop	Ud	≤1.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		0.0 1110
Product standard		EN 60947-5-2
Approvals and certificates		EN 00047 3 Z
UL approval		cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		, , , , , , , , , , , , , , , , , , , ,
Ambient temperature		-30 60 °C (-22 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		11 mm
Housing height		31 mm
Housing depth		20 mm
Degree of protection		IP67
Connection		300 mm fixed cable with M8 connector, 4-pin
Material		255 Indee deadle than the definitions, 4 pill
		PC (Polycarhonata)
Housing Optical face		PC (Polycarbonate) PMMA
Optical face		
Mass		approx. 20 g

### **Technical Data**

Cable length  $0.3 \, \text{m}$ 

### Connection




# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


(brown) (white) BN WH 2 3 4 (blue) (black) BU BK


## **Assembly**



1	Light-Dark-switching	
2	Sensitivity adjuster	
3	Signal display	yellow
4	Operating display	green

### **Characteristic Curve**





### **Accessories**

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
**	OMH-F10-ML100	Mounting aid for ML100 series
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm

# **Accessories** OMH-ML100-04 Mounting aid for ML100 series, mounting bracket OMH-ML100-05 Mounting aid for ML100 series, mounting bracket OMH-10 Mounting aid for ML100 series REF-C110-2 Reflector, round ø 84 mm, central mounting hole REF-H60-2 Reflector with mounting holes REF-H33 Reflector with screw fixing OFR-70-2 Reflective tape 70 mm x 70 mm OMH-ML100-08 Mounting aid for ML100 series, Snap-in REF-H85-2 Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes REF-H50 Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap OFR-100/100 Reflective tape 100 mm x 100 mm V31-GM-2M-PUR Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey V31-WM-2M-PUR Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey