



Retroreflective sensor MLV41-55/25/115/136



- Rugged series in corrosion-resistant metal housing
- Extremely high switching frequency
- Clear and functional display concept for the operating modes
- Resistant against noise: reliable operation under all conditions
- Aluminum housing with high quality Delta-Seal coated

Robust retroreflective sensor with polarization filter, compact housing design, 8 m detection range, red light, 2 push-pull outputs, fixed cable








Function

The unique and extremely popular design of the MLV41 series enables it be mounted correctly in confined areas and offers all the functions that are normally only found on larger phototelectric sensors. The MLV41 series comes with a range of functions. For example, highly visible status LEDs on the front and back, resistance to ambient light, crosstalk protection and universally applicable output stages that permit every possible switching logic and polarity to be realized. The enhanced resistance to ambient light ensures reliable operation even where modern energy-saving lamps with electronic ballasts are in use. The same applies where multiple devices are present, i.e. the use of a number of sensors in the same vicinity causes no problems.

Dimensions




-1 α α	hnical	ata
		ra I ra

Effective detection range Reflector distance O.1 8 m Threshold detection range 10 m Reference target Light source LED Light type modulated visible red light , 625 nm Polarization filter yes Angle deviation Diameter of the light spot Opening angle Optical face Ambient light limit proceculated parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator Operation indicator Description: LED green , statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz) LED yellow, lights up when light beam is free, flashes when falling short of the operating reserve	General specifications	
Threshold detection range 10 m Reference target H85-2 reflector Light source LED Light type modulated visible red light, 625 nm Polarization filter yes Angle deviation max. ± 1.5 ° Diameter of the light spot approx. 300 mm at detection range 8.5 m Opening angle 1.5 ° Optical face frontal Ambient light limit 20000 Lux Functional safety related parameters MTTF _d 844 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Effective detection range	0 8 m
Reference target Light source LED Light type modulated visible red light , 625 nm Polarization filter yes Angle deviation max. ± 1.5 ° Diameter of the light spot Opening angle 1.5 ° Optical face Ambient light limit 20000 Lux Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Reflector distance	0.1 8 m
Light source Light type modulated visible red light, 625 nm Polarization filter yes Angle deviation max. ± 1.5 ° Diameter of the light spot Opening angle Optical face Ambient light limit Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED modulated visible red light, 625 nm modulated visible red light, 625 nm page 3.5 m And the detection range 8.5 m To not all the detection range 8.5 m And the detection range 8.5 m Detection range 8.5 m Operation range 8.5	Threshold detection range	10 m
Light type modulated visible red light , 625 nm Polarization filter yes Angle deviation max. ± 1.5° Diameter of the light spot approx. 300 mm at detection range 8.5 m Opening angle 1.5° Optical face frontal Ambient light limit 20000 Lux Functional safety related parameters MTTF _d 844 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0% Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz) Function indicator	Reference target	H85-2 reflector
Polarization filter Angle deviation Diameter of the light spot Opening angle Optical face Ambient light limit Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Light source	LED
Angle deviation max. ± 1.5 ° Diameter of the light spot approx. 300 mm at detection range 8.5 m Opening angle 1.5 ° Optical face frontal Ambient light limit 20000 Lux Functional safety related parameters MTTF _d 844 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Light type	modulated visible red light, 625 nm
Diameter of the light spot Approx. 300 mm at detection range 8.5 m Opening angle 1.5 ° Optical face Ambient light limit Functional safety related parameters MTTF _d 844 a Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Polarization filter	yes
Opening angle Optical face frontal Ambient light limit 20000 Lux Functional safety related parameters MTTF _d 844 a Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Angle deviation	max. ± 1.5 °
Optical face frontal Ambient light limit 20000 Lux Functional safety related parameters MTTF _d 844 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Diameter of the light spot	approx. 300 mm at detection range 8.5 m
Ambient light limit Functional safety related parameters MTTF _d 844 a Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Opening angle	1.5°
Functional safety related parameters MTTF _d 844 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Optical face	frontal
MTTF _d Mission Time (T _M) 20 a Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Ambient light limit	20000 Lux
Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Functional safety related parameters	
Diagnostic Coverage (DC) Indicators/operating means Operation indicator Diagnostic Coverage (DC) LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	MTTF _d	844 a
Indicators/operating means Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Mission Time (T _M)	20 a
Operation indicator LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz) Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Diagnostic Coverage (DC)	0 %
Function indicator LED yellow, lights up when light beam is free, flashes when falling short of the	Indicators/operating means	
=== /,g,,	Operation indicator	LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz)
· · ·	Function indicator	LED yellow, lights up when light beam is free, flashes when falling short of the operating reserve


Technical Data		
Control elements		none
Electrical specifications		
Operating voltage	U _B	10 30 V DC
Ripple		max. 10 %
No-load supply current	I ₀	max. 30 mA
Output		
Signal output		2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected $$
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	U_d	≤ 2.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus Listed 57M3 (Only in association with UL Class 2 power supply; Type 1 enclosure)
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-40 60 °C (-40 140 °F)
Storage temperature		-40 75 °C (-40 167 °F)
Mechanical specifications		
Housing width		31 mm
Housing height		56.5 mm
Housing depth		13.6 mm
Degree of protection		IP67
Connection		2 m fixed cable
Material		
Housing		Aluminum , Delta-Seal coated
Optical face		glass pane
Mass		100 g

Connection Assignment




O = Light on= Dark on


Assembly



1 Operating display green 3 Optical axis transmitter 2 Function display yellow 4 Optical axis receiver

Characteristic Curve





Accessories



Acces	ssories	
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap
3	REF-VR10	Reflector, rectangular 60 mm x 19 mm, mounting holes
	ORR50G	Reflector, rectangular 50.9 mm x 60.9 mm, mounting holes, fixing strap and polarization filter
	OFR-100/100	Reflective tape 100 mm x 100 mm