



Retroreflective sensor ML100-55/25/115b/120/154



- No controls
- Miniature design
- Easy to use
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- Very bright, highly visible light spot
- Full metal thread mounting
- Not sensitive to ambient light

Retroreflective sensor with polarization filter, plastic housing, 5 m detection range, red light, light on, DC version, 2 PNP outputs, no controls, fixed cable with M12 plug








Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions





Technical Data **General specifications** Effective detection range 0 ... 5 m Reflector distance 0.01 ... 5 m Threshold detection range 7 m Reference target H50 reflector LED Light source Light type modulated visible red light Polarization filter Diameter of the light spot approx. 500 mm at a distance of 7 m Opening angle approx. 4° Optical face frontal Ambient light limit EN 60947-5-2:2007+A1:2012 Functional safety related parameters MTTF_d 860 a Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on Function indicator LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted **Electrical specifications** Operating voltage U_{B} 10 ... 30 V DC max. 10 % Ripple < 20 mA No-load supply current I_0 Output Switching type Q - Pin4: PNP normally closed / light-on /Q - Pin2: PNP normally open / dark-on Signal output 2 PNP outputs, complementary, short-circuit protected, reverse polarity protected, open collector Switching voltage max, 30 V DC Switching current max. 100 mA, resistive load Voltage drop U_{d} ≤ 1.5 V DC 1000 Hz Switching frequency 0.5 ms Response time Conformity EN 60947-5-2 Product standard Approvals and certificates cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -30 ... 60 °C (-22 ... 140 °F) Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) Mechanical specifications Housing width 11 mm 31 mm Housing height Housing depth 20 mm Degree of protection IP67 Connection fixed cable with 4-pin, M12 x 1 connector Material PC (Polycarbonate) Housing **PMMA** Optical face Cable Length 300 mm

Mass


approx. 20 g

Technical Data

Tightening torque, fastening screws

0.6 Nm

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


(brown) (white) BN 2 3 4 WH BU (blue) BK (black)


Indication



1	Signal display	yellow
2	Operating display	green

Characteristic Curve





Accessories

OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
 OMH-F10-ML100	Mounting aid for ML100 series
OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm

Accessories OMH-ML100-04 Mounting aid for ML100 series, mounting bracket OMH-ML100-05 Mounting aid for ML100 series, mounting bracket OMH-10 Mounting aid for ML100 series REF-C110-2 Reflector, round ø 84 mm, central mounting hole REF-H60-2 Reflector with mounting holes REF-H33 Reflector with screw fixing OFR-70-2 Reflective tape 70 mm x 70 mm OMH-ML100-08 Mounting aid for ML100 series, Snap-in **REF-H85-2** Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes REF-H50 Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap OFR-100/100 Reflective tape 100 mm x 100 mm