












Dimensions



Electrical connection

1 open cable end 2 safety-related inputs I1 & I2 1 output O1 3.1 AS-Interface + 1.3 | 11-Switch BU 1.2 | 12+ WH 3.2 AS-Interface -1.4 | I2-1.5 | O1+ Switch BK GY Load 1.6 01-PK PWR FAULT

Model number


VAA-2E1A-G10-SAJ/EA2J-1M

G10 safety module 2 safety inputs and 1 standard electronic output

Features

- Connection of contact safety switches, e.g. EMERGENCY STOP button
- Applications up to PL_e
- Modular safety solution
- Ultra-compact enclosure
- Degree of protection IP67

Indicating / Operating means



- status display AS-Interface
- error display
- 3 switching state inputs
- switching state output

www.pepperl-fuchs.com

Technical data		
General specifications		
Slave type	Safety-Slave	
AS-Interface specification	V3.0	
·	∨ V2.1	
Required master specification		EDA 70 Augustiantiana andul
UL File Number	E223772 "For use in N	FPA 79 Applications only"
ndicators/operating means		
LED FLT	error display; LED red red: communication er	ror or address is 0
LED AS-i	AS-Interface voltage; g green: voltage OK flashing green: addres:	
LED IN	switching state (input);	2 LED yellow
LED OUT	Switching state (output	;); LED yellow
Electrical specifications		
•	U _e 26.5 31.6 V from AS	-Interface (PELV)
· -	l _e ≤90 mA	
Protection class	III	
Surge protection	overvoltage category II	I
Rated insulation voltage	32 V	
Pulse withstand voltage	0.8 kV	
Number/Type	2 safety-related inputs	for mechanical contacts, crossed-cire
7.	monitored:	cts: up to category 2/PL c to ISO 138
	or	o to category 4/PL e to ISO 13849-1
Supply	from AS-Interface	
Voltage	20 30 V DC pulsed	
Current	input current limited ≤	15 mA
Carroni	short-circuit protected	10 110 1,
Output	р. от	
•	1 conventional alastron	nin output DND
Number/Type	1 conventional electror	iic output, PNP
Supply	from AS-Interface	
Voltage	(U _{ASI} - 7.0 V) ≤ U _{OUT} ≤	
Current	50 mA , short-circuit/ov	erload protected
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU	EN 62026-2:2013 EN 6	61000-6-2:2005 EN 61000-6-4:2007
Machinery Directive		
Directive 2006/42/EC	EN ISO 13849-1:2015 EN 62061:2005 + AC:2	EN ISO 13849-2:2012 2010 + A1:2013 + A2:2015
Standard conformity		
Degree of protection	EN 60529:2000	
Fieldbus standard	EN 62026-2:2013	
Electrical safety	IEC 61140:2009	
Emitted interference	EN 61000-6-4:2007	
AS-Interface	EN 62026-2:2013	
Noise immunity	IEC 62026-2:2013 EN	62061:2005 EN 61000-6-2:2005
Functional safety	EN ISO 13849-1:2015	EN ISO 13849-2:2012
	EN 62061:2005 + AC:2	2010 + A1:2013 + A2:2015
Programming instructions		
Profile	S-7.B	
IO code	7	
ID code	В	
ID1 code	F	
ID2 code	0	
Data bits (function via AS-Interface		output
D0	dyn. safety code 1	OUT 1
D1	dyn. safety code 1	-
D2	dyn. safety code 2	-
D3	dyn. safety code 2	-
Parameter bits (programmable via	AS-i) function	
PO	fails, the outputs are de	s), monitoring = ON, i.e. if communicate e-energised FF, if communication fails, the output
P1	not used	
P2	not used	
P3	not used	
Ambient conditions		
A malai a mat ta mana a watu wa	-20 60 °C (-4 140	°F)
Ambient temperature		
Storage temperature	-25 80 °C (-13 170	6 °F)
· ·	-25 80 °C (-13 170 < 95 %	3 °F)

Function

The VAA-2E1A-G10-SAJ/EA2J- * is an AS-Interface safety module with 2 safety-related inputs and one conventional output. A twochannel mechanical switch or a single channel mechanical switch each can be connected to the two safety-related inputs. The output is a conventional electronic nonsafety-related output, which can be loaded with 50 mA.

The module is suitable for remote connection of switches in very limited space. The onepiece housing provides a degree of protection

The connection to the AS-Interface cable is achieved by means of insulation piercing method of the inserted flat cables. The inputs and the output are connected via open cable

To display the current switching state, there is a LED for each channel mounted on top of the module. A LED indicating the AS-Interface communication and the adress 0 of the module is also available. If a communication error occurs, the outputs are switched off (only at P0 = 1).

The module can be used up to Category 4/PLe according to ISO 13849-1, SIL 3 according to EN 62061.

If two single-channel switches are connected, the module can be used up to Category 2/PLc according to ISO 13849-1, SIL1 according to EN 62061.

Accessories

VBP-HH1-V3.0-KIT

AS-Interface Handheld with accessory

VAZ-PK-FK-0,2M-V1-W

Adapter cable G10 module/hand-held programming device

Matching system components

VAZ-2E1A-F85A-S

Emergency stop button

PEPPERL+FUCHS

Chack and impact registeres	20 a 11 main 6 anotial directions 2 absolve
Shock and impact resistance	30 g, 11 ms in 6 spatial directions 3 shocks 10 g, 16 ms in 6 spatial directions 1000 shocks
Vibration resistance	0.75 mm 10 57 Hz , 5 g 57 150 Hz, 20 cycles
Pollution degree	3
Mechanical specifications	
Degree of protection	IP67 This protection class is achieved by using the AS-Interface flat cable VAZ-FK-S-YE
Connection	AS-Interface: AS-Interface flat cable Inputs/outputs: open conductor ends
Material	
Contacts	open conductor ends with connector sleeves
Housing	PBT
Cable	PUR
Mounting screw	Stainless steel 1.4305 / AISI 303
Cable	
Sheath diameter	Ø4.8 mm
Bending radius	> 8 x cable diameter, fixed > 10 x cable diameter, moving not appropriate for conveyor chains
Color	black
Cores	6 x 0.25 mm ²
Length L	1 m
Mass	200 g
Tightening torque, fastening screws	1.65 Nm
Approvals and certificates	
UL approval	cULus Listed, Type 1 enclosure

Notes


Functional safety related parame	eters	
Operating mode	1-channel	2-channel
Safety Integrity Level(SIL)	SIL 1	SIL 3
Performance Level (PL)	PL c	PL e
Category	Cat. 2	Kat. 4
MTTF _d	100 a	no significant contribution to
PFH _d	2,3 x 10 ⁻⁷	MTTFd, PFD or PFH of the
PFD	1,6 x 10 ⁻¹³	overall system
Safe reaction time	< 300 μs	< 300 μs
Diagnostic coverage	80 %	-
Design Lifetime	20 a	20 a

Safety Instructions

If a single-channel switch is used, the module is suitable for use up to category 2/PL c in accordance with ISO 13849-1, or SIL 1 in accordance with EN/IEC 62061. Only tested and certified power supplies with safe isolation may be used to supply power. These power supplies must have PELV voltage in accordance with EN 50295 / IEC 62026-2, and a minimum MTBF of 50 years. The power supplies are designed to exclude a short circuit between the primary and secondary sides.

Mounting Instructions

You may screw the device onto a level mounting surface using two M4 attachment screws. The attachement screws are not included.



Lay all cables in accordance with EN/IEC 60204.

Do not use the outputs for safety-related functions.

Do not connect inputs and outputs, which are supplied via the module from AS-interface or via auxiliary power, with power supply and signal circuits with external potentials.

See the manual for a guide to the intended use.