



(€

Model Number

ML300-P-12m-IR/76b/95/120

Thru-beam sensor with 4-pin, M8 x 1 connector


Features

- Miniature design
- Easy to use
- Infrared light
- · High operating range
- 45° connector


Product information

The ML300 series has a robust miniature housing and all the standard functional principles. Of particular note are the sensors with analog output, which return a value proportional to the distance. The 45° plug/cable connection ensures flexible mounting. An LED indicates a weak signal, e.g. due to dirt.

Dimensions



Electrical connection



O = Light on


= Dark on

Pinout

Wire colors in accordance with EN 60947-5-2

2 1 3 1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)

Indicators/operating means





| Technical data | | |
|--|----------------|---|
| System components | | |
| Emitter | | ML300-T-12m-IR/76b/95 |
| Receiver | | ML300-R-12m-IR/25/95/120 |
| General specifications | | |
| Effective detection range | | 0 12 m |
| Threshold detection range | | 14 m |
| Light source | | IRED |
| Light type | | modulated infrared light 880 nm |
| Diameter of the light spot | | approx. 4 m at 12 m |
| Angle of divergence | | approx. 7 ° |
| Ambient light limit | | |
| Continuous light | | 10000 Lux |
| Modulated light | | 5000 Lux |
| Indicators/operating means | | |
| Function indicator | | LED yellow: lights up when output is active LED green: Sufficient stability control |
| Control elements | | sensitivity adjustment |
| Electrical specifications | | |
| Operating voltage | U_B | 10 30 V DC |
| Ripple | | max. 20 % |
| No-load supply current | I ₀ | Emitter: ≤ 15 mA Receiver: ≤ 10 mA |
| Input | | |
| Test input | | emitter: 1 test input, not activated: < 4 V, activated: > 8 V or open |
| Output | | |
| Switching type | | light on / dark on |
| Signal output | | 2 PNP outputs, complementary, short-circuit protected, reverse polarity protected, open collector |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 0.1 A |
| Voltage drop | U _d | ≤2 V DC |
| Switching frequency | f | 1000 Hz |
| Response time | | 0.5 ms |
| Conformity | | |
| Product standard | | EN 60947-5-2 |
| Ambient conditions | | |
| Ambient temperature | | -25 55 °C (-13 131 °F) |
| Mechanical specifications | | |
| Housing width | | 30 mm |
| Housing height | | 30 mm |
| Housing depth | | 15 mm |
| Degree of protection | | IP67 |
| Connection | | M8 x 1 connector, 4-pin |
| Material | | DDT |
| Housing Option force | | PBT gless page |
| Optical face Connector | | glass pane metal |
| Mass | | 35 g (emitter and receiver) |
| Compliance with standards and directives | | oo y (onnities and receiver) |
| Standard conformity | | |
| Shock and impact resistance | | EN 60947-5-7 30 g, 11 ms, all axes |
| Vibration resistance | | EN 60947-5-7, 10-55 Hz/1.5 mm amplitude, all axes |
| VISIGUOTI TOSISTATIOE | | Lit 505 if 5 f, 10 55 fiz f.5 fill amplitude, all axes |
| Approvals and certificates | | |
| CCC approval | | CCC approval / marking not required for products rated \leq 36 V |

Accessories

OMH-ML300-01

Bracket for mounting ML300 series sensors

OMH-ML300-02

Bracket for mounting ML300 series sensors on a 35 mm DIN rail

V31-GM-2M-PVC

Female cordset single-ended, M8, 4-pin, **PVC** cable

V31-WM-2M-PVC

Female cordset single-ended, M8, 4-pin, **PVC** cable

V31-GM-5M-PUR

Female cordset single-ended, M8, 4-pin, PUR cable

V31-WM-5M-PUR

Female cordset single-ended, M8, 4-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com

FPEPPERL+FUCHS

Curves/Diagrams

