


Ultrasonic sensor UC500-30GM70S-2E2R2-V15


- 2 switch outputs
- Synchronization options
- Temperature compensation
- Can be parameterized via the ULTRA-PROG-IR software and interface (accessories)

Ultrasonic diffuse sensor with pivoting transducer



Dimensions





Technical Data

General specifications		
Sensing range		45 500 mm
Adjustment range		50 500 mm
Dead band		0 45 mm
Standard target plate		100 mm x 100 mm
Transducer frequency		approx. 300 kHz
Response delay		≤ 60 ms
Nominal ratings		
Temperature drift		$\leq \pm 1.5$ % of full-scale value
Time delay before availability	t _v	≤ 85 ms

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com




Technical Data

Limit data Permissible cable length max. 300 m Indicators/operating means LED yellow solid Switching state switch output 1 LED green/yellow yellow: switching state switch output 2 green: Teach-In Potentiometer Switching output 1 and Switching output 2 adjustable Electrical specifications Rated operating voltage Ue 24 V DC UB 12 ... 30 V DC (including ripple) Operating voltage ≤ 10 % Ripple No-load supply current I_0 ≤ 50 mA Interface Interface type Infrared Mode point-to-point connection Input/Output Input/output type 1 synchronization connection, bidirectional (Factory setting: synchronized mode) / Teach-In input 0 Level ≤ 3 V 1 Level ≥ 15 V Input impedance typ. 900 Ω Number of sensors max. 10 Switching output Output type 2 switch outputs PNP, NO (NC contact programmable) Default setting 50 ... 500 mm (adjustable via potentiometer) Repeat accuracy R ± 0.5 mm Operating current I_{L} per 150 mA, short-circuit/overload protected Switching frequency ≤5 Hz Switching hysteresis 5 mm (programmable) ≤ 3 V Voltage drop Off-state current ≤ 10 µA Compliance with standards and directives Standard conformity EN IEC 60947-5-2:2020 Standards IEC 60947-5-2:2019 Approvals and certificates cULus Listed, Class 2 Power Source UL approval CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions -25 ... 70 °C (-13 ... 158 °F) Ambient temperature Storage temperature -40 ... 85 °C (-40 ... 185 °F) Shock resistance 30 g, 11 ms period Vibration resistance 10 ... 55 Hz , Amplitude ± 1 mm Mechanical specifications Connection type Connector plug M12 x 1 , 5-pin Housing diameter 30 mm Degree of protection IP65 Material Housing brass, nickel-plated epoxy resin/hollow glass sphere mixture; polyurethane foam Transducer Installation position any position Mass 170 g Construction type Cylindrical

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

2

Connection



Connection Assignment




Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

Characteristic Curve


Characteristic response curve




Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

Switching outputs operating mode

Switching output mode





Ultrasonic sensor

Accessories

	BF 30	Mounting flange, 30 mm				
C C C	BF 5-30	Universal mounting bracket for cylindrical sensors with a diameter of 5 30 mm				
ø /	V15-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 5-pin, PUR cable grey				
<u>O</u> r	ULTRA-PROG-IR	Configuration software for ultrasonic sensors				
1	UC-PROG-IR-USB	Interface cable for parameterization of sensors with IrDA interface				

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

4

Indication

Displays and Controls

The sensor has two potentiometers and two display LEDs.

LED 1 (yellow)	On/off: Switching state of switching output 1 Flashing: Error when setting the switching points (switching point 2 < switching point 1). This state only occurs in window function operating mode (2 switching points).	LED 1 potentiometer 2 connector yellow		
LED 2 (yellow)	On/off: Switching state of switching output 2 Flashing: Error when setting the switching points (switching point 2 < switching point 1). This state only occurs in window function operating mode (2 switching points).			
LED 2 (green)	approx. 500 ms on: Range limit taught in Off: Normal mode			
Potentiometer 1	Setting a switching point (Default setting: Setting the switching point of switching output 1)	potentiometer 1 LED 2 temperature yellow / green sensor		
Potentiometer 2	Setting a switching point (Default setting: Setting the switching point of switching output 2)			

Function

Setting the Sensor Using the Potentiometers

The sensor is equipped with two potentiometers. These potentiometers are assigned to the two switching outputs by default. The switching outputs operate in switching point mode by default. Potentiometer P1 is used to set the switching point on switching output 1. Potentiometer P2 is used to set the switching point on switching output 2.


Note:

The function of the potentiometer can be altered using the ULTRA-PROG-IR software. As soon as a configuration has been changed, the potentiometer function selected using ULTRA-PROG-IR is activated.

Parameterization

Parameterization via ULTRA-PROG-IR

In order to be able to set the sensor parameters and adjust the sensor to the respective application, the sensor is able to communicate with a PC via the integrated infrared interface. The UC-18/30GM-IR interface cable is required to allow communication via this method. This cable is connected to an unused USB port on the PC.



The ULTRA-PROG-IR parameterization software is also required for setting the sensor parameters. The ULTRA-PROG-IR software can be downloaded for free from the www.pepperl-fuchs.com website. The software allows all open parameters to be set, including:

- All trip points and switching hystereses
- Output modes and behaviors
- Delay times
- Settings and setting ranges of the potentiometer .
- Settings for teach-in and synchronization
- Definition of blind zones
- Sensor modes and measurement methods
- Filtering measurement values
- The following service functions are also available:
- Observing and recording measurement values
- **Diagnosing interference reflections**

Teach-in

The sensor is equipped with a function input (XI). In order to teach in a limit value, this sensor must be parameterized as the Teach-in input using the ULTRA-PROG-IR parameterization software. This parameterization software allows you to specify what limit value is taught in.

Note:

The Teach-in function is not activated when the sensor is delivered.

Description of the Teach-in process:

Refer to "General Notes Relating to Pepperl+Fuchs Product Information USA: +1 330 486 0001



Ultrasonic sensor

- 1. Position an object at the required distance.
- 2. Connect the Teach-in input to L-.
- The green LED lights up briefly after approx. 3 seconds. This indicates that the required distance has been successfully saved.
- 3. Disconnect the Teach-in input from L-.

Note:

If the Teach-in input remains connected to L-, the Teach-in process is repeated every 3 seconds.

Commissioning

Synchronization

The sensor features a function input (XI). Using the ULTRA-PROG-IR parameterization software, this function input can be configured as a synchronization input to suppress mutual interference from external ultrasonic signals. This is illustrated in the following description. If the synchronization input is not connected, the sensor operates with internally generated cycle pulses.

External synchronization

The sensor can be synchronized by applying external rectangular pulses. The pulse duration must be $\geq 100 \ \mu$ s. Each rising pulse edge sends an individual ultrasonic pulse. If the signal at the synchronization input is high, the sensor reverts to the normal, unsynchronized operating mode. If a low signal is applied to the synchronization input, the sensor switches to standby. In this operating mode, the last recorded output statuses are retained.

Internal synchronization

Common mode operation

Up to ten sensors can be synchronized with each other. To do this, the synchronization inputs of the individual sensors are connected to each other. When configured in this state, all of the sensors send the ultrasonic signals together at the same time. The cycle rate corresponds to the cycle rate of the sensor with the lowest rate.

Multiplex mode

Up to ten sensors can work in multiplex mode; i.e. the sensors send their ultrasonic signals in succession. This prevents the sensor signals interfering with each other. In multiplex mode, the synchronization inputs of all sensors are connected to each other. An address must also be assigned to each sensor using the ULTRA-PROG-IR parameterization software, and the number of sensors to be synchronized must be determined. To start multiplex mode, all sensors are commissioned together by switching on the power supply.