

Safety edge PSE4-SL-01



- Safety thru-beam sensor
- Evaluation via safety control unit PSE4-SC-01
- Modulated infrared light
- For mounting in sensor strip PSE4-RUB and -ROI
- No additional mounting materials required
- Component of PSE4 modular system

Safety photoelectric sensor for the PSE4 series










Dimensions



Technical Data

Release date: 2020-10-06 Date of issue: 2020-10-06 Filename: 233909_eng.pdf


General specifications	
Effective detection range	0.4 10 m
Number of protective field beams	1
Light source	LED
Light type	modulated infrared light

PSE4-SL-01

Performance level (PL) PL e Category Cat. 4 Mission Time (T _M) 20 a Electrical specifications Operating voltage U _B Power supply via control unit Conformity Functional safety ISO 13849-1 Froduct standard EN 12978; ISO 13856-2 Approvals and certificates UL approval cULus Listed File no: NRNT.E344450 TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection Emitter: 10 m Receiver: 2.9 m Mech. capacity Son N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black			
Category Mission Time (T _M) 20 a Electrical specifications Operating voltage U _B Power supply via control unit Conformity Functional safety Product standard EN 12978; ISO 13856-2 Approvals and certificates UL approval TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature Degree of protection IP68 Connection Fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Functional safety related parameters		
Mission Time (T _M) Electrical specifications Operating voltage U _B Power supply via control unit Conformity Functional safety Product standard EN 12978; ISO 13856-2 Approvals and certificates UL approval TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature Degree of protection IP68 Connection Fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Performance level (PL)		PL e
Electrical specifications Operating voltage U _B Power supply via control unit Conformity Functional safety Product standard EN 12978; ISO 13856-2 Approvals and certificates UL approval TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature Degree of protection IP68 Connection Fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Category		Cat. 4
Operating voltage UB Power supply via control unit Conformity Functional safety ISO 13849-1 Product standard EN 12978; ISO 13856-2 Approvals and certificates UL approval CULus Listed File no: NRNT.E344450 TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Mission Time (T _M)		20 a
Conformity Functional safety Functional safety Product standard EN 12978; ISO 13856-2 Approvals and certificates UL approval UL approval TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Electrical specifications		
Functional safety Product standard EN 12978; ISO 13856-2 Approvals and certificates UL approval CULus Listed File no: NRNT.E344450 TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Operating voltage	U_B	Power supply via control unit
Product standard EN 12978 ; ISO 13856-2 Approvals and certificates UL approval cULus Listed File no: NRNT.E344450 TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE) ; Emitter: gray / Receiver: black	Conformity		
Approvals and certificates UL approval cULus Listed File no: NRNT.E344450 TÜV approval TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Functional safety		ISO 13849-1
UL approvalcULus Listed File no: NRNT.E344450TÜV approvalTÜV Rheinland 968/M 301.00/11Ambient conditionsAmbient temperature5 55 °C (41 131 °F)Mechanical specificationsDegree of protectionIP68Connectionfixed cable Emitter: 10 m Receiver: 2.9 mMech. capacity500 NMaterialHousingPolyethylene (PE); Emitter: gray / Receiver: black	Product standard		EN 12978 ; ISO 13856-2
TÜV Rheinland 968/M 301.00/11 Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Approvals and certificates		
Ambient conditions Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	UL approval		cULus Listed File no: NRNT.E344450
Ambient temperature 5 55 °C (41 131 °F) Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	TÜV approval		TÜV Rheinland 968/M 301.00/11
Mechanical specifications Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Ambient conditions		
Degree of protection IP68 Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Polyethylene (PE); Emitter: gray / Receiver: black	Ambient temperature		5 55 °C (41 131 °F)
Connection fixed cable Emitter: 10 m Receiver: 2.9 m Mech. capacity 500 N Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Mechanical specifications		
Emitter: 10 m Receiver: 2.9 m Mech. capacity Material Housing Polyethylene (PE); Emitter: gray / Receiver: black	Degree of protection		IP68
Material Housing Polyethylene (PE) ; Emitter: gray / Receiver: black	Connection		Emitter: 10 m
Housing Polyethylene (PE) ; Emitter: gray / Receiver: black	Mech. capacity		500 N
	Material		
0.11	Housing		Polyethylene (PE); Emitter: gray / Receiver: black
Cable PUR	Cable		PUR
Mass Per 150 g	Mass		Per 150 g

Connection

Receiver:



Force path diagram Measurement parameters: T = 23 °C, mounting position B as per EN 1760-2, measuring location C (EN 1760-2), v = 100 mm/s up to A, v = 10 mm/s from A. Force [N] 600 500 400 300 200 100 0 25 Path in [mm] 5 20 Point of activation using PSE4-SC-01 В С Force path diagram representing the deformation of the sensor strip under force

| Deformation under force with control unit PSE4-SC-01 | | Deformation [mm] | Force [N] | | A | Resistance | 12.8 | 80 | B | 22.0 | 250 | C | 23.0 | 400 | D | 24.0 | 600

Notes

The modular PSE system comprises the following components:

PSE4-SL safety thru-beam sensors:

The plug electronics are fully encapsulated in the housing to achieve a high level of resistance to environmental influences such as water, dust, and moisture. Degree of protection IP68 is achieved.

Rubber profiles PSE4-RUB and PSE4-ROI:

The rubber profile is designed as a double-chamber profile. The emitter and receiver are inserted in the round hollow chamber at the top. When the profile is actuated, the optical channel is interrupted and the enable circuits on the control unit open. When actuated near the end, the emitter and/or receiver dip into the lower chamber. This ensures that the beam of light is broken. However, the forces required are high, meaning the end areas are inactive areas in line with EN 1760-2.

PSE safety control units:

Controller for the emitter/receiver system.


PSE4-ALU aluminum rails:

The aluminum rails are available in various lengths and can be used as an option.

Functional Principle

The emitter transmits pulses of infrared light, which are detected by the receiver. When the emitter light is detected, the receiver turns off the emitter via a control input. The "luminous flux" stops. The receiver also detects this status and the emitter is then switched on again after a specified time. This coupling produces a dynamic signal that is conveyed, in principle, to a charge pump. The pump's charge state is analyzed in the evaluation.

Any errors in the emitter/receiver system affect the optical or electrical signal, which results in the absence of a dynamic signal.



Note:

Safety edges must be fully installed to comply with the EC-Type Examination Certificate for the PSE4 series.

Possible combinations


	PSE4-ALU-*	PSE4-ALU-3009-*	PSE4-ROI-*	PSE4-RUB-*	PSE4-RUB-30EPDM58-*	PSE2-SC-*	PSE4-SC-*	PSE4-SL-*
PSE4-ALU-*			Χ	Х	-	Х	Χ	Χ
PSE4-ALU-3009-*			-	-	Х	Х	Χ	Χ
PSE4-ROI-*	Х	-				Х	Х	Χ
PSE4-RUB-*	Х	-				Х	Х	Χ
PSE4-RUB-30EPDM58-*	-	Х				Х	Х	Χ
PSE2-SC-*	Х	Х	Х	Х	Х			Χ
PSE4-SC-*	Х	Х	Х	Χ	Х			Χ
PSE4-SL-*	Χ	Χ	Χ	Χ	Χ	Χ	Χ	

Mounting

Mounting or replacing the sensors

Sensor strip PSE4-RUB-XX or PSE4-ROI-XX and accompanying aluminum mounting

Cut PSE4-ALU-XX to the required length.



Slide the emitter and receiver into the upper chamber.

Guide the emitter cable through the lower chamber to the receiver side.

Other suitable accessories can be found at www.pepperl-fuchs.com

In its entirety, the PSE4 safety edge system consists of the control interface, sensors, a rubber sensor strip, and an optional aluminum mounting strip.

The system can be used within a temperature range of 5 °C to 55 °C.

The control interface analyzes the signal from the sensors and is designed to be installed in a switch cabinet.

The safety contact of the control interface is released by actuating the safety edge.

The system as a whole can be used in applications up to Cat. 4/PL e as defined in EN ISO 13849-1.