Release date: 2023-05-09 Date of issue: 2023-05-09 Filename: 235087_eng.pdf

C Co

Inductive sensor

NBN3-F31K2M-E8-B13-S


- Direct mounting on standard actuators
- Rugged metal base
- Weatherproof housing for outdoor applications
- Temperature range -40 ... 167 °F (-40°C to 75°C)
- LED for power on
- LEDs for switching state of sensor and solenoid valve
- Plug-in terminals





Installation


The connections to this sensor are sealed with stopping plugs to protect against dirt and moisture. If not all of the connections are used in your application, then seal the remaining stopping plugs on the sensor permanently or check during initial installation and when performing regular maintenance work that the stopping plugs are secure and impermeable. If necessary, tighten the stopping plugs to a torque of 1 Nm.

Dimensions










Technical Data

Outliable as forestion		0aarraallaaraa (NO)
Switching function		2 x normally open (NO)
Output type		PNP
Rated operating distance	Sn	2.5 mm
Installation		for non-flush mounting
Output polarity		DC
Assured operating distance	Sa	0 2.05 mm
Output type		4-wire
Nominal ratings		
Operating voltage	U_B	10 30 V
Switching frequency	f	0 100 Hz
Hysteresis	Н	typ. 5 %
Reverse polarity protection		all connections
Short-circuit protection		pulsing
Voltage drop	U_d	≤3 V
Operating current	lμ	0 100 mA
Off-state current	l _r	$0 \dots 0.5$ mA typ. $0.1~\mu A$
No-load supply current	I_0	≤ 25 mA
Operating voltage indicator		LED, green
Switching state indicator		LED, yellow
Valve status indicator		LED, yellow
Functional safety related parameters		
MTTF _d		490 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Valve circuit		
Voltage		max. 32 V DC
Current		max. 240 mA
Short-circuit protection		no
Reverse polarity protection		yes, with reversed output LED is out of function, therfore more power for solenoid valve
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012 VDI / VDE 3845
Approvals and certificates		
UL approval		cULus Listed, General Purpose, Class 2 Power Source
Ambient conditions		
Ambient temperature		-40 75 °C (-40 167 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Mechanical specifications		
Connection (system side)		screw terminal, M20 x 1.5 cable gland
Core cross section (system side)		1.5/2.5 mm² flexible/rigid
Connection (valve side)		screw terminal , Cable gland M20 x 1.5
Housing material		rugged, translucent polycarbonate (PC) optimised for outdoor use
Housing base		powder coated aluminum
Degree of protection		IP66 / IP68 / IP69
Tightening torque, fastening screws		4 Nm 5 Nm
Tightening torque, housing screws		≤ 2 Nm
Tightening torque of cover srews		1.5 Nm
Tightening torque, earthing screw		1.5 Nm
Tightening torque, cable gland		M20 x 1.5 ; max. 11 Nm

2

Connection



Matching System Components

BT115A	Activator for F31 series
BT115X	Activator for F31 series

Accessories

BT65-F31K2-RG-EN	Activator for F31K2 series
BT65A	Activator for F31 series
BT65X	Activator for F31 series