


# Cable connector

## V31S-GM-BK1M-PUR-U




- Suitable for drag chains and abrasion resistant
- Suitable for robotic applications / torsion resistant
- Degree of protection IP68
- Free of paint wetting interfering substances
- Resistant to microbes and hydrolysis
- UV resistant
- UL listed for USA and Canada
- Halogen-free
- Specific design protects against loosening and inaccurate installation

Male cordset single-ended M8 straight A-coded, 4-pin, PUR cable black, UL-approved, drag chain suitable, torsion resistant



### Dimensions



### Technical Data

#### General specifications

|                   |                  |
|-------------------|------------------|
| Connector 1       |                  |
| Connection        | plug             |
| Construction type | M8               |
| Style             | straight         |
| Locking           | screw connection |
| Number of pins    | 4                |
| Coding            | A-coded          |
| Connector 2       |                  |
| Connection        | cable end        |

#### Electrical specifications

|                   |       |                 |
|-------------------|-------|-----------------|
| Operating voltage | $U_B$ | max. 30 V AC/DC |
| Operating current | $I_B$ | max. 4 A        |

#### Conformity

|                      |                                    |
|----------------------|------------------------------------|
| Degree of protection | EN 60529                           |
| Plug connection      | connector M8 x 1 : IEC 61076-2-104 |
| Flammability         | UL 1581; DIN EN 60332-2-2          |
| Halogen-free         | IEC 60754-1                        |

#### Approvals and certificates

|                |  |
|----------------|--|
| UL approval    | AWM STYLE 20549 AWM I/II A/B 80°C 300V FT2 (cable) |
| UL File Number | E231213  |

#### Ambient conditions

|                     |  |
|---------------------|--|
| Ambient temperature |  |
|---------------------|--|

Release date: 2023-09-04 Date of issue: 2023-09-04 Filename: 240807-100002\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Technical Data

|                                  |   |   |
|----------------------------------|---|---|
| Plug connector                   |   | -40 ... 90 °C (-40 ... 194 °F)                                  |
| Cable, fixed                     |   | -40 ... 80 °C (-40 ... 176 °F)                                  |
| Cable, flexing                   |   | -20 ... 80 °C (-4 ... 176 °F)                                   |
| Pollution degree                 |   | 3   |
| <b>Mechanical specifications</b> |   |   |
| Plug connector                   |   |   |
| Tightening torque                |   | 0.4 Nm  |
| Loosening protection             |   | available   |
| Tool installation                |   | straight knurling and hexagon nut SW = 9 mm                     |
| Mating cycles                    |   | min. 100  |
| Degree of protection             |   | IP68  |
| Cable                            |   | according to IEC/EN 60228 (DIN VDE 0295) class 6                |
| Sheath diameter                  |   | 4.3 mm  |
| Bending radius                   |   | > 10 x cable diameter, moving<br>> 5 x cable diameter, fixed    |
| Sheath stripping force           |   | max. 80 N / 300 mm  |
| Sheath color                     |   | black (similar to RAL 9005)                                     |
| Number of cores                  |   | 4   |
| Core cross section               |   | 0.34 mm <sup>2</sup>  |
| Cores color                      |   | Core 1: brown<br>Core 2: white<br>Core 3: blue<br>Core 4: black |
| Core construction                |   | 42 x 0.1 mm Ø   |
| Length                           | L | 1 m   |
| Cable code                       |   | Li 9Y 11Y 4 x 0.34  |
| <b>Drag chain suitability</b>    |   |   |
| Drag chain cycles                |   | min. 5000000  |
| Motion velocity                  |   | max. 3.3 m/s  |
| Traverse distance                |   | max. 5 m  |
| Acceleration                     |   | max. 5 m/s <sup>2</sup>   |
| Torsion cycles                   |   | min. 1000000  |
| Torsional stress                 |   | ± 180 °/m   |
| <b>Material</b>                  |   |   |
| PWIS free                        |   | yes   |
| Halogen-free                     |   | yes   |
| <b>Plug connector</b>            |   |   |
| Screw connection                 |   | Zinc diecast, nickel-plated                                     |
| Body                             |   | TPU, black  |
| Contact surface                  |   | gold plated (Au)  |
| Flammability                     |   | V-2   |
| <b>Cable</b>                     |   |   |
| Sheathing                        |   | PUR based on polyether  |
| Core insulation                  |   | PP  |
| UV resistance                    |   | yes   |
| Chemical resistance              |   | good  |
| Oil resistance                   |   | yes   |
| Cooling lubricant resistance     |   | yes   |
| Microbial resistance             |   | yes   |
| Hydrolysis resistance            |   | yes   |
| Flammability                     |   | FT2   |

Release date: 2023-09-04 Date of issue: 2023-09-04 Filename: 240807-100002\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com


USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com






Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

## Connection



## Accessories

|   |                          |  |
|---|--------------------------|--|
|  | <b>MH V3-SCREWDRIVER</b> | Torque screwdriver (0.4 Nm)                |
|  | <b>MH V3-BIT M8</b>      | plug-in cap for M8                         |
|  | <b>V1/V3-LABELHOLDER</b> | Label holder                               |
|  | <b>V1/V3-LABEL</b>       | Label plate                                |
|  | <b>MH V3-Holder</b>      | Modular universal holder for M8 connectors |

Release date: 2023-09-04 Date of issue: 2023-09-04 Filename: 240807-100002\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com