



## Inductive sensor NBN3-F31K2-E8-B33-S


- Direct mounting on standard actuators
- Weatherproof housing for outdoor applications
- Temperature range -40 ... 167 °F (-40°C to 75°C)
- LED for power on
- LEDs for switching state of sensor and solenoid valve
- Plug-in terminals



### Installation

The connections to this sensor are sealed with stopping plugs to protect against dirt and moisture. If not all of the connections are used in your application, then seal the remaining stopping plugs on the sensor permanently or check during initial installation and when performing regular maintenance work that the stopping plugs are secure and impermeable. If necessary, tighten the stopping plugs to a torque of 1 Nm.

### Dimensions



### Technical Data

#### General specifications

|                          |                        |
|--------------------------|------------------------|
| Switching function       | 2 x normally open (NO) |
| Output type              | PNP                    |
| Rated operating distance | s <sub>n</sub> 2.5 mm  |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PEPPERL+FUCHS**

## Technical Data

|                                                 |                |                                                                                                                                                                                         |
|-------------------------------------------------|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Installation                                    |                | for non-flush mounting                                                                                                                                                                  |
| Output polarity                                 |                | DC                                                                                                                                                                                      |
| Assured operating distance                      | s <sub>a</sub> | 0 ... 2.05 mm                                                                                                                                                                           |
| Output type                                     |                | 4-wire                                                                                                                                                                                  |
| <b>Nominal ratings</b>                          |                |                                                                                                                                                                                         |
| Operating voltage                               | U <sub>B</sub> | 10 ... 30 V                                                                                                                                                                             |
| Switching frequency                             | f              | 0 ... 100 Hz                                                                                                                                                                            |
| Hysteresis                                      | H              | typ. 5 %                                                                                                                                                                                |
| Reverse polarity protection                     |                | all connections                                                                                                                                                                         |
| Short-circuit protection                        |                | pulsing                                                                                                                                                                                 |
| Voltage drop                                    | U <sub>d</sub> | ≤ 3 V                                                                                                                                                                                   |
| Operating current                               | I <sub>L</sub> | 0 ... 100 mA                                                                                                                                                                            |
| Off-state current                               | I <sub>r</sub> | 0 ... 0.5 mA typ. 0.1 µA                                                                                                                                                                |
| No-load supply current                          | I <sub>0</sub> | ≤ 25 mA                                                                                                                                                                                 |
| Operating voltage indicator                     |                | LED, green                                                                                                                                                                              |
| Switching state indicator                       |                | LED, yellow                                                                                                                                                                             |
| Valve status indicator                          |                | LED, yellow                                                                                                                                                                             |
| <b>Functional safety related parameters</b>     |                |                                                                                                                                                                                         |
| MTTF <sub>d</sub>                               |                | 605 a                                                                                                                                                                                   |
| Mission Time (T <sub>M</sub> )                  |                | 20 a                                                                                                                                                                                    |
| Diagnostic Coverage (DC)                        |                | 0 %                                                                                                                                                                                     |
| <b>Valve circuit</b>                            |                |                                                                                                                                                                                         |
| Voltage                                         |                | max. 32 V DC                                                                                                                                                                            |
| Current                                         |                | max. 240 mA                                                                                                                                                                             |
| Short-circuit protection                        |                | no                                                                                                                                                                                      |
| Reverse polarity protection                     |                | yes, with reversed output LED is out of function, therefore more power for solenoid valve                                                                                               |
| <b>Compliance with standards and directives</b> |                |                                                                                                                                                                                         |
| Standard conformity                             |                |                                                                                                                                                                                         |
| Standards                                       |                | EN IEC 60947-5-2                                                                                                                                                                        |
| <b>Approvals and certificates</b>               |                |                                                                                                                                                                                         |
| UL approval                                     |                | cULus Listed<br>Load Type: General Purpose<br>Circuitry: Class 2 Power Source<br>Enclosure Type Rating: Type 1<br>Supply/Switching Voltage: 30 V DC<br>Output Switching Current: 200 mA |
| <b>Ambient conditions</b>                       |                |                                                                                                                                                                                         |
| Ambient temperature                             |                | -40 ... 75 °C (-40 ... 167 °F)                                                                                                                                                          |
| Storage temperature                             |                | -40 ... 85 °C (-40 ... 185 °F)                                                                                                                                                          |
| <b>Mechanical specifications</b>                |                |                                                                                                                                                                                         |
| Connection (system side)                        |                | screw terminal , M20 x 1.5 cable gland                                                                                                                                                  |
| Core cross section (system side)                |                | 1.5/2.5 mm <sup>2</sup> flexible/rigid                                                                                                                                                  |
| Connection (valve side)                         |                | 4-pin, M12 x 1 socket                                                                                                                                                                   |
| Housing material                                |                | rugged, translucent polycarbonate (PC) optimised for outdoor use                                                                                                                        |
| Housing base                                    |                | PC                                                                                                                                                                                      |
| Degree of protection                            |                | IP66 / IP67 / IP69                                                                                                                                                                      |
| Tightening torque, fastening screws             |                | ≤ 5 Nm                                                                                                                                                                                  |
| Tightening torque, housing screws               |                | 1.5 Nm                                                                                                                                                                                  |
| Tightening torque, cable gland                  |                | M20 x 1.5 ; max. 7 Nm<br>M12 x 1 max. 3 Nm                                                                                                                                              |
| Tightening torque, stopping plug                |                | 1 Nm                                                                                                                                                                                    |
| <b>Dimensions</b>                               |                |                                                                                                                                                                                         |
| Height                                          |                | 53 mm                                                                                                                                                                                   |
| Width                                           |                | 100 mm                                                                                                                                                                                  |
| Length                                          |                | 106 mm                                                                                                                                                                                  |

Release date: 2025-07-02 Date of issue: 2025-07-02 Filename: 244541\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.comUSA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.comGermany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com
 **PEPPERL+FUCHS**

Connection Assignment

