

AS-Interface Gateway/Safety Monitor VBG-PB-K30-DMD-S16-EV

- Gateway and safety monitor in one housing
- Connection to PROFIBUS DP
- SafeLink
- Certified up to SIL 3 according to IEC 61508 and EN 62061 and up to PL_{e} according to EN 13849
- 2 AS-Interface networks
- 2 safe output relays and 2 safe electronic outputs
- Integrated data decoupling
- Diagnostics via RJ45 Ethernet port
- AS-Interface POWER24

Gateway with integrated Safety Monitor



Function

The VBG-PB-K30-DMD-S16-EV is a PROFIBUS gateway with a safety monitor and a double master according to AS-Interface specification 3.0. The gateway is used to connect AS-Interface systems to a higher-level PROFIBUS. It acts as a master for the AS-Interface segment and as a slave for the PROFIBUS. During cyclic and acyclic data exchange, the AS-Interface functions are provided via PROFIBUS - DP V1. During cyclic data exchange the binary data of an AS-Interface segment is transferred. Analog values as well as the complete command set of the new AS-Interface specification are transferred via PROFIBUS using a command interface.

The gateway has four inputs and four outputs. The four inputs are used either for extended EDM device monitoring or as start inputs. Two sets of two outputs act as relay outputs and switch output circuits 1 and 2 and, as semiconductor outputs, output circuits 3 and 4. The K30 model is particularly suitable for installation in a control cabinet.

Configuration of the device can be performed using switches. Seven LED located on the front panel indicate the current status of the AS-Interface segment. One LED shows the power supply via AUX. A further eight LEDs indicate the status of the inputs and outputs.


With the graphical display, the commissioning of the AS-Interface circuits and testing of the connected peripherals can take place completely separately from the commissioning of the higher-level network and the programming. With the 4 switches, all functions can be controlled and visualized on the display.


An RJ-45 Ethernet port provides a way of exporting data relating to the gateway, network and operation directly from the gateway for extended local diagnosis purposes.

Via the RJ-45 Ethernet diagnostic interface, up to 31 devices can establish a secure cross-communication. The integrated data decoupling allows to operate 2 AS-Interface circuits with just a standard power supply.

The integrated data decoupling allows to operate 2 AS-Interface circuits with just a standar The device has a card slot for a memory card for the storage of configuration data.

Dimensions





Technical Data

General specifications

AS-Interface specification PLC-Functionality V3.0 activateable

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



AS-Interface Gateway/Safety Monitor

Technical Data

VBG-PB-K30-DMD-S16-EV

| Duplicate address detection | | from AS-Interface slaves |
|--------------------------------------|----------------|--|
| Earth fault detection | EFD | integrated |
| EMC monitoring | | integrated |
| Diagnostics function | | Extended function via display |
| Data decoupling | | integrated |
| Switch-on delay | | < 10 s |
| Response delay | | < 40 ms |
| UL File Number | | E223772 only from low voltage, limited energy source (SELV or PELV) or listed Class 2 source |
| Functional safety related parameters | | |
| Safety Integrity Level (SIL) | | SIL 3 |
| Performance level (PL) | | PLe |
| MTTF _d | | 200 a |
| B _{10d} | | 2 E+7 |
| Indicators/operating means | | |
| Display | | Illuminated graphical LC display for addressing and error messages |
| LED PROFIBUS | | PROFIBUS master detected; LED green |
| LED AS-i ACTIVE | | AS-Interface operation normal; LED green |
| LED CONFIG ERR | | configuration error; LED red |
| LED PRG ENABLE | | autom. programming; LED green |
| LED POWER | | voltage ON; LED green |
| LED PRJ MODE | | projecting mode active; LED yellow |
| LED U AS-i | | AS-Interface voltage; LED green |
| LED AUX | | ext. auxiliary voltage U _{AUX} ; LED green |
| LED EDM/Start | | External device monitoring circuit inputs closed, 4x yellow LEDs |
| LED output circuit | | Output circuit closed; 4 x green LEDs |
| Button | | 4 |
| Electrical specifications | | |
| Insulation voltage | Ui | ≥ 500 V |
| Rated operating voltage | U _e | 30 V DC 20 31.6 V (PELV) |
| Rated operating current | le | 300 mA (PELV) |
| Power supply | | max. 4 A per AS-Interface circuit |
| Interface 1 | | |
| Interface type | | RS-485 |
| Protocol | | PROFIBUS DP V1 |
| Transfer rate | | 9.6 kBit/s / 12 MBit/s , Automatic baud rate detection |
| Interface 2 | | |
| Interface type | | Ethernet: RJ-45 Diagnostic Interface |
| Interface 3 | | |
| Interface type | | Chip card slot |
| Input | | |
| Number/Type | | 4 EDM/Start inputs: EDM: Inputs for the external device monitoring circuits Start: start inputs: Static switching current 4 mA at 24 V, dynamic 30 mA at 24 V (T=100 μs) |
| Output | | |
| Safety output | | Output circuits 1 and 2: 2 potential-free contacts, max. contact load: 3 A_{DC-13} at 30 V_{DC} , 3 A_{AC-15} at 30 V_{AC} Output circuits 3 and 4: 2 PNP transistor outputs max. contact load: 0.5 A_{DC-13} at 30 V_{DC} |
| Connection | | |
| PROFIBUS | | Sub-D interface |
| | | |

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Gr

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Release date: 2022-03-24 Date of issue: 2022-03-24 Filename: 245875_eng.pdf


Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

AS-Interface Gateway/Safety Monitor

VBG-PB-K30-DMD-S16-EV


| Technical Data | |
|-------------------------------|--|
| AS-Interface | spring terminals, removable |
| Directive conformity | |
| Electromagnetic compatibility | |
| Directive 2014/30/EU | EN 62026-2:2013 EN 61000-6-2:2005, EN 61000-6-4:2007 |
| Standard conformity | |
| Electromagnetic compatibility | EN 61000-6-2:2005, EN 61000-6-4:2007 |
| Degree of protection | EN 60529:2000 |
| Fieldbus standard | PROFIBUS according to DIN 19245 Part 3 |
| AS-Interface | EN 62026-2:2013 |
| Shock resistance | EN 61131-2:2004 |
| Standards | IEC 61508:2010 (SIL3) IEC 62061:2005 (SIL3) EN ISO 13849-1:2008 (PL e) |
| Approvals and certificates | |
| UL approval | An isolated source with a secondary open circuit voltage of ≤ 30 V _{DC} with a 3 A maximum over current protection. Over current protection is not required when a Class 2 source is employed. UL mark does not provide UL certification for any functional safety rating or aspects of the device. |
| CCC approval | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions | |
| Ambient temperature | 0 55 °C (32 131 °F) |
| Storage temperature | -25 85 °C (-13 185 °F) |
| Mechanical specifications | |
| Degree of protection | IP20 |
| Material | |
| Housing | Stainless steel |
| Mass | 800 g |
| Construction type | Low profile housing , Stainless steel |

Connection



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Assembly



Installation

Supply of 2 AS-Interface circuits and optional supply of several gateways with one power supply unit. For short cable lengths, a standard 24 V power supply can be used.

Operation

In an AS-Interface network only one device can be operated earth fault detection. If there are many devices in an AS-Interface network, this can lead to the earth fault monitoring response threshold becoming less sensitive.

Accessories

| | VAZ-SW-SIMON+ | Software for configuration of K30 Master Monitors/K31 and KE4 Safety Monitors |
|------------|---------------|---|
| | | |
| Brings.com | | |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

