


Thru-beam sensor, 30 m detection range, red light, light on, sensitivity adjustment, AC/DC version, relais output, fixed cable

# 

**Dimensions** 



# **Technical Data**

#### System components

Release date: 2023-10-13 Date of issue: 2023-10-13 Filename: 246997\_eng.pdf

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 G

LA31/115



### LA31/LK31/16/25/31/115

Receiver		
		LK31/16/25/31/115
eneral specifications		
Effective detection range		0 30 m
Threshold detection range		43 m
Light source		LED
Light type		modulated visible red light , 630 nm
Alignment aid		LED yellow: 1. LED illuminates: Sufficient light signal received, emitter and receiver alignment is correct 2. LED flashes: Reaching switching point 3. LED off: Light beam is interrupted or the alignment is out
Diameter of the light spot		approx. 800 mm at a distance of 30 m
Opening angle		Emitter: 0.5 ° , Receiver: 1.5 °
Ambient light limit		50000 Lux ; according to EN 60947-5-2
unctional safety related parameters		
		620 a
Mission Time ( $T_M$ )		20 a
Diagnostic Coverage (DC)		0%
ndicators/operating means		
Operation indicator		LED green: power on
Function indicator		LED yellow: 1. LED lit constantly: signal > 2 x switching point (function reserve) 2. LED flashes: signal between 1 x switching point and 2 x switching point 3. LED off: signal < switching point
Control elements		sensitivity adjustment
lectrical specifications		
Operating voltage	$U_B$	24 240 V AC 12 240 V DC
No-load supply current	I <sub>0</sub>	Emitter: ≤ 20 mA Receiver: ≤ 20 mA
Power consumption	P <sub>0</sub>	Emitter: ≤ 1 VA Receiver: ≤ 1 VA
Putput		
Switching type		light-on
Signal output		Relay, 1 alternator
Switching voltage		max. 250 V AC/DC
Switching current		max. 3 A
Switching power		DC: max. 150 W AC: max. 750 VA
Switching frequency	f	≤ 20 Hz
Response time		≤ 25 ms
conformity		
Product standard		EN 60947-5-2
compliance with standards and directives		
Standard conformity		
Standards		EN 62103
pprovals and certificates		
Protection class		II , rated voltage $\leq$ 250 V AC with pollution degree 1-2 according to IEC 60664-1 Output circuit basis insulation of input circuit according to EN 50178, rated insulatio voltage 240 V AC
CCC approval		Certified by China Compulsory Certification (CCC)
mbient conditions		
A 11 11		-25 55 °C (-13 131 °F)
Ambient temperature		-40 70 °C (-40 158 °F)
•		
Storage temperature		
Storage temperature		18 mm
Storage temperature		

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

2

#### **Technical Data**

Degree of protection	IP67
Connection	Emitter: 2 m fixed cable,2-wire Receiver: 2 m fixed cable,5-wire
Material	
Housing	Polycarbonate
Optical face	PMMA
Mass	Emitter: 116 g Receiver: 131 g


# **Connection Assignment**



#### **Characteristic Curve**

10

----



20

30

40

50

Distance X [m]

0

0

----

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3

### **Characteristic Curve**

#### Relative received light strength Stability control

#### Accessories

	OMH-RL31-01	Mounting bracket
	OMH-RL31-02	Mounting bracket narrow
	OMH-RL31-03	Mounting bracket narrow
50	OMH-RL31-04	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-RL31-05	Mounting bracket for mounting on flat surfaces with 2 M4 screws
a lui	OMH-RL31-06	Stainless steel mounting bracket with adjustable half clamp on the side

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".