



Retroreflective sensor MLV41-6/25/70/136



- Rugged series in corrosion-resistant metal housing
- Extremely high switching frequency
- Clear and functional display concept for the operating modes
- Resistant against noise: reliable operation under all conditions
- Aluminum housing with high quality Delta-Seal coated


Robust retroreflective sensor, compact housing design, 9.5 m detection range, red light, 2 push-pull outputs, M9 plug



Function

The unique and extremely popular design of the MLV41 series enables it be mounted correctly in confined areas and offers all the functions that are normally only found on larger phototelectric sensors. The MLV41 series comes with a range of functions. For example, highly visible status LEDs on the front and back, resistance to ambient light, crosstalk protection and universally applicable output stages that permit every possible switching logic and polarity to be realized. The enhanced resistance to ambient light ensures reliable operation even where modern energy-saving lamps with electronic ballasts are in use. The same applies where multiple devices are present, i.e. the use of a number of sensors in the same vicinity causes no problems.

Dimensions



General specifications					
Effective detection range	0 9.5 m				
Reflector distance	Foil reflector 0.05 3 m Retro-reflector 0.01 9.5 m				
Threshold detection range	12 m				
Reference target	OFR-22800/76, H85-2 reflector				
Light source	LED				
Light type	modulated visible red light , 625 nm				
Polarization filter	no				
Angle deviation	max. \pm 1.5 $^{\circ}$				
Diameter of the light spot	approx. 300 mm at detection range 8.5 m				
Opening angle	1.5 °				
Optical face	frontal				
Ambient light limit	20000 Lux				
Functional safety related parameters					
MTTF _d	940 a				
Mission Time (T_M)	20 a				
Diagnostic Coverage (DC)	0 %				
Indicators/operating means					

Operation indicator

Function indicator


Technical Data

LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz)

 $\ensuremath{\mathsf{LED}}$ yellow, lights up when light beam is free, flashes when falling short of the operating reserve

Technical Data		
Control elements		none
Electrical specifications		
Operating voltage	U_B	10 30 V DC
Ripple		max. 10 %
No-load supply current	I _o	max. 30 mA
Output		
Signal output		2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	U_{d}	≤ 2.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus Listed 57M3 (Only in association with UL Class 2 power supply; Type 1 enclosure)
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-40 60 °C (-40 140 °F)
Storage temperature		-40 75 °C (-40 167 °F)
Mechanical specifications		
Housing width		31 mm
Housing height		56.5 mm
Housing depth		13.6 mm
Degree of protection		IP67
Connection		with M9, 5-pin metal connector
Material		
Housing		Aluminum , Delta-Seal coated
Optical face		glass pane
Connector		metal
Mass		50 g

Connection Assignment



Note:

In the case of replacements for MLV40, the differing pin assignment (EURO standard) must be taken into account

O = Light on

= Dark on

3

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 244369_eng.pdf


Connection Assignment




Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	RK	(black)


Assembly






			3	Optical axis transmitter
			4	Optical axis receiver

Characteristic Curve





Accessories

(E)	ОМН-09	Mounting bracket for Sensors series MLV41 for M12 rod mounting
	OMH-40	Mounting bracket
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap
	REF-VR10	Reflector, rectangular 60 mm x 19 mm, mounting holes
	ORR50G	Reflector, rectangular 50.9 mm x 60.9 mm, mounting holes, fixing strap and polarization filter
	OFR-100/100	Reflective tape 100 mm x 100 mm