

Universal Temperature Converter KFD2-UT2-2-1

- 2-channel signal conditioner
- 24 V DC supply (Power Rail)
- Thermocouple, RTD, potentiometer or voltage input
- Usable as signal splitter (1 input and 2 outputs)
- Voltage output 0/1 V ... 5 V
- Configurable by PACTware
- Line fault (LFD) and sensor burnout detection
- Up to SIL 2 acc. to IEC/EN 61508 / IEC/EN 61511


(€ SIL2

Function

This signal conditioner provides the galvanic isolation between field circuits and control circuits.

The device converts the signal of a resistance thermometer, thermocouple, or potentiometer to a proportional output voltage. The device converts the signal of a resistance thermometer, thermocouple, or potentioneter to a proportional output voltage. The device can also be configured as a signal splitter. The removable terminal block K-CJC-** is available as an accessory for internal cold junction compensation of thermocouples. A fault is signalized by LEDs acc. to NAMUR NE44 and a separate collective error message output. The device is easily configured by the use of the PACTware configuration software. For additional information, refer to the manual and www.pepperl-fuchs.com.

Connection



Technical Data

General specifications		
Signal type		Analog input
Functional safety related parameters		
Safety Integrity Level (SIL)		SIL 2
Supply		
Connection		terminals 14+, 15- or power feed module/Power Rail
Rated voltage	Ur	20 30 V DC
Ripple		within the supply tolerance
Power dissipation		≤ 0.8 W
Power consumption		max. 0.8 W

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com




Technical Data

Interface	
Programming interface	programming socket
Input	
Connection side	field side
Connection	terminals 1, 2, 3; 4, 5, 6
RTD	type Pt10, Pt50, Pt100, Pt500, Pt1000 (EN 60751: 1995) type Pt10GOST, Pt50GOST, Pt100GOST, Pt500GOST, Pt1000GOST (6651-94) type Cu10, Cu50, Cu100 (P50353-92) type Ni100 (DIN 43760)
Measuring current	approx. 200 μA with RTD
Types of measuring	2-, 3-wire connection
Lead resistance	max. 50 Ω per line
Measurement loop monitoring	sensor breakage, sensor short-circuit
Thermocouples	type B, E, J, K, N, R, S, T (IEC 584-1: 1995) type L (DIN 43710: 1985) type TXK, TXKH, TXA (P8.585-2001)
Cold junction compensation	external and internal
Measurement loop monitoring	sensor breakage
Potentiometer	0 20 k Ω (2-wire connection), 0.8 20 k Ω (3-wire connection)
Voltage	selectable within the range -100 100 mV
Input resistance	≥ 1 MΩ (-100 100 mV)
Output	
Connection side	control side
Voltage output	$0 \hdots 5 \ensuremath{V}$ or $1 \hdots 5 \ensuremath{V}$; output resistance: $\leq 5 \ensuremath{\Omega}$; load: $\geq 10 \ensuremath{k\Omega}$
Connection	output I: terminals 7-, 8+ output II: terminals 10-, 11+
Fault signal	downscale 0 V or 0.5 V, upscale 5.375 V
Transfer characteristics	
Deviation	
After calibration	$\begin{array}{l} Pt100:\pm(0.06\ \%\ of\ measurement\ value\ in\ K+0.1\ K\ (4-wire\ connection))\\ thermocouple:\ \pm\ (0.05\ \%\ of\ measurement\ value\ in\ ^C\ +\ 1\ K\ (1.2\ K\ for\ types\ R\ and\ S))\ ,\\ includes\ \pm\ 0.8\ K\ fault\ of\ the\ cold\ junction\ compensation\ (CJC)\\ mV:\ \pm\ 50\ \muV\\ potentiometer:\ \pm\ 0.05\ \%\ of\ full\ scale,\ (excludes\ faults\ due\ to\ lead\ resistance)\\ output:\ 1\ to\ 5\ V\ output:\ \pm\ 4\ mV\ from\ 0\ to\ 103.1\ \%\ of\ span;\ 0\ to\ 5\ V\ output:\ \pm\ 4\ mV\ from\ 0.3\ to\ 102.5\ \%\ of\ span \end{array}$
Influence of ambient temperature	Pt100: ± (0.0015 % of measurement value in K + 0.006 % of span)/K ΔT_{amb} [*]) thermocouple: ± (0.02 K + 0.005 % of measurement value in °C + 0.006 % of span)/K ΔT_{amb} [*]), influence of cold junction compensation (CJC) included mV: ± (0.01 % of measurement value + 0.006 % of span)/K ΔT_{amb} [*]) potentiometer: ± 0.006 % of span/K ΔT_{amb} [*]) [*]) ΔT_{amb} = ambient temperature change referenced to 23 °C (296 K)
Influence of supply voltage	< 0.01 % of span
Reaction time	worst case value (sensor breakage and/or sensor short circuit detection enabled) mV: 1.2 s, thermocouples with CJC: 1.4 s, thermocouples with fixed ref. temp: 1.4 s, 3- or 4-wire RTD: 1.1 s, 2-wire RTD: 920 ms, Potentiometer: 3-wire connection 2.8 s, 2-wire connection 2.25 s
Galvanic isolation	
Input/Other circuits	basic insulation according to IEC 61010-1, rated insulation voltage 300 $\mathrm{V}_{\mathrm{eff}}$
Output/supply, programming input	functional insulation, rated insulation voltage 50 V AC There is no electrical isolation between the programming input and the supply. The programming cable provides galvanic isolation so that ground loops are avoided.
Indicators/settings	
Display elements	LEDs
Configuration	via PACTware
Labeling	space for labeling at the front
Directive conformity	
Electromagnetic compatibility	
Directive 2014/30/EU	EN 61326-1:2013 (industrial locations)
Conformity	
Electromagnetic compatibility	NE 21:2006

Release date: 2023-01-03 Date of issue: 2023-01-03 Filename: 248763_eng.pdf

Technical Data	
Degree of protection	IEC 60529:2001
Ambient conditions	
Ambient temperature	-20 60 °C (-4 140 °F)
Mechanical specifications	
Degree of protection	IP20
Connection	screw terminals
Mass	approx. 130 g
Dimensions	20 x 119 x 115 mm (0.8 x 4.7 x 4.5 inch) (W x H x D) , housing type B2
Mounting	on 35 mm DIN mounting rail acc. to EN 60715:2001
General information	
Supplementary information	Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

Assembly



Match	ing System Comp	oonents
<u>O</u> r	DTM Interface Technology	Device type manager (DTM) for interface technology
PACTware V	PACTware 5.0	FDT Framework
	K-ADP-USB	Programming adapter with USB interface
	KFD2-EB2	Power Feed Module
	UPR-03	Universal Power Rail with end caps and cover, 3 conductors, length: 2 m

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Matching Sy	vstem Com	ponents

UPR-03-M	Universal Power Rail with end caps and cover, 3 conductors, length: 1,6 m
UPR-03-S	Universal Power Rail with end caps and cover, 3 conductors, length: 0.8 m
K-DUCT-GY	Profile rail, wiring comb field side, gray
K-DUCT-GY-UPR-03	Profile rail with UPR-03-* insert, 3 conductors, wiring comb field side, gray

Accessories

	К-СЈС-ВК	Terminal block for cold junction compensation, 3-pin screw terminal, black
	KF-ST-5GN	Terminal block for KF modules, 3-pin screw terminal, green
*	KF-CP	Red coding pins, packaging unit: 20 x 6

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0002
 Getwww.pepperl-fuchs.com
 ga-info@us.pepperl-fuchs.com
 ga-info@us.pepperl-fuchs.com

4