



Vision Sensor

PHA200-F200-R2



- Large capture range
- High operating range
- Integrated contrast compensation
- Compact design
- Integrated illumination
- Detects the position of an index hole


Precision positioning on hole in the 70 mm x 70 mm housing



Function

The sensor has been developed for the precision positioning of high-bay racking operating equipment. It detects circular holes in the racking structure and their positional deviation from the nominal position. The sensor operates in two dimensions.

Dimensions



Technical Data

General specifications

| | |
|----------------|-------------------------------------|
| Light source | LED |
| Light type | Integrated LED lightning (infrared) |
| Object size | Hole diameter 13 mm |
| Response delay | 100 ms |
| Read distance | 200 mm |

Release date: 2024-02-07 Date of issue: 2024-02-07 Filename: 252264_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

| | | |
|---|----------------|---|
| Depth of focus | | ± 50 mm |
| Capture range | | max. 120 mm x 100 mm |
| Nominal ratings | | |
| Camera | | |
| Type | | CMOS , Global shutter |
| Number of pixels | | 752 x 480 pixels |
| Gray scale | | 256 |
| Functional safety related parameters | | |
| MTTF _d | | 65 a |
| Mission Time (T _M) | | 10 a |
| Diagnostic Coverage (DC) | | 0 % |
| Indicators/operating means | | |
| Operation indicator | | LED green: Ready for operation |
| Function indicator | | 4 x LED yellow: +X, -X, +Y, -Y |
| Control elements | | none |
| Electrical specifications | | |
| Operating voltage | U _B | 24 V DC ± 15% , PELV |
| No-load supply current | I ₀ | max. 250 mA |
| Power consumption | P ₀ | 6 W |
| Interface | | |
| Interface type | | serial , RS 232 |
| Transfer rate | | max. 115.2 kBit/s |
| Cable length | | max. 30 m |
| Interface 1 | | |
| Interface type | | Ethernet |
| Protocol | | TCP/IP |
| Transfer rate | | 100 MBit/s |
| Cable length | | max. 30 m |
| Input | | |
| Input voltage | | to be applied externally 24 V ± 15% PELV |
| Number/Type | | Cycle stop, relative stroke |
| Input current | | 1.6 mA at 24 V |
| Switching threshold | | low: < 10 V, high: > 15 V |
| Cable length | | max. 30 m |
| Output | | |
| Switching type | | PNP , short-circuit/overload protected |
| Signal output | | +X, -X, +Y, -Y |
| Switching voltage | | 24 V |
| Switching current | | max. 100 mA each output |
| Cable length | | max. 30 m |
| Conformity | | |
| Shock resistance | | EN 60068-2-27:2009 |
| Vibration resistance | | EN 60068-2-6:2008 |
| Emitted interference | | EN 61000-6-4:2007+A1:2011 |
| Noise immunity | | EN 61326-1:2013 |
| Photobiological safety | | exempt group according to EN 62471:2008 |
| Approvals and certificates | | |
| CE conformity | | CE |
| CCC approval | | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions | | |
| Operating temperature | | 0 ... 60 °C (32 ... 140 °F) , -20 ... 60 °C (-4 ... 140 °F) (noncondensing; prevent icing on the lens!) |
| Storage temperature | | -20 ... 85 °C (-4 ... 185 °F) |

Release date: 2024-02-07 Date of issue: 2024-02-07 Filename: 252264_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Technical Data

| | |
|----------------------------------|---|
| Relative humidity | 90 % , noncondensing |
| Shock resistance | < 50 g |
| Vibration resistance | < 3 G , 11 ... 200 Hz |
| Mechanical specifications | |
| Degree of protection | IP67 |
| Connection | 8-pin, M12x1 connector, standard (supply+IO) , 5-pin, M12x1 socket, standard (RS 232) , 4-pin, M12x1 socket, standard (LAN) |
| Material | |
| Housing | PC/ABS |
| Optical face | Plastic pane |
| Installation | 4 x M6 threading |
| Mass | approx. 160 g |
| Dimensions | |
| Height | 70 mm |
| Width | 70 mm |
| Depth | 50 mm |

Connection


RS 232



| Pin | Signal |
|-----|--------|
|-----|--------|

- 1 +UB
- 2 TX RS232
- 3 GND
- 4 RX RS232
- 5 NC


LAN



| Pin | Signal |
|-----|--------|
|-----|--------|

- 1 TX+ Ethernet
- 2 RX+ Ethernet
- 3 TX- Ethernet
- 4 RX- Ethernet

24 V DC+IO





| Pin | Signal |
|-----|--------|
|-----|--------|


- 1 OUT +X
- 2 +UB
- 3 OUT -Y
- 4 OUT +Y
- 5 OUT -X
- 6 IN 1
- 7 GND
- 8 IN 2

Release date: 2024-02-07 Date of issue: 2024-02-07 Filename: 252264_eng.pdf

Assembly



Characteristic Curve



Release date: 2024-02-07 Date of issue: 2024-02-07 Filename: 252264_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com