

Background suppression sensor ML100-8-H-100-5986



- Diffuse mode sensor with multiple light spots
- Specially designed for detecting critical objects such as PCBs
- Miniature design
- Detects objects in front of a close background through precise background suppression
- Can be adapted to the application in question thanks to the adjustable detection range
- Precision object detection, almost irrespective of the color
- Not sensitive to ambient light, even with switched energy saving

Diffuse mode sensor with special light spots for detecting PCBs, background suppression, miniature design, 100 mm detection range, red light, light on, PNP output, fixed cable with M8 plug








Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Application

File not found

Dimensions




100	nnica	ata

General specifications Detection range 20 100 mm Detection range min. 10 25 mm Detection range max. 25 100 mm Adjustment range 25 100 mm Reference target standard white, 100 mm x 100 mm Light source LED Light type modulated visible red light Polarization filter no Black-white difference (6 %/90 %) < 20 %	
Detection range min. Detection range max. 25 100 mm Adjustment range 25 100 mm Reference target standard white, 100 mm x 100 mm Light source LED Light type modulated visible red light Polarization filter Black-white difference (6 %/90 %) 10 25 mm 25 100 mm modulated visible red light no 81 consideration filter 92 consideration filter 93 consideration filter 94 consideration filter 95 consideration filter 96 consideration filter 97 consideration filter 98 consideration filter 98 consideration filter 99 consideration filter 90 consideration filter	
Detection range max. Adjustment range 25 100 mm 25 100 mm Reference target standard white, 100 mm x 100 mm Light source LED Light type modulated visible red light Polarization filter Black-white difference (6 %/90 %) 25 100 mm no standard white, 100 mm x 100 mm compared to modulated visible red light no 	

Technical Data		
Control elements		Light-on/dark-on changeover switch
Electrical specifications		
Operating voltage	U_B	10 30 V DC
Ripple		max. 10 %
No-load supply current	I_0	< 15 mA
Output		
Switching type		The switching type of the sensor is adjustable. The default setting is: light-on
Signal output		1 PNP output, short-circuit protected, reverse polarity protected, open collector
Switching voltage		max. 30 V DC
Switching current		max. 100 mA, resistive load
Voltage drop	U_{d}	≤ 1.5 V DC
Switching frequency	f	500 Hz
Response time		1 ms
Conformity		
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-30 60 °C (-22 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		11 mm
Housing height		31 mm
Housing depth		20 mm
Degree of protection		IP67
Connection		400 mm fixed cable with plug with M8 connector, 3-pin
Material		
Housing		PC (Polycarbonate)
Optical face		PMMA
Mass		approx. 50 g
Tightening torque, fastening screws		0.6 Nm
Cable length		0.4 m

Connection




Connection Assignment




Wire colors in accordance with EN 60947-5-2

1 BN (brown) 3 BU (blue) 4 BK (black)

Assembly



1	Alignment Mode	
2	Light-Dark-switching	
3	Sensitivity adjuster	
4	Signal display	yellow
5	Operating display	green



Accessories

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
W. Harris	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm

Accessories			
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket	
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket	
	OMH-ML100-S2	Mounting aid for ML100 series, mounting bracket	

Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 258449_eng.pdf

Configuration Information

Setting mode (A-Mode):

A-Mode is an additional switch position that is integrated into the light ON/dark ON switch. A-Mode is located between position L and position D. A-Mode is a help mode which enables you to detect whether all three light spots are directed onto the object. If A-Mode is selected, the yellow signal indicator LED flashes; the number of times that the LED flashes equates to the number of detected light spots.

The following scenarios exist:

- · No flashing/LED off: No light spots detected
- Fast flashing (8 Hz): One light spot detected
- · Slow flashing (4 Hz): Two light spots detected
- · Static illumination/LED on: Three light spots detected

As soon as you exit A-Mode, the yellow LEDs light up in the standard manner again.