



Safety light curtain SLCS90/35



- Resolution 90 mm
- Protection field height up to 2400 mm
- Self-monitoring (type 4 according to IEC/EN 61496-1)
- SIL3 (IEC 61508)
- Sensing range up to 20 m
- Degree of protection IP67
- Temperature range -35 ... 60°C (-31 ... 140 °F)
- Slim design, mounting on three sides

Safety light curtain




Function

The safety light curtain consists of a transmitter and a receiver unit. The protected area is formed by infrared light beams transmitted from the transmitter unit to the receiver unit. The spacing between the individual light beams determines the minimum obstruction size (90 mm) that can be reliably detected within the entire protected area range.

Application

- Active opto-electronic protective device (AOPD) for protection of people in danger zones and high risk areas
- Hand protection from 30 mm resolution
- Finger protection from 14 mm resolution

Dimensions



Technical Data

General specifications	
Effective detection range	5 ... 20 m
Light source	IREC
Light type	modulated infrared light , 850 nm
Protection field height	see Table 1, max. 2400 mm
Operating mode	Startup/restart disable, deactivateable
Optical resolution	90 mm
Opening angle	< 5 °
Ambient light limit	Not sensitive to ambient light in accordance with IEC 61496-2
UL File Number	E215245
Functional safety related parameters	
Safety Integrity Level (SIL)	SIL 3
Performance level (PL)	PL e
Category	Cat. 4
Mission Time (T _M)	20 a
PFH _d	Depending on the protection field height; see Manual
Type	4
Indicators/operating means	
Operation indicator	green: Power on
Function indicator	Green: OSSD ON , Red: OSSD OFF
Status indicator	Transmitter unit: LED yellow: Mode, test or error Receiver: LED yellow: Start readiness, function reserve or error
Electrical specifications	
Operating voltage	U _B 24 V DC (-20%, +30%) ; Power supply with safe isolation: 24 V DC

Release date: 2023-02-14 Date of issue: 2023-02-14 Filename: 265790_eng.pdf

Technical Data

No-load supply current	I_0	Transmitter unit: ≤ 150 mA Receiver: ≤ 150 mA (without outputs)
Protection class		III, IEC 61140
Power consumption	P_0	Transmitter unit: 5 W Receiver: 15 W
Input 1		
Input type		Transmitter unit test
Input format		Break contact
Switching voltage		24 V DC
Input current		5 mA
Input 2		
Input type		Transmitter unit, mode A/B
Function		Beam Code A: open or 0 V Beam Code B: 24 V DC, 5 mA
Input 3		
Input type		Receiver unit relay monitor
Input format		Break contact
Switching voltage		24 V DC
Input current		5 mA
Input 4		
Input type		Receiver unit, start release
Input format		Break contact
Input current		5 mA
Input 5		
Input type		Receiver unit, mode A/B (see transmitter unit, mode A/B)
Output		
Response time		see Table 1, max. 17 ms
Output 1		
Output type		Receiver unit OSSD
Signal output		PNP semiconductor, monitored for short and cross circuits
Switching voltage		ON: $U_B - 2 V$; OFF: $< 1 V$
Switching current		ON: max. 0.1 A; OFF: $< 5 \mu A$
Output 2		
Output type		Receiver signal output start readiness
Signal output		PNP-semiconductor, short-circuit protected, 0.1 A
Conformity		
Functional safety		ISO 13849-1; EN 61508 part1-4
Product standard		EN 61496-1; IEC 61496-2
Photobiological safety		Risk group 0 according to IEC 62471
Approvals and certificates		
CE conformity		CE
UKCA conformity		UKCA
UL approval		cULus Listed
TÜV approval		TÜV SÜD
Ambient conditions		
Ambient temperature		-35 ... 60 °C (-31 ... 140 °F)
Storage temperature		-35 ... 70 °C (-31 ... 158 °F)
Relative humidity		max. 95 %, not condensing
Shock resistance		10 g, 16 ms; stationary applications only
Vibration resistance		0.35 mm, 10 ... 55 Hz; stationary applications only
Mechanical specifications		
Housing length L		see table 2
Degree of protection		IP67, For indoor use only


Release date: 2023-02-14 Date of issue: 2023-02-14 Filename: 265790_eng.pdf

Technical Data

Connection	Transmitter unit: 4-pin, M12 x 1 connector Receiver: 8-pin, M12 x 1 connector Cable cross section min. 0.25 mm ² Max. cable length 50 m
Material	
Housing	extruded aluminum section , gold anodized
Optical face	Plastic pane , Transparent polycarbonate
Mass	see table 2
General information	
Supplementary information	EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com .


Connection

Transmitter unit:



Pin	Transmitter unit
1	24 V DC
2	Mode A/B
3	0 V DC
4	Test


Receiver unit:




Pin	Receiver unit
1	Restart Interlock (RI)
2	24 V DC
3	Relay Monitor (RM)
4	Status / Select RI-RM
5	OSSD1
6	OSSD2
7	0 V DC
8	Mode A/B

Assembly

Transmitter unit




Receiver unit



1	Power	green
2	Mode A/B, Status	yellow
3	OSSD OFF	red
4	OSSD ON	green
5	Restart/Status	yellow
6	Mode A/B	yellow

Application



Technical Features

Table 1: Response Time

Protection field height [mm]	Response time [ms]
300	8
600	10
900	11
1200	12
1500	14
1800	15
2100	16
2400	17

Table 2: Total Length and Weight

Protection field height [mm]	Total length of transmitter/receiver unit [mm]	Weight of transmitter/receiver unit [g]
300	419	250
600	719	430
900	1019	600
1200	1319	760
1500	1625	940
1800	1925	1100
2100	2225	1270
2400	2525	1440

Type Code

S	L	C	(1)	(2)	(2)	-	(3)	(3)	(3)	(3)	-	(4)	/	(5)	(5)
----------	----------	----------	-----	-----	-----	---	-----	-----	-----	-----	---	-----	---	-----	-----

SLC	Device
SLC	Safety light curtain

(1)	Safety light curtain type
S	Self-monitoring, type 4
T	Testing, type 2

(2)	Resolution
14	14 mm
30	30 mm
60	60 mm
90	90 mm

(3)	Protection field height
100	100 mm
200	110 mm
300	300 mm
...	...
2400	2400 mm

















Release date: 2023-02-14 Date of issue: 2023-02-14 Filename: 265790_eng.pdf

Type Code

(4) Principle	
T	Transmitter
R	Receiver










(5) Option	
35	Extended detection range

Accessories

	TR 14/30/50/60	Test rod for safety light curtain SLCT
	AA SLCT-01	Profile alignment aid; simplified alignment of the SLCS and SLCT safety light curtains
	OMH-SLCT-100-1200	Mounting base for floor mounting and cover plate
	OMH-SLCT-100-1500	Mounting base for floor mounting and cover plate
	OMH-SLCT-100-2100	Mounting base for floor mounting and cover plate
	OMH-SLCT-100-2500	Mounting base for floor mounting and cover plate
	OMH-SLCT-110-1200	Mounting base for floor mounting with rear panel and cover plate
	OMH-SLCT-110-1500	Mounting base for floor mounting with rear panel and cover plate
	OMH-SLCT-110-2100	Mounting base for floor mounting with rear panel and cover plate
	OMH-SLCT-120-1200	Side protection for mounting base
	OMH-SLCT-120-1500	Side protection for mounting base
	OMH-SLCT-120-2100	Side protection for mounting base
	OMH-SLCT-120-2500	Side protection for mounting base
	OMH-SLCT-200	Floor mount
	SLCT-M-01-1200	Inclined mirror for stable 90° deflection with cover plate
	SLCT-M-01-1500	Inclined mirror for stable 90° deflection with cover plate
	SLCT-M-01-2100	Inclined mirror for stable 90° deflection with cover plate

Release date: 2023-02-14 Date of issue: 2023-02-14 Filename: 265790_eng.pdf

Accessories

	OMH-SLCT-10	Clamp mounting suitable for 6 mm ... 11.5 mm groove
	OMH-SLCT-11	Reverse clamp mounting suitable for 8.5 mm ... 10.5 mm groove
	OMH-SLCT-12-500	Mounting bracket, muting arm with round rod d=12 mm
	OMH-SLCT-01	Quick clamp and adjustment system
	OMH-SLCT-02	Attachment aid for OMH-SLCT-01
	OMH-SLCT-03	Mounting bracket including adjustment
	OMH-SLCT-04	Mounting bracket including adjustment (with loose bearing)
	OMH-SLCT-05	Mounting bracket including adjustment
	OMH-SLCT-06	Swivel Bracket

Release date: 2023-02-14 Date of issue: 2023-02-14 Filename: 265790_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com