

# Diffuse mode sensor OBD1000-R101-EP-IO-0,3M-V3



- Miniature design with versatile mounting options
- Extended temperature range -40 °C ... 60 °C
- High degree of protection IP69K
- IO-Link interface for service and process data

Diffuse mode sensor












#### **Function**

The miniature optical sensors are the first devices of their kind to offer an end-to- end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation


The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

### **Dimensions**



Release date: 2023-10-23 Date of issue: 2023-10-23 Filename: 267075-100047\_eng.pdf





Technical Data

#### **General specifications** 2 ... 1000 mm Detection range Detection range min. 20 ... 50 mm Adjustment range 50 ... 1000 mm Reference target standard white, 100 mm x 100 mm LED Light source Light type modulated visible red light LED risk group labelling exempt group Diameter of the light spot approx. 65 mm at a distance of 1000 mm 3.7° Opening angle Ambient light limit EN 60947-5-2 Functional safety related parameters 724 a $\mathsf{MTTF}_\mathsf{d}$ Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Operation indicator Function indicator constantly on - object detected constantly off - object not detected Control elements Light-on/dark-on changeover switch Control elements Sensing range adjuster **Electrical specifications** $U_{B}$ 10 ... 30 V DC Operating voltage Ripple max. 10 % No-load supply current $I_0$ < 25 mA at 24 V supply voltage Protection class Ш Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision 1.1 Device ID 0x110101 (1114369) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms

Process data width		Process data input 1 Bit Process data output 2 Bit
SIO mode support		yes
Compatible master port type		A
Output		
Switching type		The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / light-on, PNP normally closed / dark-on, IO-Link
Signal output		1 push-pull (4 in 1) output, short-circuit protected, reverse polarity protected, overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA, resistive load
Usage category		DC-12 and DC-13
Voltage drop	$U_{d}$	≤ 1.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Communication interface		IEC 61131-9
Product standard		EN 60947-5-2
Approvals and certificates		


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

UL approval

E87056, cULus Listed, class 2 power supply, type rating 1

Ambient conditions	
Ambient temperature	-40 60 °C (-40 140 °F) , fixed cable -25 60 °C (-13 140 °F) , movable cable not appropriate for conveyor chains
Storage temperature	-40 70 °C (-40 158 °F)
Mechanical specifications	
Housing width	13.9 mm
Housing height	33.8 mm
Housing depth	18.3 mm
Degree of protection	IP67 / IP69 / IP69K
Connection	300 mm fixed cable with M8 x 1, 3-pin connector
Material	
Housing	PC (Polycarbonate)
Optical face	PMMA
Mass	approx. 10 g
Cable length	0.3 m

### Connection



## **Connection Assignment**





Wire colors in accordance with EN 60947-5-2

1 | BN (brown) 3 | BU (blue) 4 | BK (black)


- 1 Light-on/dark-on changeover switch
- 2 Sensitivity adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- 5 Operating indicator / light on

### **Characteristic Curve**






### Characteristic Curve



### Configuration



- 1 Light on / dark on changeover switch
- 2 Sensing range / sensitivity adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- 5 Operating indicator / light on

To unlock the adjustment functions turn the sensing range adjuster for more than 180 degrees.

### Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.

Turn sensing range /sensitivity adjuster counterclockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

#### Light on / Dark on Configuration

Press the light on / dark on changeover switch for more than 1 second (less than 4 seconds). The light on / dark on mode changes and the operating indicators are activated accordingly.

If you press the light on / dark on changeover switch for more than 4 seconds, the light on / dark on mode changes back to the original setting. On release of the light on / dark on changeover switch the current state is activated.

#### **Restore Factory Settings**

Press the light on / dark on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light on / dark on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range / sensitivity adjuster for more than 180 degrees.