

AS-Interface Safety Monitor VAS/M-2A8L-KE4-8SE-C1

- Compact safety controller up to SIL 3/PLe
- 4 integrated, safe inputs
- 2 integrated, safe outputs (OSSDs)
- 8 logical, safe output groups (switchable)
- Increased functionality through integrated expansion port
- Parameterizable muting, timer and logic functions using SIMON+ software
- Integrated data decoupling

Safety Monitor, 8 decentralized output circuits







Function

The AS-Interface safety monitor compact with master function VAS/M-2A8L-KE4-8SE-C1 is a control cabinet module with up to 8/4 local safe inputs and up to 8 independent outputs and disconnectable master.


The safe inputs can optionally be configured as standard inputs and signalling outputs. Two of the safe inputs are also suitable as inputs for OSSDs, the others only for potential-free contacts. Each safe input can also be configured as two standard inputs. 8 independent AS-Interface release circuits support multiple safe AS-Interface outputs on a single address. In addition, the test pulse outputs can be switched as diagnostic outputs (not control-safe). The safe circuit for the connected consumers is created using two safety relays.

The housing, which is only 22.5 mm wide, requires little space in the switch cabinet. The module is mounted by clicking it onto the 35 mm mouting

rail, compliant with EN 50022


The AS-Interface and external power supply are each connected by means of a 2-station terminal block. Connection of the inputs and outputs is by means of multiple 4-station terminal blocks. This permits the simple removal of the supply during commissioning or servicing. The supply to the connected slaves is fed either internally via the module from the AS-interface or via an external supply. For external supply via a standard power supply unit, the safety module has a decoupling function. The current status of the inputs and outputs is indicated via yellow LEDs. Communication faults are indicated via red LEDs. The display of the operating voltage and the address 0 is provided by a green LED. A Micro-USB interface is used for configuration with the AS-i-Control Tools via ASIMON. The configuration can be transferred to a replacement device using a chip card.

Dimensions



Technical Data

General specifications		
AS-Interface specification	V3.0	
Data decoupling	integrated	
UL File Number	E223772	
Functional safety related parameters		



bdf
eng.
1770
: 26
-ilename
-09-27 F
: 2021
fissue
Date o
-09-27
2021
date
Release


Fechnical Data		
Safety Integrity Level (SIL)		SIL 3
Performance level (PL)		PL e
Mission Time (T _M)		20 a
PFH_d		5.08 E-9
ndicators/operating means		
LED AS-i M		Status of AS interface master, multicolored LED green: Master OK
LED SM		Status of safety monitor, multicolored LED green: Safety monitor OK
LED S1 S8		Status of inputs S1 S8, yellow LED yellow: Contact open
LED 01, 02		Status of outlputs, multicolored LED yellow: Output on
electrical specifications		
Auxiliary voltage (input)	U_{EXT}	20 30 V _{DC} PELV
Insulation voltage	Ui	500 V AS-Interface/U _{AUX} :
Rated operating voltage	U _e	18,0 31.6 V from AS-Interface
Rated operating current	l _e	≤ 200 mA from AS-Interface; ≤ 4 A from AUX
nterface 1		
Interface type		Chip card slot
nterface 2		
Interface type		Micro USB Programming interface
nput		
Number/Type		8 / 4 safe inputs cat. 4 or 8 standard inputs and outputs
Supply		24 V U _{AUX}
Current loading capacity		10 mA per signal output 1.4 A OSSD supply output
Input current		Static switching current 4 mA at 24 V, dynamic 30 mA at 24 V (T=100 µs)
Output		
Number/Type		Output circuits 1 and 2 max. contact rating: 700 m A _{DC-13} at 24 V
Supply		24 V U _{AUX}
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU		EN 62026-2:2013 EN 61000-6-2:2005/AC:2005 EN 61000-6-4:2007/A1:2011
Machinery Directive		
Directive 2006/42/EC		EN 13849-1:2008/AC:2009 EN 62061:2005
Standard conformity		
Electromagnetic compatibility		EN 50295:1999 EN 61000-6-2:2005/AC:2005 EN 61000-6-4:2007/A1:2011
Degree of protection		EN 60529:2000
Electrical safety		IEC 61508:2010 and EN 62061:2005 (up to SIL3) EN 13849-1:2008/AC:2009 EN 61326-3-1:2008
AS-Interface		EN 62026-2:2013
Programming instructions		
Profile		S-0.B.E
IO code		0
ID code		В
ID1 code		F
Ambient conditions		
and chi conditions		

5PEPPERL+FUCHS

Technical Data


Mechanical specifications	
Degree of protection	IP20
Connection	removable terminals rated connection capacity: rigid/flexible (with and without wire-end ferrules): 0.25 mm ² 2.5 mm ² for multiple-wire connection with two wires of equal cross-section: flexible with twin wire-end ferrules: 0.5 mm ² 1.5 mm ²
Material	
Housing	PA 66-FR
Mounting	DIN mounting rail

Assembly



SET = Service button CHIP CARD = Chip card

Connection



Accessories VAZ-SW-SIMON+ Software for configuration of K30 Master Monitors/K31 and KE4 Safety Monitors **VAZ-SIMON-USB** USB Type A to Micro-USB connector