



# Triangulation sensor (SbR) OQT150-R101-2EP-IO-V31



- Miniature design with versatile mounting options
- Multi Pixel Technology (MPT) flexibility and adaptability
- Reduction of device variety several switch points within one
- Reliable detection of all surfaces, independent of color and structure
- Low sensitivity to target color
- IO-Link interface for service and process data

Switching diffuse mode sensor with measurement core technology, 150 mm detection range, red light, IO-Link, 2 x push-pull output, M8 plug












### **Function**


The miniature optical sensors are the first devices of their kind to offer an end-to- end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

#### **Dimensions**






Technical Data

#### **General specifications** 5 ... 150 mm Detection range Detection range min. 5 ... 20 mm Detection range max. 5 ... 150 mm Adjustment range 20 ... 150 mm standard white, 100 mm x 100 mm Reference target Light source modulated visible red light Light type LED risk group labelling exempt group Black-white difference (6 %/90 %) < 5 % at 150 mm Diameter of the light spot approx. 10 mm at a distance of 150 mm Opening angle approx. 4° EN 60947-5-2: 30000 Lux Ambient light limit Functional safety related parameters $\mathsf{MTTF}_\mathsf{d}$ 600 a Mission Time (T<sub>M</sub>) 20 a 0 % Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator LED vellow: constantly on - switch output active constantly off - switch output inactive Control elements Teach-In key 5-step rotary switch for operating modes selection Control elements **Electrical specifications** Operating voltage $\mathsf{U}_\mathsf{B}$ 10 ... 30 V DC Ripple max. 10 % No-load supply current < 25 mA at 24 V supply voltage $I_0$ Protection class Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision Device profile **Smart Sensor** Device ID 0x110801 (1116161) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms Process data width Process data input 2 Bit Process data output 2 Bit SIO mode support yes Compatible master port type Α Output The default setting is: C/Q - Pin4: NPN normally open, PNP normally closed, IO-Link Q2 - Pin2: NPN normally-open, PNP normally-closed Switching type Signal output 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load DC-12 and DC-13 Usage category Voltage drop ≤ 1.5 V DC $U_d$ Switching frequency f 217 Hz Response time 2.3 ms Conformity

Technical Data		
Communication interface	IEC 61131-9	
Product standard	EN 60947-5-2	
Approvals and certificates		
UL approval	E87056, cULus Listed, class 2 power supply, type rating 1	
Ambient conditions		
Ambient temperature	-40 60 °C (-40 140 °F)	
Storage temperature	-40 70 °C (-40 158 °F)	
Mechanical specifications		
Housing width	13.9 mm	
Housing height	41.4 mm	
Housing depth	18.3 mm	
Degree of protection	IP67 / IP69 / IP69K	
Connection	M8 x 1 connector, 4-pin	
Material		
Housing	PC (Polycarbonate)	
Optical face	PMMA	
Mass	approx. 10 g	

### Connection




# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)


### **Assembly**



- TEACH-IN button
- 2 Mode rotary switch
- 3 Switch output indicator Q2
- 4 Switch output indicator Q1
- 5 Operating indicator
- Switch output 1 / switch point B
- Switch output 1 / switch point A
- Switch output 2 / switch point A
- IV Switch output 2 / B
- Keylock

# **Characteristic Curve**





#### **Accessories**



OMH-R101

Mounting Clamp

# **Accessories** OMH-R101-Front Mounting Clamp OMH-4.1 Mounting Clamp OMH-ML6 Mounting bracket OMH-ML6-U Mounting bracket OMH-ML6-Z Mounting bracket ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection V31-GM-2M-PUR Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey V31-WM-2M-PUR Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey

The yellow LEDs indicate the current state of the selected output. To store a threshold value, press and hold the "TI" button until the yellow and green LEDs flash in phase (approx. 1 s). Teach-In starts when the "TI" button is released.


Successful Teach-In is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

An unsuccessful Teach-In is indicated by rapidly alternating flashing (8 Hz) of the yellow and green LEDs.


After an unsuccessful Teach-In, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Different switching modes can be defined by teaching in the relevant distance measured values for the switching thresholds A and B:

Single point mode:



Window mode:



Every taught-in switching threshold can be retaught (overwritten) by pressing the "TI" button again.

Pressing and holding the "TI" button for > 4 s completely deletes the taught-in value. The yellow and green LEDs go out simultaneously to indicate that this procedure has been completed. Successful resetting is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

### **Resetting to Factory Default Settings**

Press the "TI" button for > 10 s in rotary switch position ,O' to reset to factory default settings. The yellow and green LEDs go out simultaneously to indicate the resetting.

Resetting process starts when the "TI" button is released and is indicated by the yellow LED. After the process the sensor works with factory default settings, immediately.

OMT:

- Factory default settings switch signal Q1: Switch signal active, window mode
- Factory default settings switch signal Q2: Switch signal active, window mode

OQT:

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 267075-100162\_eng.pdf

- Factory default settings switch signal Q1: Switch signal active, BGS mode (background suppression)
- Factory default settings switch signal Q2: Switch signal active, BGS mode (background suppression)

### Configuration

### Configuring different operating modes via the IO-Link interface

The devices are equipped with an IO-Link interface as standard for diagnostics and parameterization tasks to ensure optimum adjustment of the sensors to the relevant application. Four different operating modes can be set, among other features:

#### Background suppression operating mode (one switch point):

• Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.



#### Background evaluation operating mode (one switch point):

• Detection of objects irrespective of type and color against a defined background. Reliable detection of objects at close range

### Triangulation sensor (SbR)

(detection range >= 0 mm). The background serves as reference.

active detection range

Background evaluation

#### Single point mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.
- The switch point corresponds exactly to the set point.




#### Window mode operating mode (two switch points):

- Detection of objects irrespective of type and color in a defined detection range. Reliable detection when object leaves the
  detection range.
- · Window mode with two switch points.




#### Center window mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Sets a defined window around a given object. Objects outside this window are not detected.
- Window mode with one switch point.



#### Two point mode operating mode (hysteresis operating mode):

Detection of objects irrespective of type and color between a defined switch-on and switch-off point.



#### Inactive operating mode:

• Evaluation of switching signals is deactivated.

The associated IODD device description file can be found in the download area at www.pepperl-fuchs.com.