



Distance sensor OMT200-R101-2EP-IO-0,3M-V31



- Miniature design with versatile mounting options
- Space-saving distance sensors in small standardized design
- Multi Pixel Technology (MPT) exact and precise signal
- IO-Link interface for service and process data

Measurement to object, 200 mm detection range, red light, measured value via IO-Link, 2 x push-pull output, fixed cable with M8 plug










Function

The miniature optical sensors are the first devices of their kind to offer an end-to- end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

Dimensions




Technical Data

General specifications	
Measurement range	60 200 mm
Reference target	standard white, 100 mm x 100 mm
Light source	LED
Light type	modulated visible red light
LED risk group labelling	exempt group
Angle deviation	max. +/- 1.5 °
Diameter of the light spot	approx. 12 mm at a distance of 200 mm
Opening angle	4 °
Ambient light limit	EN 60947-5-2 : 30000 Lux
Resolution	0.1 mm
Functional safety related parameters	
MTTF _d	600 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %
Indicators/operating means	
Operation indicator	LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode
Function indicator	LED yellow: constantly on - switch output active constantly off - switch output inactive
Control elements	Teach-In key

Technical Data Control elements 5-step rotary switch for operating modes selection **Electrical specifications** Operating voltage U_{B} 10 ... 30 V DC Ripple max. 10 % No-load supply current I_0 < 25 mA at 24 V supply voltage Protection class Ш Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision 1.1 Device profile **Smart Sensor** Device ID 0x110905 (1116421) Transfer rate COM2 (38.4 kBit/s) Min. cycle time Process data width Process data input 3 Byte Process data output 2 Bit SIO mode support Compatible master port type Α Output Switching type The default setting is: C/Q - Pin4: NPN normally open, PNP normally closed, IO-Link Q2 - Pin2: NPN normally-open, PNP normally-closed 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, Signal output overvoltage protected Switching voltage max, 30 V DC Switching current max. 100 mA, resistive load DC-12 and DC-13 Usage category Voltage drop U_{d} ≤ 1.5 V DC Response time 2 ms Conformity IEC 61131-9 Communication interface Product standard EN 60947-5-2 Measurement accuracy 0.05 %/K Temperature drift Warm up time 5 min Repeat accuracy ≤1% Linearity error ±1% Approvals and certificates **UL** approval E87056, cULus Listed, class 2 power supply, type rating 1 **Ambient conditions** 10 ... 60 °C (50 ... 140 °F) Ambient temperature -40 ... 70 °C (-40 ... 158 °F) Storage temperature Mechanical specifications Housing width 13.9 mm 41.4 mm Housing height Housing depth 18.3 mm Degree of protection IP67 / IP69 / IP69K Connection fixed cable 300 mm with M8 x 1 male connector; 4-pin Material Housing PC (Polycarbonate) Optical face **PMMA** approx. 17 g Mass 0.3 m Cable length

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2

ΒN (brown) 2 WH (white) BU (blue) BK (black)

Assembly



- TEACH-IN button 2 Mode rotary switch 3 Switch output indicator Q2 4 Switch output indicator Q1 5 Operating indicator
- Switch output 1 / switch point B Switch output 1 / switch point A Ш Switch output 2 / switch point A IV Switch output 2 / B Keylock

Accessories

11-	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs
11-	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs
	ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs

Accessories

ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection V31-GM-2M-PUR Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey V31-WM-2M-PUR Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey

www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

reach in

You can use the rotary switch to select the relevant switching threshold A and/or B for teaching in for switch signal Q1 or Q2. The yellow LEDs indicate the current state of the selected output.

To store a threshold value, press and hold the "TI" button until the yellow and green LEDs flash in phase (approx. 1 s). Teach-In starts when the "TI" button is released.


Successful Teach-In is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

An unsuccessful Teach-In is indicated by rapidly alternating flashing (8 Hz) of the yellow and green LEDs.


After an unsuccessful Teach-In, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Different switching modes can be defined by teaching in the relevant distance measured values for the switching thresholds A and B:

Single point mode:



Window mode:



Every taught-in switching threshold can be retaught (overwritten) by pressing the "TI" button again.

Pressing and holding the "TI" button for > 4 s completely deletes the taught-in value. The yellow and green LEDs go out simultaneously to indicate that this procedure has been completed. Successful resetting is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

Resetting to Factory Default Settings

Press the "TI" button for > 10 s in rotary switch position ,O' to reset to factory default settings. The yellow and green LEDs go out simultaneously to indicate the resetting.

Resetting process starts when the "TI" button is released and is indicated by the yellow LED. After the process the sensor works with factory default settings, immediately.

OMT:

- Factory default settings switch signal Q1: Switch signal active, window mode
- Factory default settings switch signal Q2: Switch signal active, window mode

OQT:

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 267075-100208_eng.pdf

- Factory default settings switch signal Q1: Switch signal active, BGS mode (background suppression)
- Factory default settings switch signal Q2: Switch signal active, BGS mode (background suppression)

Configuration

Setting different operating modes via the IO-Link interface

The devices are equipped with an IO-Link interface as standard for diagnostics and parameterization tasks to ensure optimum adjustment of the sensors to the relevant application.

Single point mode operating mode (one switch point):

- "Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.
- "The switch point corresponds exactly to the set point.

active detection range

Background suppression

Refer to "General Notes Relating to Pepperl+Fuchs Product Information

Distance sensor


Window mode operating mode (two switch points):

- Detection of objects irrespective of type and color in a defined detection range. Reliable detection when object leaves the
 detection range.
- · Window mode with two switch points.




Center window mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Sets a defined window around a given object.
 Objects outside this window are not detected.
- · Window mode with one switch point.



Two point mode operating mode (hysteresis operating mode):

Detection of objects irrespective of type and color between a defined switch-on and switch-off point.



Inactive operating mode:

Evaluation of switching signals is deactivated.

The associated IODD device description file can be found in the download area at www.pepperl-fuchs.com.