

# Triangulation sensor (BGE) OBT350-R101-2EP-IO-1T



- Miniature design with versatile mounting options
- Secure and gapless detection, even near the surface through background evaluation
- Precision object detection, almost irrespective of the color
- Extended temperature range -40 °C ... 60 °Ċ
- High degree of protection IP69K
- IO-Link interface for service and process data

Triangulation sensor with background evaluation












### **Function**


The miniature optical sensors are the first devices of their kind to offer an end-to- end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.


The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

### **Dimensions**





20.5 18.3 6.4



**Emitter** 


Technical Data

#### **General specifications** 5 ... 350 mm **Detection range** Detection range min. 5 ... 25 mm Detection range max. 5 ... 350 mm Adjustment range 25 ... 350 mm standard white, 100 mm x 100 mm Reference target Light source modulated visible red light Light type LED risk group labelling exempt group Black-white difference (6 %/90 %) < 15 % at 350 mm Diameter of the light spot approx. 20 mm at a distance of 350 mm Opening angle approx. 3° Ambient light limit EN 60947-5-2: 40000 Lux Functional safety related parameters $\mathsf{MTTF}_\mathsf{d}$ 600 a Mission Time (T<sub>M</sub>) 20 a 0 % Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator LED vellow: constantly on - background detected (object not detected) constantly off - object detected Control elements Light-on/dark-on changeover switch Control elements Sensing range adjuster **Electrical specifications** Operating voltage $\mathsf{U}_\mathsf{B}$ 10 ... 30 V DC Ripple max. 10 % No-load supply current < 25 mA at 24 V supply voltage $I_0$ Protection class Interface Interface type IO-Link (via C/Q = BK) IO-Link revision Device profile **Smart Sensor** Device ID 0x110701 (1115905) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms Process data width Process data input 1 Bit Process data output 2 Bit SIO mode support yes Compatible master port type Α Output The switching type of the sensor is adjustable. The default setting is: C/Q - BK: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link /Q - WH: NPN normally closed / light-on, PNP normally open / dark-on Switching type Signal output 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load DC-12 and DC-13 Usage category Voltage drop ≤ 1.5 V DC $U_d$ 500 Hz Switching frequency f Response time 1 ms


Conformity

| Technical Data             |   |
|----------------------------|---|
|                            |   |
| Communication interface    | IEC 61131-9   |
| Product standard           | EN 60947-5-2  |
| Approvals and certificates |   |
| UL approval                | E87056, cULus Listed, class 2 power supply, type rating 1   |
| Ambient conditions         |   |
| Ambient temperature        | -40 60 °C (-40 140 °F) , fixed cable -25 60 °C (-13 140 °F) , movable cable not appropriate for conveyor chains |
| Storage temperature        | -40 70 °C (-40 158 °F)  |
| Mechanical specifications  |   |
| Housing width              | 13.9 mm   |
| Housing height             | 33.8 mm   |
| Housing depth              | 18.3 mm   |
| Degree of protection       | IP67 / IP69 / IP69K   |
| Connection                 | 2 m fixed cable   |
| Material                   |   |
| Housing                    | PC (Polycarbonate)  |
| Optical face               | PMMA  |
| Mass                       | approx. 36 g  |
| Cable length               | 2 m   |

### Connection




### **Assembly**



- Light-on/dark-on changeover switch
- 2 Sensing range adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- Operating indicator / light on

## Triangulation sensor (BGE)



### **Accessories**

| He .   | ICE2-8IOL-G65L-V1D   | EtherNet/IP IO-Link master with 8 inputs/outputs   |
|--|----------------------|--|
| II.  | ICE3-8IOL-G65L-V1D   | PROFINET IO IO-Link master with 8 inputs/outputs   |
| 110  | ICE1-8IOL-G30L-V1D   | Ethernet IO-Link module with 8 inputs/outputs  |
| 0 0<br>0 0<br>0 0<br>0 0<br>0 0<br>0 0<br>0 0<br>0 0<br>0 0<br>0 0 | ICE1-8IOL-G60L-V1D   | Ethernet IO-Link module with 8 inputs/outputs  |
|  | ICE2-8IOL-K45P-RJ45  | EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors                               |
| 8  | ICE2-8IOL-K45S-RJ45  | EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal                                   |
|  | ICE3-8IOL-K45P-RJ45  | PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals                                |
| 8  | ICE3-8IOL-K45S-RJ45  | PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal                                   |
| 1  | IO-Link-Master02-USB | IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection |

- 1 Light on / dark on changeover switch
- 2 Sensing range / sensitivity adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- 5 Operating indicator / light on

To unlock the adjustment functions turn the sensing range adjuster for more than 180 degrees.

### Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.

Turn sensing range /sensitivity adjuster counterclockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

#### Light on / Dark on Configuration

Press the light on / dark on changeover switch for more than 1 second (less than 4 seconds). The light on / dark on mode changes and the operating indicators are activated accordingly.

If you press the light on / dark on changeover switch for more than 4 seconds, the light on / dark on mode changes back to the original setting. On release of the light on / dark on changeover switch the current state is activated.

#### **Restore Factory Settings**

Press the light on / dark on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light on / dark on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range / sensitivity adjuster for more than 180 degrees.