

Diffuse mode sensor OBD800-R103-2EP-IO-V31



- Miniature design with versatile mounting options
- Extended temperature range -40 °C ... 60 °C
- High degree of protection IP69K
- IO-Link interface for service and process data

Diffuse mode sensor

Function


The R103 series miniature optical sensors are the first devices of their kind to offer an endto- end solution in a small single standard design from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.


The entire series enables sensors to communicate via IO-Link. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.


The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.



Dimensions










ø 3.3 x 2



15



Technical Data

General specifications			
Detection range	2 800 mm		
Detection range min.	20 40 mm		
Adjustment range	40 800 mm		
Reference target	standard white, 100 mm x 100 mm		
Light source	LED		
Light type	modulated visible red light		
LED risk group labelling	exempt group		
Diameter of the light spot	approx. 55 mm at a distance of 800 mm		
Opening angle	3.7 °		
Ambient light limit	EN 60947-5-2		
Functional safety related parameters			
MTTF _d	724 a		
Mission Time (T _M)	20 a		
Diagnostic Coverage (DC)	0 %		
Indicators/operating means			
Operation indicator	LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode		
Function indicator	LED yellow: constantly on - object detected constantly off - object not detected		
Control elements	Light-on/dark-on changeover switch		


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Technical Data

Control elements		sensitivity adjustment	
Electrical specifications			
Operating voltage	U _B	10 30 V DC	
Ripple		max. 10 %	
No-load supply current	I ₀	< 25 mA at 24 V supply voltage	
Protection class			
nterface			
Interface type		IO-Link (via C = pin 4)	
IO-Link revision		1.1	
Device ID		0x110103 (1114371)	
Transfer rate		COM2 (38.4 kBit/s)	
Min. cycle time		2.3 ms	
Process data width		Process data input 1 Bit Process data output 2 Bit	
SIO mode support		yes	
Compatible master port type		A	
Dutput			
Switching type		The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / light-on, PNP normally closed / dark-on, IO-Link /Q - Pin2: NPN normally closed / dark-on, PNP normally open / light-on	
Signal output		2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA , resistive load	
Usage category		DC-12 and DC-13	
Voltage drop	U _d	≤ 1.5 V DC	
Switching frequency	f	1000 Hz	
Response time		0.5 ms	
Conformity			
Communication interface		IEC 61131-9	
Product standard		EN 60947-5-2	
Approvals and certificates			
UL approval		E87056 , cULus Listed , class 2 power supply , type rating 1	
Ambient conditions			
Ambient temperature		-40 60 °C (-40 140 °F)	
Storage temperature		-40 70 °C (-40 158 °F)	
Mechanical specifications			
Housing width		15 mm	
Housing height		43.9 mm	
Housing depth		26.7 mm	
Degree of protection		IP67 / IP69 / IP69K	
Connection		M8 x 1 connector, 4-pin	
Material			
Housing		PC (Polycarbonate)	
Optical face		РММА	
Mass		approx. 12 g	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3




Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Assembly



1	Light-on/dark-on changeover switch
2	Sensitivity adjuster
3	Operating indicator / dark on
4	Function indicator


5 Operating indicator / light on

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

4


Characteristic Curve



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2023-10-23 Date of issue: 2023-10-23 Filename: 267075-100257_eng.pdf

Configuration



- 1 Light-on / dark-on changeover switch
- 2 Sensing range / sensitivity adjuster
- 3 Operating indicator / dark on
- 4 Signal indicator
- 5 Operating indicator / light on

To unlock the adjustment functions turn the sensing range adjuster / sensitivity adjuster for more than 180 degrees. Sensing Range/ Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.

Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.

If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on /dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

Restore Factory Settings

Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjuster for more than 180 degrees.

6