

# Distance sensor OMT150-R101-EP-IO-V3-L



- Miniature design with versatile mounting options
- Space-saving distance sensors in small standardized design
- Multi Pixel Technology (MPT) exact and precise signal evaluation
- DuraBeam Laser Sensors durable and employable like an LED
- IO-Link interface for service and process data

Measurement to object, 150 mm detection range, red laser light, laser class 1, measured value via IO-Link, push-pull output, M8 plug


CE 🖑 KA 🔬 🏵 IO-Link

#### **Function**

The miniature optical sensors are the first devices of their kind to offer an end-to- end solution in a small single standard design — from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor. The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.

## Dimensions



Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 267075-100222\_eng.pdf

41.4


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com




## **Technical Data**

General specifications			
Measurement range		60 150 mm	
Reference target		standard white, 100 mm x 100 mm	
Light source		laser diode	
Light type		modulated visible red light	
Laser nominal ratings		J. J	
Note		LASER LIGHT , DO NOT STARE INTO BEAM	
Laser class		1	
Wave length		680 nm	
Beam divergence		> 5 mrad d63 d63 < 1 mm in the range of 50 mm 250 mm	
Pulse length			
Repetition rate	approx. 3 kHz		
max. pulse energy		15.2 nJ	
Angle deviation		max. +/- 1.5 °	
Diameter of the light spot		approx. 2 mm at a distance of 150 mm	
Opening angle		approx. 1 °	
Ambient light limit		EN 60947-5-2 : 30000 Lux	
Resolution		0.1 mm	
Functional safety related parameters			
MTTF <sub>d</sub>		560 a	
Mission Time (T <sub>M</sub> )		20 a	
Diagnostic Coverage (DC)		0 %	
Indicators/operating means			
Operation indicator		LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode	
Function indicator		LED yellow: constantly on - switch output active constantly off - switch output inactive	
Control elements		Teach-In key	
Control elements		5-step rotary switch for operating modes selection	
Electrical specifications			
Operating voltage	$U_B$	10 30 V DC	
Ripple		max. 10 %	
No-load supply current	I <sub>0</sub>	< 25 mA at 24 V supply voltage	
Protection class		III	
Interface			
Interface type		IO-Link (via $C/Q = pin 4$ )	
IO-Link revision		1.1	
Device profile		Smart Sensor	
Device ID		0x110906 (1116422)	
Transfer rate		COM2 (38.4 kBit/s)	
Min. cycle time		3 ms	
Process data width		Process data input 3 Byte Process data output 2 Bit	
SIO mode support		yes	
Compatible master port type		A	
Output			
Switching type		The default setting is: C/Q - Pin4: NPN normally open, PNP normally closed, IO-Link	
Signal output		1 push-pull (4 in 1) output, short-circuit protected, reverse polarity protected, overvoltage protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA , resistive load	



Technical Data		
rechincar Data		
Usage category		DC-12 and DC-13
Voltage drop	U <sub>d</sub>	≤ 1.5 V DC
Response time		2 ms
Conformity		
Communication interface		IEC 61131-9
Product standard		EN 60947-5-2
Laser safety		EN 60825-1:2014
Measurement accuracy		
Temperature drift		0.05 %/K
Warm up time		5 min
Repeat accuracy		≤1 %
Linearity error		±1%
Approvals and certificates		
UL approval		E87056 , cULus Listed , class 2 power supply , type rating 1
FDA approval		IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007
Ambient conditions		
Ambient temperature		10 60 °C (50 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		13.9 mm
Housing height		41.4 mm
Housing depth		18.3 mm
Degree of protection		IP67 / IP69 / IP69K
Connection		M8 x 1 connector, 3-pin
Material		
Housing		PC (Polycarbonate)
Optical face		PMMA
Mass		approx. 10 g

## Connection



# **Connection Assignment**



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


3

## **Connection Assignment**

Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
3	BU	(blue)
4	BK	(black)

## Assembly



## **Safety Information**



Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey

**TEACH-IN** button

Mode rotary switch

Operating indicator

Switch output 2 / B

Keylock

Switch output indicator Q2

Switch output indicator Q1

Switch output 1 / switch point B

Switch output 1 / switch point A

Switch output 2 / switch point A

1

2

3

4

5

|

Ш

IV

٧

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

1

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 267075-100222\_eng.pdf

USA: +1 330 486 0001 Gerr fa-info@us.pepperl-fuchs.com fa-info

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



4

#### **Distance sensor**

Acces	Accessories		
6/	V31-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey	
6/	V3-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey	
le la	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs	
n e e e e e e e e e e e e e e e e e e e	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs	
and a second second	ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs	
	ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs	
	ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors	
8	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal	
	ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals	
	ICE3-8IOL-K45S-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal	
	IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection	

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

5

## Teach-In

You can use the rotary switch to select the relevant switching threshold A and/or B for teaching in for switch signal Q1 or Q2. The yellow LEDs indicate the current state of the selected output.

To store a threshold value, press and hold the "TI" button until the yellow and green LEDs flash in phase (approx. 1 s). Teach-In starts when the "TI" button is released.

Successful Teach-In is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.


An unsuccessful Teach-In is indicated by rapidly alternating flashing (8 Hz) of the yellow and green LEDs.

After an unsuccessful Teach-In, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.


Different switching modes can be defined by teaching in the relevant distance measured values

for the switching thresholds A and B:

Single point mode:



Window mode:



Every taught-in switching threshold can be retaught (overwritten) by pressing the "TI" button again.

Pressing and holding the "TI" button for > 4 s completely deletes the taught-in value. The yellow and green LEDs go out simultaneously to indicate that this procedure has been completed. Successful resetting is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

#### **Resetting to Factory Default Settings**

Press the "TI" button for > 10 s in rotary switch position ,O' to reset to factory default settings. The yellow and green LEDs go out simultaneously to indicate the resetting.

Resetting process starts when the "TI" button is released and is indicated by the yellow LED. After the process the sensor works with factory default settings, immediately.

OMT:

- Factory default settings switch signal Q1: Switch signal active, window mode
- Factory default settings switch signal Q2: Switch signal active, window mode

OQT:

- Factory default settings switch signal Q1:
- Switch signal active, BGS mode (background suppression) • Factory default settings switch signal Q2:
- Switch signal active, BGS mode (background suppression)

## Configuration

#### Setting different operating modes via the IO-Link interface

The devices are equipped with an IO-Link interface as standard for diagnostics and parameterization tasks to ensure optimum adjustment of the sensors to the relevant application.

#### Single point mode operating mode (one switch point):

- "Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.
- "The switch point corresponds exactly to the set point.

active detection range

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 267075-100222\_eng.pdf

Background suppression



#### **Distance sensor**

#### Window mode operating mode (two switch points):

- Detection of objects irrespective of type and color in a defined detection range. Reliable detection when object leaves the detection range.
- Window mode with two switch points.

a	ctive detection range
Foreground suppression	Background suppression

#### Center window mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Sets a defined window around a given object. Objects outside this window are not detected.
- Window mode with one switch point.

active	detection range
Foreground suppression	Background suppression

#### Two point mode operating mode (hysteresis operating mode):

• Detection of objects irrespective of type and color between a defined switch-on and switch-off point.

	active detection range	
		Output
Output	Hysteresis	Culpur

Inactive operating mode:

• Evaluation of switching signals is deactivated.

The associated IODD device description file can be found in the download area at www.pepperl-fuchs.com.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"