



Triangulation sensor (SbR) OQT120-R103-2EP-IO-V31



- Miniature design with versatile mounting options
- Multi Pixel Technology (MPT) flexibility and adaptability
- Reduction of device variety several switch points within one
- Reliable detection of all surfaces, independent of color and structure
- Low sensitivity to target color
- IO-Link interface for service and process data

Measuring sensor with multiple switch points, small design, background suppression and more adjustable operating modes, IO-Link interface









Function

The R103 series miniature optical sensors are the first devices of their kind to offer an endto- end solution in a small single standard design from thru-beam sensor through to a distance measurement device. As a result of this design, the sensors are able to perform practically all standard automation tasks.


The entire series enables sensors to communicate via IO-Link.


The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.


The use of Multi Pixel Technology gives the standard sensors a high level of flexibility and enables them to adapt more effectively to their operating environment.


www.pepperl-fuchs.com


Dimensions












Technical Data

General specifications			
Detection range	5 120 mm		
Detection range min.	5 20 mm		
Detection range max.	5 120 mm		
Adjustment range	20 120 mm		
Reference target	standard white, 100 mm x 100 mm		
Light source	LED		
Light type	modulated visible red light		
LED risk group labelling	exempt group		
Black-white difference (6 %/90 %)	< 5 % at 120 mm		
Diameter of the light spot	approx. 8 mm at a distance of 120 mm		
Opening angle	approx. 4 °		
Ambient light limit	EN 60947-5-2 : 30000 Lux		
Functional safety related parameters			
MTTF _d	600 a		
Mission Time (T _M)	20 a		
Diagnostic Coverage (DC)	0 %		
Indicators/operating means			
Operation indicator	LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode		

Technical Data Function indicator LED yellow: constantly on - switch output active constantly off - switch output inactive Control elements Teach-In key Control elements 5-step rotary switch for operating modes selection Electrical specifications U_B 10 ... 30 V DC Operating voltage Ripple max. 10 % < 25 mA at 24 V supply voltage No-load supply current Protection class Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision 1.1 Device profile **Smart Sensor** Device ID 0x110803 (1116163) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms Process data width Process data input 2 Bit Process data output 2 Bit SIO mode support yes Compatible master port type Α Output Switching type The default setting is: C/Q - Pin4: NPN normally open, PNP normally closed, IO-Link Q2 - Pin2: NPN normally-open, PNP normally-closed Signal output 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load Usage category DC-12 and DC-13 Voltage drop U_{d} ≤ 1.5 V DC Switching frequency f 217 Hz Response time 2.3 ms Conformity Communication interface IEC 61131-9 Product standard EN 60947-5-2 Approvals and certificates **UL** approval E87056, cULus Listed, class 2 power supply, type rating 1 **Ambient conditions** Ambient temperature -40 ... 60 °C (-40 ... 140 °F) Storage temperature -40 ... 70 °C (-40 ... 158 °F) Mechanical specifications Housing width 15 mm Housing height 43.9 mm Housing depth 26.7 mm Degree of protection IP67 / IP69 / IP69K Connection M8 x 1 connector, 4-pin Material Housing PC (Polycarbonate) Optical face **PMMA** Mass approx. 12 g

FPEPPERL+FUCHS

Connection




Connection Assignment




Wire colors in accordance with EN 60947-5-2

1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)

Assembly







1	Teach-in button
2	Mode rotary switch
3	Switch output indicator Q2
4	Switch output indicator Q1
5	Operating indicator

1	Switch output 1 / switch point B
	Switch output 1 / switch point A
Ш	Switch output 2 / switch point A
IV	Switch output 2 / switch point B
٧	Keylock

Characteristic Curve





Accessories

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
1	OMH-R103-01	Mounting bracket
8	OMH-ML6	Mounting bracket
	OMH-ML6-U	Mounting bracket
CARE	OMH-ML6-Z	Mounting bracket
4 83	OMH-R10X-01	Mounting bracket
	OMH-R10X-04	Mounting bracket
T. T	OMH-R10X-10	Mounting bracket

Accessories OMH-ML100-031 Mounting aid for round steel ø 10 ... 14 mm or sheet 1 mm ... 5 mm OMH-ML100-03 Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE2-8IOL-K45S-RJ45 ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection V31-GM-2M-PUR Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey V31-WM-2M-PUR



You can use the rotary switch to select the relevant switching threshold A and/or B for teaching in for switch signal **Q1 or Q2**. The yellow LEDs indicate the current state of the selected output.

To store a threshold value, press and hold the "TI" button until the yellow and green LEDs flash in phase (approx. 1 s). Teach-In starts when the "TI" button is released.


Successful Teach-In is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

An unsuccessful Teach-In is indicated by rapidly alternating flashing (8 Hz) of the yellow and green LEDs.


After an unsuccessful Teach-In, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Different switching modes can be defined by teaching in the relevant distance measured values for the switching thresholds A and B:

Single point mode:



Window mode:



Every taught-in switching threshold can be retaught (overwritten) by pressing the "TI" button again.

Pressing and holding the "TI" button for > 4 s completely deletes the taught-in value. The yellow and green LEDs go out simultaneously to indicate that this procedure has been completed. Successful resetting is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

Resetting to Factory Default Settings

Press the "TI" button for > 10 s in rotary switch position ,O' to reset to factory default settings. The yellow and green LEDs go out simultaneously to indicate the resetting.

Resetting process starts when the "TI" button is released and is indicated by the yellow LED. After the process the sensor works with factory default settings, immediately.

OMT:

- Factory default settings switch signal Q1: Switch signal active, window mode
- Factory default settings switch signal Q2: Switch signal active, window mode

OQT:

- Factory default settings switch signal Q1:
 Switch signal active, BGS mode (background suppression)
- Factory default settings switch signal Q2: Switch signal active, BGS mode (background suppression)

Configuration

Configuring different operating modes via the IO-Link interface

The devices are equipped with an IO-Link interface as standard for diagnostics and parameterization tasks to ensure optimum adjustment of the sensors to the relevant application. Four different operating modes can be set, among other features:

Background suppression operating mode (one switch point):

• Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.



Background evaluation operating mode (one switch point):

• Detection of objects irrespective of type and color against a defined background. Reliable detection of objects at close range

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 267075-100354_eng.pdf

Triangulation sensor (SbR)

(detection range >= 0 mm). The background serves as reference.

active detection range

Background evaluation

Single point mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.
- The switch point corresponds exactly to the set point.




Window mode operating mode (two switch points):

- Detection of objects irrespective of type and color in a defined detection range. Reliable detection when object leaves the
 detection range.
- · Window mode with two switch points.




Center window mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Sets a defined window around a given object.
 Objects outside this window are not detected.
- · Window mode with one switch point.



Two point mode operating mode (hysteresis operating mode):

Detection of objects irrespective of type and color between a defined switch-on and switch-off point.



Inactive operating mode:

• Evaluation of switching signals is deactivated.

The associated IODD device description file can be found in the download area at www.pepperl-fuchs.com.