

Vibration Limit Switch LVL-A7-BG4B-E5PU-CG-EMS

- Limit switch for liquids
- Process connection G1
- Suitable for process temperatures up to 150 °C (302 °F)
 - Rugged stainless steel housing
- Onsite function check possible thanks to LED indication
- External function test with test magnet

CEU


Function


The Vibracon LVL-A7 is a limit switch for liquids and is used in tanks, vessels and pipes. The device is used for overfill prevention or pump protection in cleaning and filter systems as well as in cooling and lubrication vessels, for instance. The device is suitable for applications in which float switches or conductive, capacitance and optical sensors have been used up to now. The device also works in areas where these measuring principles are not suitable due to conductivity, buildup, turbulence, flow conditions or air

bubbles. The device can be used for process temperatures up to 150 °C (302 °F). The device is not suitable for use in hazardous areas.


For hygienic areas we recommend the use of Vibracon LVL A7H.

Connection





Dimensions



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



Technical Data

LVL-A7-BG4B-E5PU-CG-EMS

General specifications		
Measuring method		The tuning fork is brought to its resonance frequency by means of a piezoelectric drive If the tuning fork is covered by liquid, this frequency changes. The electronics monitor the resonance frequency and indicate whether the tuning fork is freely vibrating or is covered by liquid.
Construction type		device with short tube
Operating mode		MAX = maximum safety: The device keeps the electronic switch closed as long as the liquid level is below the fork. example application: overspill protection MIN = minimum safety: The device keeps the electronic switch closed as long as the fork is immersed in liquid example application: dry running protection of pumps The electronic switch opens if the limit is reached, if a fault occurs or in the event of a power fails (quiescent current principle)
Series		LVL-A*
Supply		
Connection		This device may be used with any sequential circuit, as long as the circuit can support the electrical circuit values of the switching elements.
Rated voltage	Ur	10 35 V DC
Fusing		external 500 mA slow
Current consumption		< 15 mA
Power consumption		975 mW
Residual ripple		5 V _{ss} at 0 400 Hz
Input		
Measured variable		density
Measurement range		min. 0.7 g/cm ³
Output		
Output type		switching output
Switching current		max. 250 mA
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU		EN 61326-1:2006, EN 61326-2-3:2006
Directive 2004/108/EC		EN 61326-1:2006, EN 61326-2-3:2006
Conformity		
Electromagnetic compatibility		NE 21
Degree of protection		IEC 60529
Shock resistance		EN 60068-2-27
Vibration resistance		EN 60068-2-64
Climate class		DIN EN 60068-2-38/IEC 68-2-38
Measurement accuracy		Din Lin 00000-2-30/IEC 00-2-30
Reference operating conditions		 ambient temperature: 25 °C (+77 °F) process pressure: 1 bar (14.5 psi) fluid: water (density: approx. 1 g/cm³, viscosity: 1 mm²/s) medium temperature: 25 °C (+77 °F) density setting: > 0.7 g/cm³ switching time delay: standard (0,5 s, 1 s)
Measured value resolution		< 0.5 mm
Measuring frequency		approx. 1100 Hz in air
Switching point		13 mm ± 1 mm
Non-repeatability		± 1 mm acc. to DIN 61298-2
Hysteresis		max. 3 mm
Influence of ambient temperature		negligible
Influence of medium temperature		-25 μm/°C
Influence of medium pressure		-20 μm/bar
Switching time		 - 0.5 s when tuning fork is covered - 1.0 s when tuning fork is uncovered
Switch-on delay		max. 3 s
Operating conditions		
-		

Installation conditions

Installation conditions

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Release date: 2023-12-18 Date of issue: 2023-12-18 Filename: 275573-100030_eng.pdf

Germany: +49 621 776 2222 pa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 pa-info@sg.pepperl-fuchs.com **Technical Data**

LVL-A7-BG4B-E5PU-CG-EMS

Installation position	see technical information (TI)
Ambient conditions	
Ambient temperature	-40 70 °C (-40 158 °F)
Storage temperature	-40 85 °C (-40 185 °F)
Shock resistance	a = 300 m/s ² = 30 g, 3 planes x 2 directions x 3 shocks x 18 ms, as per test Ea
Vibration resistance	a(RMS) = 50 m/s², ASD = 1.25 (m/s²)²/Hz, f = 5 to 2000 Hz, t = 3 x 2 h
Process conditions	
Medium temperature	-40 150 °C (-40 302 °F)
Process pressure (static pressure)	-1 +40 bar (-14.5 +580 psi)
State of aggregation	liquid
Density	min. 0.7 g/cm ³
Viscosity	1 10000 mPa/s, dynamic viscosity
Solid contents	< Ø5 mm
Mechanical specifications	
Degree of protection	IP65 , NEMA 4X
Connection	valve connector M16
Material	process connection and short tube: stainless steel 316L (1.4401/1.4435) tuning fork: stainless steel 316L housing cover and connector: PPSU
Surface quality	R _a < 3.2 μm
Mass	approx. 169 g
Process connection	thread G1 acc. to ISO 228
Indication and operation	
Display elements	The LED display is on the connection side. - green LED: indication of ready to operate - red LED: fault indication - yellow LED: operating mode indication
Function test	function test with test magnet (optional accessory)
Certificates and approvals	
CSA approval	cCSAus Listed, General Purpose
Overspill protection	see approval (ZE)
General information	
Supplementary documentation	technical information (TI) manual (BA) approval (ZE)
Supplementary information	Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl- fuchs.com.
Accessories	
Designation	see technical information (TI)

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3