



Retroreflective sensor OBR15M-R201-2EP-IO-0,3M-V1



- Medium design with versatile mounting options
- Extended temperature range -40 °C ... 60 °C
- High degree of protection IP69K
- IO-Link interface for service and process data

Retroreflective sensor with polarization filter











Function


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design - from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.

Dimensions




Technical Data

| Effective detection range 0 15 m Reflector distance 0.02 15 m Threshold detection range 18.5 m Reference target H85-2 reflector Light source LED Light type modulated visible red light LED risk group labelling exempt group Polarization filter yes Diameter of the light spot approx. 520 mm at a distance of 15 m Opening angle 2° Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d 724 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode | General specifications | |
|---|--------------------------------------|--|
| Threshold detection range Reference target Light source Light type Light type Light type LED modulated visible red light LED risk group labelling Polarization filter Diameter of the light spot Opening angle Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Effective detection range | 0 15 m |
| Reference target Light source Light type Light type LeD risk group labelling Polarization filter Diameter of the light spot Opening angle Ambient light limit Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator H85-2 reflector LED modulated visible red light exempt group yes approx. 520 mm at a distance of 15 m 2 ° Approx. 520 mm at a distance of 15 m 3 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 4 ° Approx. 520 mm at a distance of 15 m 5 ° Approx. 520 mm at a distance of 15 m 5 ° App | Reflector distance | 0.02 15 m |
| Light source Light type Light type LED risk group labelling Polarization filter Diameter of the light spot Opening angle Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Threshold detection range | 18.5 m |
| Light type modulated visible red light LED risk group labelling exempt group Polarization filter yes Diameter of the light spot approx. 520 mm at a distance of 15 m Opening angle 2° Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d 724 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Reference target | H85-2 reflector |
| LED risk group labelling exempt group Polarization filter yes Diameter of the light spot approx. 520 mm at a distance of 15 m Opening angle 2° Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d 724 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Light source | LED |
| Polarization filter Diameter of the light spot Opening angle Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Light type | modulated visible red light |
| Diameter of the light spot approx. 520 mm at a distance of 15 m Opening angle 2° Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d 724 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | LED risk group labelling | exempt group |
| Opening angle Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Polarization filter | yes |
| Ambient light limit Functional safety related parameters MTTF _d Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Diameter of the light spot | approx. 520 mm at a distance of 15 m |
| Functional safety related parameters MTTF _d 724 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Opening angle | 2° |
| MTTF _d 724 a Mission Time (T _M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: | Ambient light limit | EN 60947-5-2 : 60000 Lux |
| Mission Time (T _M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Functional safety related parameters | |
| Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | MTTF _d | 724 a |
| Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Mission Time (T _M) | 20 a |
| Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit | Diagnostic Coverage (DC) | 0 % |
| constantly on - power on flashing (4Hz) - short circuit | Indicators/operating means | |
| | Operation indicator | constantly on - power on flashing (4Hz) - short circuit |

| Technical Data | | |
|---|----------------|---|
| Function indicator | | Yellow LED: Permanently lit - light path clear Permanently off - object detected Flashing (4 Hz) - insufficient operating reserve |
| Control elements | | Light-on/dark-on changeover switch |
| Control elements | | sensitivity adjustment |
| Electrical specifications | | |
| Operating voltage | U _B | 10 30 V DC |
| Ripple | | max. 10 % |
| No-load supply current | I ₀ | < 18 mA at 24 V Operating voltage |
| Protection class | | III |
| Interface | | |
| Interface type | | IO-Link (via $C/Q = pin 4$) |
| IO-Link revision | | 1.1 |
| Device profile | | Identification and diagnosis Smart Sensor type 2.4 |
| Device ID | | 0x111211 (1118737) |
| Transfer rate | | COM2 (38.4 kBit/s) |
| Min. cycle time | | 2.3 ms |
| Process data width | | Process data input 2 Bit Process data output 2 Bit |
| SIO mode support | | yes |
| Compatible master port type | | A |
| Output | | |
| Switching type | | The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link /Q - Pin2: NPN normally closed / light-on, PNP normally open / dark-on |
| Signal output | | 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 100 mA, resistive load |
| Usage category | | DC-12 and DC-13 |
| Voltage drop | U _d | ≤ 1.5 V DC |
| Switching frequency | f | 1000 Hz |
| Response time | | 0.5 ms |
| Conformity | | |
| Communication interface | | IEC 61131-9 |
| Product standard | | EN 60947-5-2 |
| Approvals and certificates | | |
| UL approval | | E87056, cULus Listed, class 2 power supply, type rating 1 |
| CCC approval | | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions Ambient temperature | | -40 60 °C (-40 140 °F) , fixed cable |
| Change to many and | | -20 60 °C (-4 140 °F), movable cable not appropriate for conveyor chains |
| Storage temperature | | -40 70 °C (-40 158 °F) |
| Mechanical specifications | | 45 |
| Housing width | | 15 mm |
| Housing height | | 61.7 mm |
| Housing depth | | 41.7 mm |
| Degree of protection | | IP67 / IP69 / IP69K |
| Connection | | 300 mm fixed cable with M12 x 1, 4-pin connector |
| Material | | PC (Polygorhanata) |
| Housing | | PC (Polycarbonate) |
| Optical face | | PMMA |
| Mass | | approx. 55 g |
| Cable length | | 0.3 m |

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


ΒN (brown) 2 WH (white) BU (blue) BK (black)

Assembly




| 1 | Sensitivity adjustment | |
|---|--------------------------------------|----|
| 2 | Light-on / dark-on changeover switch | |
| 3 | Operating indicator / dark on | GN |
| 4 | Signal indicator | YE |
| 5 | Operating indicator / light on | GN |

Characteristic Curve



Characteristic Curve



Commissioning

To unlock the adjustment functions turn the sensing range / sensitivity adjuster for more than 180 degrees.

Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.

Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.

If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on / dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

Restore Factory Settings

Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range / sensitivity adjuster for more than 180 degrees.

Accessories

| REF-H85-2 | Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes |
|-------------|--|
| REF-C110-2 | Reflector, round ø 84 mm, central mounting hole |
| REF-H50 | Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap |
| REF-VR10 | Reflector, rectangular 60 mm x 19 mm, mounting holes |
| OFR-100/100 | Reflective tape 100 mm x 100 mm |
| OMH-RL31-02 | Mounting bracket narrow |

Accessories OMH-RL31-03 Mounting bracket narrow OMH-RL31-04 Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm OMH-RL31-07 Mounting bracket including adjustment OMH-RL31-08 Mounting aid for round steel ø 12 mm or sheet 1.5 mm ... 3 mm OMH-R20x-Quick-Mount | Quick mounting accessory ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors V1-G-2M-PUR Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey V1-W-2M-PUR Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey