

UB800-18GM60A-E5-V1-M




- Short version: 55 mm
- Function indicators visible from all directions
- Switching output
- 5 different output functions can be set
- Program input
- Temperature compensation
- E1-Type approval

Single head system



Dimensions



Technical Data


General specifications		
Sensing range		50 800 mm
Adjustment range		70 800 mm
Dead band		0 50 mm
Standard target plate		100 mm x 100 mm
Transducer frequency		approx. 255 kHz
Response delay		approx. 100 ms
Indicators/operating means		
LED green		Power on
LED yellow		indication of the switching state flashing: program function object detected
LED red		solid red: Error red, flashing: program function, object not detected
Electrical specifications		
Operating voltage	U _B	10 30 V DC , ripple 10 %ss
No-load supply current	I_0	≤ 20 mA
Input		

Technical Data Input type 1 program input operating distance 1: -U_B ... +1 V, operating distance 2: +6 V ... +U_B input impedance: > 4,7 kΩ program pulse: ≥ 1 s Output 1 switching output E5, PNP NO/NC, programmable Output type Rated operating current 200 mA, short-circuit/overload protected Default setting Switch point A1: 70 mm Switch point A2: 800 mm Voltage drop $U_{\text{d}} \\$ ≤3 V Repeat accuracy ≤1 % Switching frequency f ≤ 4 Hz Н 1 % of the set operating distance Range hysteresis Temperature influence ± 1.5 % of full-scale value Compliance with standards and directives Standard conformity Standards EN IEC 60947-5-2:2020 IEC 60947-5-2:2019 Approvals and certificates **UL** approval cULus Listed, General Purpose CCC approval CCC approval / marking not required for products rated ≤36 V UN/ECE Regulation No. 10 (E1) Type-approval number: 10R-058090 **Ambient conditions** Ambient temperature -25 ... 70 °C (-13 ... 158 °F) Storage temperature -40 ... 85 °C (-40 ... 185 °F) Mechanical specifications Connection type Connector plug M12 x 1, 4-pin Housing diameter 18 mm IP67 Degree of protection Material Housing brass, nickel-plated Transducer epoxy resin/hollow glass sphere mixture; foam polyurethane, cover PBT Mass 32 g

Connection

Standard symbol/Connections:

(version E5, pnp)



Core colours in accordance with EN 60947-5-2.

Connection Assignment




Connection Assignment

Wire colors in accordance with EN 60947-5-2

BN (brown) 2 WH (white) 3 BU (blue) 4 BK (black)


Characteristic Curve

Characteristic response curve



Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

Programmable output modes



^{5.} A1 -> ∞ , A2 -> ∞ : Object presence detection mode Object detected: Switch output closed No object detected: Switch output open

Accessories

21	UB-PROG2	Programming unit
	OMH-04	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	BF 18	Mounting flange, 18 mm
	BF 18-F	Plastic mounting adapter, 18 mm

Accessories BF 5-30 Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm V1-G-2M-PVC Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey V1-W-2M-PUR Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey

Adjusting the switching points

The ultrasonic sensor features a switch output with two teachable switching points. These are set by applying the supply voltage -UB or +UB to the TEACH-IN input. The supply voltage must be applied to the TEACH-IN input for at least 1 s. LEDs indicate whether the sensor has recognised the target during the TEACH-IN procedure. Switching point A1 is taught with -UB, A2 with +U_B.

Five different output functions can be set

- 1. Window mode, normally-open function
- 2. Window mode, normally-closed function
- 3. one switching point, normally-open function
- 4. one switching point, normally-closed function
- 5. Detection of object presence

TEACH-IN window mode, normally-open function

- Set target to near switching point
- TEACH-IN switching point A1 with -UB
- Set target to far switching point
- TEACH-IN switching point A2 with +U_B

TEACH-IN window mode, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A2 with +U_B
- Set target to far switching point
- TEACH-IN switching point A1 with -UB

TEACH-IN switching point, normally-open function

- Set target to near switching point
- TEACH-IN switching point A2 with +U_B
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UB

TEACH-IN switching point, normally-closed function

- Set target to near switching point
- TEACH-IN switching point A1 with -UB
- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A2 with +U_B

TEACH-IN detection of objects presence

- Cover sensor with hand or remove all objects from sensing range
- TEACH-IN switching point A1 with -UR
- TEACH-IN switching point A2 with +U_B

LED Displays

Displays in dependence on operating mode	Red LED	Yellow LED
TEACH-IN switching point:		
Object detected	off	flashes
No object detected	flashes	off
Object uncertain (TEACH-IN invalid)	On	off
Normal operation	off	Switching state
Fault	on	Previous state