

# Triangulation sensor (BGE) OBT300-R200-2EP-IO-V31-1T



- Medium design with versatile mounting options
- Secure and gapless detection, even near the surface through background evaluation
- Precision object detection, almost irrespective of the color
- Extended temperature range -40 °C ... 60 °Ċ
- High degree of protection IP69K
- IO-Link interface for service and process data

Triangulation sensor with background evaluation











#### **Function**


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design – from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.

#### **Dimensions**



Technical Data


#### **General specifications** Detection range 30 ... 300 mm Detection range min. 30 ... 80 mm Detection range max. 30 ... 300 mm Adjustment range 80 ... 300 mm Reference target standard white, 100 mm x 100 mm Light source modulated visible red light Light type LED risk group labelling exempt group Black-white difference (6 %/90 %) < 5 % at 300 mm Diameter of the light spot approx. 8 mm x 8 mm at a distance of 300 mm Opening angle approx. 1.5° Ambient light limit EN 60947-5-2: 70000 Lux Functional safety related parameters $\mathsf{MTTF}_\mathsf{d}$ 600 a Mission Time (T<sub>M</sub>) 20 a 0 % Diagnostic Coverage (DC) Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator LED vellow: constantly on - background detected (object not detected) constantly off - object detected Control elements Light-on/dark-on changeover switch Control elements Sensing range adjuster **Electrical specifications** Operating voltage $\mathsf{U}_\mathsf{B}$ 10 ... 30 V DC Ripple max. 10 % No-load supply current < 26 mA at 24 V supply voltage $I_0$ Protection class Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision Device profile Identification and diagnosis Smart Sensor type 2.4 Device ID 0x111702 (1120002) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms Process data width Process data input 1 Bit Process data output 2 Bit SIO mode support ves Compatible master port type Α Output The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link /Q - Pin2: NPN normally closed / light-on, PNP normally open / dark-on Switching type Signal output 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max, 30 V DC Switching current max. 100 mA, resistive load Usage category DC-12 and DC-13 ≤ 1.5 V DC Voltage drop $U_{\text{d}}$ Switching frequency f 500 Hz Response time 1 ms

Conformity

| ,   |  |
|-----|--|
|     | C  |
|     | 2  |
|     | -  |
|     | 7  |
|     | ã  |
|     | Ĭ  |
|     | $\overline{2}$                           |
|     | č  |
| 1   | 2  |
| 1   | ≒  |
| - 8 | ⋍  |
|     | ٠,                                       |
| - 9 |  |
| Į   | Ŋ  |
|     | Ľ  |
| -   | 7  |
|     | o  |
| 1   |  |
|     | a  |
|     | č  |
|     | Ξ  |
|     | C  |
|     | ž  |
|     | u  |
| į   | Ī  |
|     | 4  |
| - 1 |  |
|     | ٦  |
|     | '  |
|     | ֚֚֚֚֡֝֜֝֜֝֟֝֟֝֟֝ <del>֚</del>            |
|     | 2-01                                     |
|     | 23-01                                    |
|     | 23-01                                    |
|     | 2003-01-0                                |
|     | - 10-8606 -                              |
|     | - LU-8006 - ol                           |
|     | -10-8003-01-3                            |
|     | Selia 2023-01-3                          |
|     | Icelia: 2023-01-2                        |
|     | of ice io 2023-01-2                      |
|     | of ice in 2023-01-2                      |
|     | to of ice io '2023-01-2                  |
|     | 2-10-2003-01-3                           |
|     | Date of ice in: 2023-01-3                |
|     | 1 Date of ice in 2023-01-3               |
|     | 24 Date of ice in: 2023-01-3             |
|     | -24 Date of ice in 2023-01-3             |
|     | 1-24 Date of ice in: 2023-01-3           |
|     | .01-24 Date of ice in: 2023-01-2         |
|     | 3-01-24 Date of ice io: 2023-01-3        |
|     | 23-01-24 Date of ice in 2023-01-3        |
|     | 123-01-24 Date of ice inc 2023-01-2      |
|     | 2023-01-24 Date of issue: 2023-01-2      |
|     | 2003-01-24 Date of issue: 2003-01-3      |
|     | a. 2023-01-24 Date Oficeria. 2023-01-2   |
|     | Po. 2023-01-24 D                         |
|     | ate: 2023-01-24 Date of issue: 2023-01-3 |

| Technical Data             |  |
|----------------------------|--|
| Communication interfere    | IEO 04404 0  |
| Communication interface    | IEC 61131-9  |
| Product standard           | EN 60947-5-2   |
| Approvals and certificates |  |
| UL approval                | E87056, cULus Listed, class 2 power supply, type rating 1    |
| CCC approval               | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions         |  |
| Ambient temperature        | -40 60 °C (-40 140 °F)                                       |
| Storage temperature        | -40 70 °C (-40 158 °F)                                       |
| Mechanical specifications  |  |
| Housing width              | 15 mm  |
| Housing height             | 50.6 mm  |
| Housing depth              | 41.7 mm  |
| Degree of protection       | IP67 / IP69 / IP69K  |
| Connection                 | 4-pin, M8 x 1 connector, 90° rotatable                       |
| Material                   |  |
| Housing                    | PC (Polycarbonate)   |
| Optical face               | PMMA   |
| Mass                       | approx. 35 g   |

# Connection




# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


| 1 | BN | (browr  |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue)  |
| 4 | BK | (black) |

# **Assembly**



| 1 | Sensitivity adjustment               |  |
|---|--------------------------------------|--|
| 2 | Light-on / dark-on changeover switch |  |
| 3 | 3 Operating indicator / dark on G    |  |
| 4 | Signal indicator                     |  |
| 5 | Operating indicator / light on       |  |

# Minimum object height (typical)



# **Accessories**

| 6/         | V31-GM-2M-PUR        | Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey        |
|------------|----------------------|---|
| 61         | V31-WM-2M-PUR        | Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey          |
| Men        | OMH-MLV12-HWG        | Mounting bracket for series MLV12 sensors                                     |
| THE OF HER | OMH-R200-01          | Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm                     |
|            | OMH-MLV12-HWK        | Mounting bracket for series MLV12 sensors                                     |
| 77         | OMH-R20x-Quick-Mount | Quick mounting accessory  |
| The S      | ICE2-8IOL-G65L-V1D   | EtherNet/IP IO-Link master with 8 inputs/outputs                              |
| 11-        | ICE3-8IOL-G65L-V1D   | PROFINET IO IO-Link master with 8 inputs/outputs                              |
| 9          | ICE2-8IOL-K45S-RJ45  | EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal    |
|            | ICE3-8IOL-K45P-RJ45  | PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals |
| 9          | ICE3-8IOL-K45S-RJ45  | PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal    |

# IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors

To unlock the adjustment functions, rotate the sensing range/sensitivity adjuster by more than 180°.

#### Sensing Range/Sensitivity

To increase the sensing range/sensitivity, rotate the sensing range/sensitivity adjuster clockwise.

To reduce the sensing range/sensitivity, rotate the sensing range/sensitivity adjuster counter-clockwise.

As soon as the end of the adjustment range is reached, the signal indicator flashes at 8 Hz.

### Configuring Light On/Dark On

Press the light-on/dark-on changeover switch for more than 1 second (but less than 4 seconds). "Light on/dark on" mode changes and the relevant operating indicator lights up.

If you press the light-on/dark-on changeover switch for longer than 4 seconds, the "light on/dark on" mode will switch back to the original setting. The current status is activated when the light-on/dark-on changeover switch is released.

#### **Restoring Factory Settings**

Press the light-on/dark-on changeover switch for more than 10 seconds (but less than 30 seconds) until all LEDs go out. When the light-on/dark-on changeover switch is released, the signal indicator lights up. After 5 seconds, the sensor resumes operation with the factory settings.

The adjustment functions are locked after 5 minutes of inactivity. To unlock the adjustment functions, rotate the sensing range/sensitivity adjuster again by more than 180°.