

SMART Current Driver KFD2-SCD2-Ex2.LK

- 2-channel isolated barrier
- 24 V DC supply (Power Rail)
- Current output up to 650 Ω load
- HART-IP and valve positioner
- Line fault detection (LFD)
- Accuracy 0.1 %
- Up to SIL 2 (SC 3) acc. to IEC/EN 61508















Function

This isolated barrier is used for intrinsic safety applications.

The device drives SMART I/P converters, electrical valves, and positioners in hazardous areas.

Digital signals are superimposed on the analog values at the field side or control side and are transferred bi-directionally.

Current transferred across the DC/DC converter is repeated at terminals 1, 2 and 4, 5. Terminals 2, 3 and 5, 6 are used when no short circuit


detection is required.


An open or short field circuit presents a high impedance to the control side to allow alarm conditions to be monitored by the control system. If the HART communication resistance in the loop is too low, the internal resistance can be used.

Test sockets for the connection of HART communicators are integrated into the terminals of the device.

A fault is signalized by LEDs and a separate collective error message output.

Connection






Technical Data

Release date: 2023-03-02 Date of issue: 2023-03-02 Filename: 295089_eng.pdf

General specifications				
Signal type		Analog output		
Functional safety related parameters				
Safety Integrity Level (SIL)		SIL 2		
Systematic capability (SC)		SC 3		
Supply				
Connection		Power Rail or terminals 14+, 15-		
Rated voltage	U_{r}	19 30 V DC		
Ripple		≤ 10 %		

Rated current	≤ 45 mA at 24 V	
Power dissipation	\leq 1 W at 20 mA and 500 Ω load	
Power consumption	≤ 1 W	
nput		
Connection side	control side	
Connection	terminals 7-, 8+, (9+); 10-, 11+, (12+)	
Input signal	4 20 mA, limited to approx. 30 mA	
Input voltage	open loop voltage of the control system \leq 30 V	
Voltage drop	approx. 6 V at 20 mA	
Input resistance	field wiring open circuit : > 100 k Ω field wiring < 50 Ω : > 100 k Ω when using terminals 1, 2 a	nd 4, 5
utput		
Connection side	field side	
Connection	terminals 1+, 2-; 4+, 5- terminals 3+, 2-; 6+, 5- (no short circuit detection)	
Voltage	≥ 13 V at 20 mA	
Current	4 20 mA	
Load	100 650 Ω , for terminals 1, 2; 4, 5 0 550 Ω , for Terminals 2, 3; 5, 6	
Ripple	20 mV rms	
Line fault detection	breakage, load > 100 k Ω , short-circuit, load < 50 Ω	
ault indication output		
Output type	open collector transistor (internal fault bus)	
ransfer characteristics		
Deviation	at 20 °C (68 °F), 4 20 mA < 0.1 % of full scale, incl. non-linearity and hysteresis	
Influence of ambient temperature	< 2 μA/K (-20 70 °C (-4 158 °F)); < 4 μA/K (-4020	0 °C (-404 °F))
Frequency range	field side into the control side: bandwidth with 0.5 V_{pp} sign control side into the field side: bandwidth with 0.5 V_{pp} sign	
Rise time	10 to 90 % ≤ 10 ms	
alvanic isolation		
Input/Output	basic insulation according to IEC/EN 61010-1, rated insul	lation voltage 300 V _{eff}
Input/power supply	basic insulation according to IEC/EN 61010-1, rated insul	lation voltage 300 V _{eff}
Output/power supply	reinforced insulation according to IEC/EN 61010-1, rated	insulation voltage 300 V _{ef}
Input/input	functional insulation, rated insulation voltage 50 V AC	
ndicators/settings		
Display elements	LEDs	
Labeling	space for adhesive label at the front	
irective conformity		
Electromagnetic compatibility		
Directive 2014/30/EU	EN 61326-1:2013 (industrial locations)	
onformity		
Electromagnetic compatibility	NE 21:2017 EN 61326-3-2:2018	
Degree of protection	IEC 60529	
Protection against electrical shock	UL 61010-1:2012	
mbient conditions		
Ambient temperature	-40 70 °C (-40 158 °F)	
lechanical specifications		
Degree of protection	IP20	
	screw terminals	
Connection		
Connection Mass	approx. 135 g	
	approx. 135 g 20 x 124 x 115 mm (0.8 x 4.9 x 4.5 inch) (W x H x D) , hou	ısing type B2




Technical Data		
EU-type examination certificate		BAS 00 ATEX 7240 X
Marking		 II (1)G [Ex ia Ga] IIC II (1)D [Ex ia Da] IIIC I (M1) [Ex ia Ma] I
Output		Ex ia, Ex iaD
Voltage	U_{o}	25.2 V
Current	Io	93 mA
Power	P_{o}	585.3 mW
Internal capacitance	Ci	1.05 nF
Internal inductance	L_{i}	0
Supply		
Maximum safe voltage	U_{m}	250 V _{rms} (Attention! The rated voltage can be lower.)
Input		
Maximum safe voltage	U_{m}	250 V _{rms} (Attention! The rated voltage can be lower.)
Certificate		FIDI 22 ATEX 0002X
Marking		
Galvanic isolation		
Input/Output		safe electrical isolation acc. to IEC/EN 60079-11, voltage peak value 375 V
Output/power supply		safe electrical isolation acc. to IEC/EN 60079-11, voltage peak value 375 V
Directive conformity		
Directive 2014/34/EU		EN IEC 60079-0:2018, EN 60079-11:2012, EN IEC 60079-7:2015+A1:2018
International approvals		
UL approval		E106378
Control drawing		116-0345 (cULus)
IECEx approval		
IECEx certificate		IECEx BAS 04.0014X
IECEx marking		[Ex ia Ga] IIC , [Ex ia Da] IIIC , [Ex ia Ma] I Ex ec IIC T4 Gc
General information		
Supplementary information		Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.



Assembly

Front view



Operation

Lead monitoring, input characteristics

During lead breakage (> 16 V) in the field the input resistance is > 100 k Ω , the field current is 0 mA, the input current is < 0.3 mA and the red LED is flashing. During short circuit (< 50 Ω) in the field the input resistance is > 100 k Ω , the input current is < 100 μ A, the field current is < 2.5 mA and the red LED is flashing. The voltage drop at the current input (terminals 7-, 8+ and 10-, 11+) is lower than 6 V.

Matching System Components

KFD2-EB2	Power Feed Module
UPR-03	Universal Power Rail with end caps and cover, 3 conductors, length: 2 m
UPR-03-M	Universal Power Rail with end caps and cover, 3 conductors, length: 1,6 m
UPR-03-S	Universal Power Rail with end caps and cover, 3 conductors, length: 0.8 m
K-DUCT-BU	Profile rail, wiring comb field side, blue
K-DUCT-BU-UPR-03	Profile rail with UPR-03- * insert, 3 conductors, wiring comb field side, blue

Accessories

KF-ST-5GN	Terminal block for KF modules, 3-pin screw terminal, green

Accessories					
	KF-ST-5BU	Terminal block for KF modules, 3-pin screw terminal, blue			
*	KF-CP	Red coding pins, packaging unit: 20 x 6			

5PEPPERL+FUCHS