

# OMT300-R201-2EP-IO-0,3M-V1-L



- Medium design with versatile mounting options
- Space-saving distance sensors in small standardized design
- Multi Pixel Technology (MPT) exact and precise signal evaluation
- IO-Link interface for service and process data

Distance sensor

# UK 🙈 😧 IO-Link


#### **Function**


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design - from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation tasks.

The entire series enables sensors to communicate via IO-Link. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor. Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.



### **Dimensions**





# **Technical Data**

| General specifications               |  |
|--------------------------------------|--|
| Measurement range                    | 100 300 mm   |
| Reference target                     | standard white, 100 mm x 100 mm                      |
| Light source                         | laser diode  |
| Light type                           | modulated visible red light                          |
| Laser nominal ratings                |  |
| Note                                 | LASER LIGHT , DO NOT STARE INTO BEAM                 |
| Laser class                          | 1  |
| Wave length                          | 680 nm   |
| Beam divergence                      | > 5 mrad, d63 < 2,8 mm in the range of 350 mm 800 mm |
| Pulse length                         | 5.5 μs   |
| Repetition rate                      | approx. 2.4 kHz                                      |
| max. pulse energy                    | <40 nJ   |
| Angle deviation                      | max. +/- 1.5 °                                       |
| Diameter of the light spot           | approx. 3 mm at a distance of 300 mm                 |
| Opening angle                        | approx. 0.3 °  |
| Ambient light limit                  | EN 60947-5-2 : 45000 Lux                             |
| Resolution                           | 0.1 mm   |
| Functional safety related parameters |  |
| MTTF <sub>d</sub>                    | 560 a  |
| Mission Time (T <sub>M</sub> )       | 20 a   |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2023-01-16 Date of issue: 2023-01-16 Filename: 295670-100354\_eng.pdf

**Technical Data** 

# OMT300-R201-2EP-IO-0,3M-V1-L

| Technical Data               |                |   |
|------------------------------|----------------|---|
| Diagnostic Coverage (DC)     |                | 0 %   |
| Indicators/operating means   |                |   |
| Operation indicator          |                | LED green:  |
|                              |                | constantly on - power on<br>flashing (4Hz) - short circuit<br>flashing with short break (1 Hz) - IO-Link mode                                   |
| Function indicator           |                | LED yellow:<br>constantly on - switch output active<br>constantly off - switch output inactive  |
| Control elements             |                | Teach-In key  |
| Control elements             |                | 5-step rotary switch for operating modes selection  |
| Electrical specifications    |                |   |
| Operating voltage            | UB             | 10 30 V DC  |
| Ripple                       |                | max. 10 %   |
| No-load supply current       | I <sub>0</sub> | < 16 mA at 24 V supply voltage  |
| Protection class             |                | III   |
| Interface                    |                |   |
| Interface type               |                | IO-Link (via $C/Q = pin 4$ )  |
| IO-Link revision             |                | 1.1   |
| Device profile               |                | Identification and diagnosis<br>Smart Sensor type 0/type 3.3  |
| Device ID                    |                | 0x11191A (1120538)  |
| Transfer rate                |                | COM2 (38.4 kBit/s)  |
| Min. cycle time              |                | 3 ms  |
| Process data width           |                | Process data input 4 byte<br>Process data output 2 bits   |
| SIO mode support             |                | yes   |
| Compatible master port type  |                | A   |
| Output                       |                |   |
| Switching type               |                | The default setting is:<br>C/Q - Pin4: NPN normally open, PNP normally closed, IO-Link<br>Q2 - Pin2: NPN normally-open, PNP normally-closed     |
| Signal output                |                | 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected  |
| Switching voltage            |                | max. 30 V DC  |
| Switching current            |                | max. 100 mA , resistive load  |
| Usage category               |                | DC-12 and DC-13   |
| Voltage drop                 | U <sub>d</sub> | ≤ 1.5 V DC  |
| Response time                |                | 2 ms  |
| Conformity                   |                |   |
| Communication interface      |                | IEC 61131-9   |
| Product standard             |                | EN 60947-5-2  |
| Laser safety                 |                | EN 60825-1:2014   |
| Measurement accuracy         |                |   |
| Temperature drift            |                | 0.05 %/K  |
| Warm up time                 |                | 5 min   |
| Repeat accuracy              |                | < 0.5 %   |
| Linearity error              |                | 0.5 %   |
| Approvals and certificates   |                |   |
| UL approval                  |                | E87056, cULus Listed, class 2 power supply, type rating 1   |
| CCC approval<br>FDA approval |                | CCC approval / marking not required for products rated ≤36 V<br>IEC 60825-1:2014 Complies with 21 CFR 1040.10 and 1040.11 except for deviations |
| Ambient conditions           |                | pursuant to Laser Notice No. 50, dated June 24, 2007  |
| Ambient conditions           |                |   |
| Ambient temperature          |                | 10 60 °C (50 140 °F)  |
| Storage temperature          |                | -40 70 °C (-40 158 °F)  |
| Mechanical specifications    |                |   |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

# OMT300-R201-2EP-IO-0,3M-V1-L

| Tec | hh | 02  |  |
|-----|----|-----|--|
|     |    | Gal |  |
|     |    |     |  |

| Housing width        | 15 mm  |
|----------------------|--|
| Housing height       | 61.7 mm  |
| Housing depth        | 41.7 mm  |
| Degree of protection | IP67 / IP69 / IP69K                              |
| Connection           | 300 mm fixed cable with M12 x 1, 4-pin connector |
| Material             |  |
| Housing              | PC (Polycarbonate)                               |
| Optical face         | РММА   |
| Mass                 | approx. 55 g                                     |
| Cable length         | 0.3 m  |

# Connection



# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2

| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue)  |
| 4 | BK | (black) |


 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Gr

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

4

## Assembly





| 1 | Mode rotary switch          |    |
|---|-----------------------------|----|
| 2 | Teach-in button             |    |
| 3 | Switching output display Q2 | YE |
| 4 | Switching output display Q1 | YE |
| 5 | Operating indicator         | GN |

| Q1B | Switching output 1/switch point B |
|-----|-----------------------------------|
| Q1A | Switching output 1/switch point A |
| Q2A | Switching output 2/switch point A |
| Q2B | Switching output 2/switch point B |
| 0   | Keylock                           |

| ₩        | LASER<br>1 |
|----------|------------|
| IEC 6082 | 25-1:2014  |

# Accessories

| ø /        | V1-G-2M-PUR          | Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey       |
|------------|----------------------|---|
| <b>«</b> / | V1-W-2M-PUR          | Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey         |
|            | OMH-RL31-02          | Mounting bracket narrow   |
|            | OMH-RL31-03          | Mounting bracket narrow   |
| F.A.       | OMH-RL31-04          | Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm                     |
|            | OMH-RL31-07          | Mounting bracket including adjustment   |
| 17         | OMH-R20x-Quick-Mount | Quick mounting accessory  |
| In         | ICE2-8IOL-G65L-V1D   | EtherNet/IP IO-Link master with 8 inputs/outputs                              |
| In         | ICE3-8IOL-G65L-V1D   | PROFINET IO IO-Link master with 8 inputs/outputs                              |
|            | ICE2-8IOL-K45S-RJ45  | EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal    |
|            | ICE3-8IOL-K45P-RJ45  | PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals |
|            | ICE3-8IOL-K45S-RJ45  | PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal    |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

| Accessori | 00 |
|-----------|----|
| ACCESSON  | 69 |

| <br>IO-Link-Master02-USB | IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection |
|--------------------------|--|
| ICE1-8IOL-G30L-V1D       | Ethernet IO-Link module with 8 inputs/outputs  |
| ICE1-8IOL-G60L-V1D       | Ethernet IO-Link module with 8 inputs/outputs  |
| ICE2-8IOL-K45P-RJ45      | EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors                               |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

6

# Commissioning

#### Teach-In (TI)

Use the rotary switch for switching signal Q1 or Q2 to select the relevant switching threshold A and/or B to teach in.


The yellow LEDs indicate the current state of the selected output.

To teach in a switching threshold, press and hold the "TI" button for approximately 1 s, until the yellow and green LEDs flash in phase. Teach-in starts when the "TI" button is released.


- Teach-in successful: the yellow and green LEDs flash alternately at 2.5 Hz.
- Teach-in unsuccessful: the yellow and green LEDs quickly flash alternately at 8 Hz.
   After an unsuccessful Teach-in, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Set switching mode: you can define different switching modes by teaching in the relevant distance data for switching thresholds A and B.

1. Single point mode:



2. Window mode:



Teach in switching thresholds: you can teach in or overwrite a taught-in switching threshold at any time. To do this, press the "TI" button again.

Reset a value: you can reset a taught-in value. To do this, press the "TI" button for > 4 s, until the yellow and green LEDs go out. The reset process itself starts when the "TI" button is released.

• Reset successful: the yellow and green LEDs flash alternately at 2.5 Hz.

### **Resetting to Factory Settings**

To revert back to factory settings, press the "TI" button for > 10 s with the rotary switch set to position "O," until the yellow and green LEDs go out at the same time. The reset process itself starts when the "TI" button is released.

Reset to factory settings successful: the yellow and green LEDs light up at the same time. The sensor then continues to
operate with factory settings.

#### OMT

- Factory setting for switching signal Q1:
- Switching signal is high active, window mode
- Factory setting for switching signal Q2: Switching signal is high active, window mode

## Configuration

### Setting different operating modes via the IO-Link interface

The devices are equipped with an IO-Link interface as standard for diagnostics and parameterization tasks to ensure optimum adjustment of the sensors to the relevant application.

### Single point mode operating mode (one switch point):

- "Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.
  - "The switch point corresponds exactly to the set point.

active detection range



Refer to "General Notes Relating to Pepperl+Fuchs Product Information

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

### Window mode operating mode (two switch points):

- Detection of objects irrespective of type and color in a defined detection range. Reliable detection when object leaves the detection range.
- Window mode with two switch points.

| а                      | active detection range |
|------------------------|------------------------|
|                        |                        |
| Foreground suppression | Background suppression |

#### Center window mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Sets a defined window around a given object. Objects outside this window are not detected.
- Window mode with one switch point.

| active                 | e detection range      |
|------------------------|------------------------|
|                        |                        |
| Foreground suppression | Background suppression |

#### Two point mode operating mode (hysteresis operating mode):

• Detection of objects irrespective of type and color between a defined switch-on and switch-off point.

|        | active detection range |        |
|--------|------------------------|--------|
|        |                        |        |
|        |                        | Output |
| Output | Hysteresis             | Culpur |

Inactive operating mode:

• Evaluation of switching signals is deactivated.

The associated IODD device description file can be found in the download area at www.pepperl-fuchs.com.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



8