

Distance sensor OMT300-R200-2EP-IO-V1



- Medium design with versatile mounting options
- Space-saving distance sensors in small standardized design
- Multi Pixel Technology (MPT) exact and precise signal
- IO-Link interface for service and process data

Distance sensor











Function


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design – from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.

Dimensions






Technical Data

General specifications 100 ... 300 mm Measurement range Reference target standard white, 100 mm x 100 mm Light source Light type modulated visible red light LED risk group labelling exempt group Angle deviation max. \pm /- 1.5 $^{\circ}$ Diameter of the light spot approx. 8 mm at a distance of 300 mm Opening angle 1.8 9 EN 60947-5-2: 45000 Lux Ambient light limit Resolution 0.1 mm Functional safety related parameters 600 a MTTF_d Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means LED green: Operation indicator constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator constantly on - switch output active constantly off - switch output inactive Control elements Teach-In key Control elements 5-step rotary switch for operating modes selection Electrical specifications Operating voltage U_{B} 10 ... 30 V DC max. 10 % Ripple No-load supply current I_0 < 25 mA at 24 V supply voltage Protection class Interface Interface type IO-Link (via C/Q = pin 4) IO-Link revision 1.1 Identification and diagnosis Smart Sensor type 0/type 3.3 Device profile Device ID 0x111904 (1120516) COM2 (38.4 kBit/s) Transfer rate Min. cycle time 3 ms Process data width Process data input 4 byte Process data output 2 bits SIO mode support yes Α Compatible master port type Output Switching type The default setting is: C/Q - Pin4: NPN normally open, PNP normally closed, IO-Link Q2 - Pin2: NPN normally-open, PNP normally-closed Signal output 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load DC-12 and DC-13 Usage category Voltage drop U_{d} ≤ 1.5 V DC Response time 2 ms, see table 1 Conformity Communication interface IEC 61131-9 Product standard EN 60947-5-2

Measurement accuracy

Technical Data Temperature drift 0.05 %/K Warm up time 5 min Repeat accuracy < 0.5 %, see table 1 Linearity error 0.5 % Approvals and certificates **UL** approval E87056, cULus Listed, class 2 power supply, type rating 1 CCC approval / marking not required for products rated ≤36 V CCC approval **Ambient conditions** 10 ... 60 °C (50 ... 140 °F) Ambient temperature -40 ... 70 °C (-40 ... 158 °F) Storage temperature **Mechanical specifications** Housing width 15 mm 50.6 mm Housing height Housing depth 41.7 mm Degree of protection IP67 / IP69 / IP69K Connection 4-pin, M12 x 1 connector, 90° rotatable Material Housing PC (Polycarbonate) Optical face **PMMA** Mass approx. 37 g

Connection




Connection Assignment




Wire colors in accordance with EN 60947-5-2

1 BN 2 WH 3 BU 4 BK	(brown) (white) (blue) (black)
---------------------	---



1	Mode rotary switch	
2	Teach-in button	
3	Switching output display Q2	YE
4	Switching output display Q1	YE
5	Operating indicator	GN



Q1B	Switching output 1/switch point B
Q1A	Switching output 1/switch point A
Q2A	Switching output 2/switch point A
Q2B	Switching output 2/switch point B
0	Keylock

Accessories

	OMH-MLV12-HWK	Mounting bracket for series MLV12 sensors
	OMH-R200-01	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
17	OMH-R20x-Quick-Mount	Quick mounting accessory

Men.	OMH-MLV12-HWG	Mounting bracket for series MLV12 sensors

ICE3-8IOL-K45S-RJ45

ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs

ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs

40		
	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal

ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals

IO-I ink-Master02-IISB	IO-Link master, supply via LISB port or separate power supply. LED indicators, M12 plug for separate

IO-LITIK-Waster02	-036	connection

PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal

IOE4 OLOL OCCI VAD		

ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs				

ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs				

ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors

V1-G-2M-PHR	Female cordset single-ended M12 straight A-coded 4-nin PLIB cable gray	

Accessories



V1-W-2M-PUR

Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey

Technical Features

Table 1: Information on Measured Value Filters

Filter	1-way	2-way	4-way	16-way	64-way	256-way
Response time (ms)	2	4	8	32	128	512

Repeatability (%) < 0.5 %

Commissioning

Teach-In (TI)

Use the rotary switch for switching signal Q1 or Q2 to select the relevant switching threshold A and/or B to teach in.


· The yellow LEDs indicate the current state of the selected output.

To teach in a switching threshold, press and hold the "TI" button for approximately 1 s, until the yellow and green LEDs flash in phase. Teach-in starts when the "TI" button is released.


- Teach-in successful: the yellow and green LEDs flash alternately at 2.5 Hz.
- Teach-in unsuccessful: the yellow and green LEDs quickly flash alternately at 8 Hz.
 After an unsuccessful Teach-in, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Set switching mode: you can define different switching modes by teaching in the relevant distance data for switching thresholds A and B.

1. Single point mode:



2. Window mode:



Teach in switching thresholds: you can teach in or overwrite a taught-in switching threshold at any time. To do this, press the "TI" button again.

Reset a value: you can reset a taught-in value. To do this, press the "TI" button for > 4 s, until the yellow and green LEDs go out. The reset process itself starts when the "TI" button is released.

Reset successful: the yellow and green LEDs flash alternately at 2.5 Hz.

Resetting to Factory Settings

To revert back to factory settings, press the "TI" button for > 10 s with the rotary switch set to position "O," until the yellow and green LEDs go out at the same time. The reset process itself starts when the "TI" button is released.

Reset to factory settings successful: the yellow and green LEDs light up at the same time. The sensor then continues to
operate with factory settings.

OMT

- Factory setting for switching signal Q1:
 Switching signal is high active, window mode
- Factory setting for switching signal Q2:
 Switching signal is high active, window mode

Configuration

Setting different operating modes via the IO-Link interface

The devices are equipped with an IO-Link interface as standard for diagnostics and parameterization tasks to ensure optimum

Distance sensor

adjustment of the sensors to the relevant application.

Single point mode operating mode (one switch point):

- "Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.
- "The switch point corresponds exactly to the set point.

active detection range

Background suppression


Window mode operating mode (two switch points):

- Detection of objects irrespective of type and color in a defined detection range. Reliable detection when object leaves the
 detection range.
- · Window mode with two switch points.




Center window mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Sets a defined window around a given object.
 Objects outside this window are not detected.
- · Window mode with one switch point.



Two point mode operating mode (hysteresis operating mode):

· Detection of objects irrespective of type and color between a defined switch-on and switch-off point.



Inactive operating mode:

Evaluation of switching signals is deactivated.

The associated IODD device description file can be found in the download area at www.pepperl-fuchs.com.