

Retroreflective sensor with polarization



OBR15M-R200-A5-IO-V1

- Medium design with versatile mounting options
- Extended temperature range -40 °C ... 60 °C
- High degree of protection IP69K
- IO-Link interface for service and process data

Retroreflective sensor with polarization filter











Function


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design – from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.

Dimensions





Technical Data

General specifications 0 ... 15 m Effective detection range Reflector distance 0.02 ... 15 m Threshold detection range 18.5 m Reference target H85-2 reflector LED Light source Light type modulated visible red light LED risk group labelling exempt group Polarization filter Diameter of the light spot approx. 520 mm at a distance of 15 m Opening angle Ambient light limit EN 60947-5-2: 60000 Lux Functional safety related parameters MTTF_d 724 a Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode **Function indicator** Yellow I FD: Permanently lit - light path clear Permanently off - object detected Flashing (4 Hz) - insufficient operating reserve Control elements Light-on/dark-on changeover switch Control elements sensitivity adjustment **Electrical specifications** 10 ... 30 V 18 ... 30 V (IO-Link) Operating voltage U_{B} Ripple max. 10 % No-load supply current < 18 mA (at 24 V) I_0 Protection class Ш Interface IO-Link Interface type IO-Link revision Identification and Diagnosis - I&D Smart Sensor - SSP 2.4 Device profile Process data Input 2 Bit - switching signal 1 Bit - stability alarm 1 Bit Output 2 Bit - Emitter deactivation 1 Bit - evaluation freeze 1 Bit Vendor ID 1 (0x0001) Device ID 1118754 (0x111222) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms SIO mode support ves Compatible master port type Class A Output The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: PNP normally open / dark-on, IO-Link /Q - Pin2: PNP normally closed / light-on Switching type Signal output 2 PNP outputs, short-circuit-proof, reverse polarity protection, surge-proof max. 30 V DC Switching voltage max. 100 mA, resistive load Switching current DC-12 and DC-13 Usage category


Voltage drop

 $U_{\text{d}} \\$

≤ 1.5 V DC

Technical Data		
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Communication interface		IEC 61131-9 / IO-Link V1.1.2
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		E87056, cULus Listed, class 2 power supply, type rating 1
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-40 60 °C (-40 140 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		15 mm
Housing height		50.6 mm
Housing depth		41.7 mm
Degree of protection		IP67 / IP69 / IP69K
Connection		4-pin, M12 x 1 connector, 90° rotatable
Material		
Housing		PC (Polycarbonate)
Optical face		PMMA
Mass		approx. 37 g

Connection



Connection Assignment





Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

1	Sensitivity adjustment	
2	Light-on / dark-on changeover switch	
3	Operating indicator / dark on	GN
4	Signal indicator	
5	Operating indicator / light on	GN

Characteristic Curve





Commissioning

www.pepperl-fuchs.com

To unlock the adjustment functions turn the sensing range / sensitivity adjuster for more than 180 degrees.

Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity. Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

fa-info@us.pepperl-fuchs.com

Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.



Commissioning

If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on / dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

Restore Factory Settings
Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range / sensitivity adjuster for more than 180 degrees.

Accessories

2	IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap
	REF-VR10	Reflector, rectangular 60 mm x 19 mm, mounting holes
	OFR-100/100	Reflective tape 100 mm x 100 mm
Her	OMH-MLV12-HWG	Mounting bracket for series MLV12 sensors
HEAD (1) HAD //	OMH-R200-01	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-MLV12-HWK	Mounting bracket for series MLV12 sensors
77	OMH-R20x-Quick-Mount	Quick mounting accessory
6/	V1-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey
6/	V1-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey