

Distance sensor

VDM28-15-L1-IO/73c/110/122



- Distance measurement using object
- Measuring method PRT (Pulse Ranging Technology)
- IO-Link interface for service and process data
- Analog output 0/4 mA ... 20 mA
- Accurate, clear, and reproducible measuring results
- Laser class 1, eyesafe

Universal distance sensor, measurement to object, IO-Link interface, measuring method PRT, 15 m detection range, red laser light, laser class 1, push-pull output, analog output, M12 plug














Function

The VDM28 distance measurement device employs Pulse Ranging Technology (PRT). It has a repeat accuracy of 5 mm with an operating range of 0.2 ... 15 m and an absolute accuracy of 25 mm.

The compact housing of the Series 28 photoelectric sensors, with dimensions of 88 mm (height), 26 mm (width) and 54 mm (depth), make it the smallest device available in its class.

Dimensions



Technical Data

General specifications				
Measurement range	0.2 15 m			
Reference target	Kodak white (90%)			
Light source	laser diode typ. service life 85,000 h at Ta = +25 °C			


Release date: 2024-03-18 Date of issue: 2024-03-18 Filename: 297897_eng.pdf

Light type modulated visible red light	
-9 7/2	
Laser nominal ratings	
Note LASER LIGHT , DO NOT STARE INTO BEAM	
Laser class 1	
Wave length 660 nm	
Beam divergence < 1.5 mrad	
Pulse length approx. 4 ns	
Repetition rate 250 kHz	
max. pulse energy < 1.5 nJ	
Angle deviation max. ± 2°	
Measuring method Pulse Ranging Technology (PRT)	
Diameter of the light spot < 15 mm at a distance of 15 m at 20 °C	
Ambient light limit 50000 Lux	
ū , , , , , , , , , , , , , , , , , , ,	
Functional safety related parameters	
MTTF _d 200 a	
Mission Time (T _M) 10 a	
Diagnostic Coverage (DC) 0 %	
ndicators/operating means	
Operation indicator LED green	
Function indicator 2 LEDs yellow for switching state	
Teach-In indicator Teach-In: LED green/yellow equiphase flashing; 2.5 Hz Teach Error: LED green/yellow non equiphase flashing; 8.0	
Control elements 5-step rotary switch for operating modes selection (thresh modes)	old setting and operating
Control elements Switch for setting the threshold values	
Electrical specifications	
Operating voltage U _B 10 30 V DC / when operating in IO-Link mode: 18 30	V
Ripple 10 % within the supply tolerance	
No-load supply current $I_0 \le 70 \text{ mA} / 24 \text{ V DC}$	
Time delay before availability t _v 1.5 s	
nterface	
Interface type IO-Link	
Protocol IO-Link V1.0	
Cycle time min. 2.3 ms	
Mode COM2 (38.4 kBit/s)	
Process data width 16 bit	
SIO mode support yes	
Output	
Signal output Push-pull output, short-circuit protected, reverse polarity p	protected
Switching voltage max. 30 V DC	
Switching current max. 100 mA	
	ed
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected Switching frequency f 50 Hz Response time 10 ms	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected Switching frequency f 50 Hz Response time 10 ms	
Measurement output Switching frequency Response time 1 analog output 4 20 mA, short-circuit/overload protected from 50 Hz 10 ms Conformity	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected Switching frequency f 50 Hz Response time 10 ms Conformity Electromagnetic compatibility EN 61000-6-2, EN 61000-6-4 Laser safety IEC 60825-1:2007	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected Switching frequency f 50 Hz Response time 10 ms Conformity Electromagnetic compatibility EN 61000-6-2, EN 61000-6-4 Laser safety IEC 60825-1:2007	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected Switching frequency f 50 Hz Response time 10 ms Conformity Electromagnetic compatibility EN 61000-6-2, EN 61000-6-4 Laser safety Measurement accuracy	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected Switching frequency f 50 Hz Response time 10 ms Conformity Electromagnetic compatibility EN 61000-6-2, EN 61000-6-4 Laser safety IEC 60825-1:2007 Measurement accuracy Absolute accuracy ± 25 mm Repeat accuracy < 5 mm	
Measurement output 1 analog output 4 20 mA, short-circuit/overload protected Switching frequency f 50 Hz Response time 10 ms Conformity Electromagnetic compatibility EN 61000-6-2, EN 61000-6-4 Laser safety IEC 60825-1:2007 Measurement accuracy Absolute accuracy ± 25 mm	

Technical Data				
CCC approval	CCC approval / marking not required for products rated ≤36 V			
FDA approval	IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007			
Ambient conditions				
Ambient temperature	-30 55 °C (-22 131 °F)			
Storage temperature	-30 70 °C (-22 158 °F)			
Mechanical specifications				
Degree of protection	IP67			
Connection	4-pin, M12 x 1 connector			
Material				
Housing	Plastic ABS			
Optical face	PMMA			
Mass	90 g			
Dimensions				
Height	88 mm			
Width	25.8 mm			
Depth	54.6 mm			

Connection Assignment

Option:



- O = Light on
- = Dark on

Connection Assignment





Connection Assignment

Wire colors in accordance with EN 60947-5-2

BN (brown) 2 WH (white) 3 BU (blue) 4 BK (black)


Assembly





1	Operating display	green	
2	Signal display	yellow	
3	TEACH-IN button		
4	Mode rotary switch		
5	Laser output		

Characteristic Curve



Application



Safety Information

CLASS 1 LASER PRODUCT

IEC 60825-1: 2007 certified.

Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Safety Information

Laser Class 1 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people! Maintenance and repairs should only be carried out by authorized service personnel! Attach the device so that the warning is clearly visible and readable.

Attach the device so that the warning is clearly visible and readable.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

You can use the rotary switch to select the relevant switching threshold A and/or B for teaching in for switching output Q1. The yellow LEDs indicate the current state of the selected output.


To store a switching threshold (distance measured value), press and hold the "SET" button until the yellow and green LEDs flash in phase (approx. 2 s). Teach-In starts when the "SET" button is released.

Successful Teach-In is indicated by alternating flashing (2.5 Hz) of the yellow and green LEDs.

An unsuccessful Teach-In is indicated by rapidly alternating flashing (8 Hz) of the yellow and green LEDs.

After an unsuccessful Teach-In, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Different switching modes can be defined by teaching in the relevant distance measured values for the switching thresholds A and B:



Every taught-in switching threshold can be retaught (overwritten) by pressing the SET button again.

Pressing and holding the "SET" button for > 5 s completely deletes the taught-in value. The yellow and green LEDs go out simultaneously to indicate that this procedure has been completed.


Minimum and maximum values for the analog output Q2 are taught in in the same way as those for the switching output:

The following values apply: A = 4 mA


$$B = 20 \text{ mA}$$


This provides three different options for operation:

A < B -> rising slope



A > B -> falling slope





Reset to default settings:

Factory setting for switching output Q1:

Switching output inactive

Factory setting for analog output Q2:

 $A = 200 \, \text{mm}$

Release date: 2024-03-18 Date of issue: 2024-03-18 Filename: 297897_eng.pdf

B = 5000 mm



Value B cannot be deleted

The "zero start point" operating mode can be obtained by deleting value A

- Set the rotary switch to the "RUN" position
- Press and hold the "SET" button until the yellow and green LEDs stop flashing in phase (approx. 10 s)
- When the green LED lights up continuously, the procedure is complete.

Error messages:

Short circuit: In the event of a short circuit at the sensor output, the green LED flashes with a frequency of approx. 4 Hz.

• Teach error:In the event of a teach error, the yellow and green LEDs flash alternately with a frequency of approx. 8 Hz.

0

Note!

The difference in the taught-in distance measured values for switching thresholds A and B must be greater than 20 mm.

If the difference in the taught-in measured values is the same as or smaller than the set switching hysteresis, the sensor will visually signal an unsuccessful Teach-In. The last distance measured value that was taught in will not be adopted by the sensor.

Select a new distance measured value for switching threshold A or B with a greater difference between the switching thresholds.

Teach in this distance measured value on the sensor again.

Switching threshold A can be deleted or set to a value of zero.

(E.g., when setting the "zero start point" curve).

However, switching threshold B can neither be deleted nor set to a value of zero.