

Thru-beam sensor (pair) OBE25M-R201-SEP-IO-0,3M-V3



- Medium design with versatile mounting options
- IO-Link interface for service and process data
- Various frequencies for avoiding mutual interference (cross-talk immunity)
- Extended temperature range -40 °C ... 60 °Ċ
- High degree of protection IP69K


Function

The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design - from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation tasks.

The entire series enables sensors to communicate via IO-Link. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor. Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.



Dimensions



Technical Data

System components			
Emitter	OBE25M-R201-S-IO-0,3M-V3		
Receiver	OBE25M-R201-EP-IO-0,3M-V3		
General specifications			
Effective detection range	0 25 m		
Threshold detection range	33 m		
Light source	LED		
Light type	modulated visible red light		
LED risk group labelling	exempt group		
Alignment aid	LED red (in receiver lens) illuminated constantly: beam is interrupted, flashes: reaching switching point, off: sufficient stability control		
Diameter of the light spot	approx. 850 mm at a distance of 25 m		
Opening angle	approx. 2 °		
Ambient light limit	EN 60947-5-2 : 40000 Lux		
Functional safety related parameters			
MTTF _d	462 a		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com

Mission Time (T _M) 20 a Diagnostic Coverage (DC) 60 % Indicators/operating means 60 % Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator Yellow LED: Permanently lit - light path clear	
Diagnostic Coverage (DC) 60 % Indicators/operating means EED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator Yellow LED: Permanently lit - light path clear	
Indicators/operating means LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator Yellow LED: Permanently lit - light path clear	
Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator Yellow LED: Permanently lit - light path clear	
Permanently lit - light path clear	
Permanently off - ŏbject detected Flashing (4 Hz) - insufficient operating reserve	
Control elements Receiver: light/dark switch	
Control elements Receiver: sensitivity adjustment	
Electrical specifications	
Operating voltage U _B 10 30 V DC	
Ripple max. 10 %	
No-load supply current I₀ Emitter: ≤ 15 mA Receiver: ≤ 15 mA at 24 V Operating voltage	
Protection class III	
Interface	
Interface type IO-Link (via C/Q = pin 4)	
IO-Link revision 1.1	
Device profile Identification and diagnosis Smart Sensor: Receiver: type 2.4 Emitter: -	
Device ID Emitter: 0x111411 (1119249) Receiver: 0x111311 (1118993)	
Transfer rate COM2 (38.4 kBit/s)	
Min. cycle time 2.3 ms	
Process data width Emitter: Process data input: 0 bit Process data output: 1 bit Receiver: Process data input: 2 bit Process data output: 2 bit	
SIO mode support yes	
Compatible master port type A	
Input	
Test input emitter deactivation at +U _B	
Output	
Switching type The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / dark-on, PNP normally closed / light-on, IO	O-Link
Signal output 1 push-pull (4 in 1) output, short-circuit protected, reverse polarity protected overvoltage protected	d,
Switching voltage max. 30 V DC	
Switching current max. 100 mA, resistive load	
Usage category DC-12 and DC-13	
Voltage drop $U_d \leq 1.5 \text{ V DC}$	
Switching frequency f 1000 Hz	
Response time 0.5 ms	
Conformity	
Communication interface IEC 61131-9	
Product standard EN 60947-5-2	
Approvals and certificates	
UL approval E87056 , cULus Listed , class 2 power supply , type rating 1	
CCC approval / marking not required for products rated ≤36 V	
Ambient conditions	


Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Technical Data

Storage temperature	-40 70 °C (-40 158 °F)		
Mechanical specifications			
Housing width	15 mm		
Housing height	61.7 mm		
Housing depth	41.7 mm		
Degree of protection	IP67 / IP69 / IP69K		
Connection	300 mm fixed cable with M8 x 1, 3-pin connector		
Material			
Housing	PC (Polycarbonate)		
Optical face	PMMA		
Mass	Emitter: approx. 51 g receiver: approx. 51 g		
Cable length	0.3 m		

Connection





Connection Assignment



Wire colors in accordance with EN 60947-5-2

BN BU BK	(brown) (blue) (black)


1 3 4

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

4

Assembly


Emitter



Operating indicator


1

Receiver



1	Sensitivity adjustment	
2	Light-on / dark-on changeover switch	
3	Operating indicator / dark on	GN
4	Signal indicator	YE
5	Operating indicator / light on	GN

Characteristic Curve



Excess gain 10000 1000 100 10 10 15 20 25 ċ 5 30 35 Distance X [m]

Commissioning

Release date: 2023-01-16 Date of issue: 2023-01-16 Filename: 301104_eng.pdf

To unlock the adjustment functions turn the sensing range / sensitivity adjuster for more than 180 degrees.

Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity. Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Commissioning

If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on / dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

Restore Factory Settings Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings. After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range / sensitivity adjuster for more than 180 degrees.

Accessories				
	OMH-RL31-02	Mounting bracket narrow		
I and	OMH-RL31-03	Mounting bracket narrow		
F. <u>e</u> .	OMH-RL31-04	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm		
	OMH-RL31-07	Mounting bracket including adjustment		
	OMH-RL31-08	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm		
17	OMH-R20x-Quick-Mount	Quick mounting accessory		
In	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs		
	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs		
	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal		
	ICE3-8IOL-K45P-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals		
	ICE3-8IOL-K45S-RJ45	PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal		
The second se	IO-Link-Master02-USB	IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection		
	ICE1-8IOL-G30L-V1D	Ethernet IO-Link module with 8 inputs/outputs		
	ICE1-8IOL-G60L-V1D	Ethernet IO-Link module with 8 inputs/outputs		
6 /	ICE2-8IOL-K45P-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors		
6/	V3-GM-2M-PUR	Female cordset single-ended M8 straight A-coded, 3-pin, PUR cable grey		
6/	V3-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

