

Distance sensor OMT550-R201-2EP-IO



- Medium design with versatile mounting options
- Space-saving distance sensors in small standardized design
- Multi Pixel Technology (MPT) exact and precise signal
- IO-Link interface for service and process data

Distance sensor











Function


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design – from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.

Dimensions




Technical Data

General specifications	
Measurement range	100 550 mm
Reference target	standard white, 100 mm x 100 mm
Light source	LED
Light type	modulated visible red light
LED risk group labelling	exempt group
Angle deviation	max. +/- 1.5 °
Diameter of the light spot	approx. 20 mm at a distance of 550 mm
Opening angle	2.5 °
Ambient light limit	EN 60947-5-2 : 45000 Lux
Resolution	0.1 mm
Functional safety related parameters	
MTTF _d	600 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %
Indicators/operating means	
Operation indicator	LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode
Function indicator	LED yellow: constantly on - switch output active constantly off - switch output inactive

Release date: 2023-01-16 Date of issue: 2023-01-16 Filename: 295670-100176_eng.pdf


Technical Data						
Control elements		Teach-In key				
Control elements		5-step rotary switch for operating modes selection				
Electrical specifications		o dop rounly onnormer operating measures of solution				
Operating voltage	U_{B}	10 30 V DC				
Ripple	0.0	max. 10 %				
No-load supply current	I ₀	< 25 mA at 24 V supply voltage				
Protection class	10	III				
Interface						
Interface type		IO-Link (via C/Q = pin 4)				
IO-Link revision		1.1				
Device profile		Identification and diagnosis Smart Sensor type 0/type 3.3				
Device ID		0x111911 (1120529)				
Transfer rate		COM2 (38.4 kBit/s)				
Min. cycle time		3 ms				
Process data width		Process data input 4 byte Process data output 2 bits				
SIO mode support		yes				
Compatible master port type		A				
Output						
Switching type		The default setting is: C/Q - BK: NPN normally open, PNP normally closed, IO-Link Q2 - WH: NPN normally open, PNP normally closed				
Signal output		2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected				
Switching voltage		max. 30 V DC				
Switching current		max. 100 mA , resistive load				
Usage category		DC-12 and DC-13				
Voltage drop	U_{d}	≤ 1.5 V DC				
Response time		2 ms , see table 1				
Conformity						
Communication interface		IEC 61131-9				
Product standard		EN 60947-5-2				
Measurement accuracy						
Temperature drift		0.05 %/K				
Warm up time		5 min				
Repeat accuracy		\leq 1 % , see table 1				
Linearity error		0.75 %				
Approvals and certificates						
UL approval		E87056, cULus Listed, class 2 power supply, type rating 1				
CCC approval		CCC approval / marking not required for products rated ≤36 V				
Ambient conditions						
Ambient temperature		10 60 °C (50 140 °F)				
Storage temperature		-40 70 °C (-40 158 °F)				
Mechanical specifications						
Housing width		15 mm				
Housing height		61.7 mm				
Housing depth		41.7 mm				
Degree of protection		IP67 / IP69 / IP69K				
Connection		2 m fixed cable				
Material						
Housing		PC (Polycarbonate)				
Optical face		PMMA				
Mass		approx. 73 g				




Technical Data

Cable length 2 m


Connection



Assembly



1	Mode rotary switch	
2	Teach-in button	
3	Switching output display Q2	YE
4	Switching output display Q1	YE
5	Operating indicator	GN



_	
Q1B	Switching output 1/switch point B
Q1A	Switching output 1/switch point A
Q2A	Switching output 2/switch point A
Q2B	Switching output 2/switch point B
0	Keylock

Accessories

	OMH-RL31-02	Mounting bracket narrow
	OMH-RL31-03	Mounting bracket narrow
	OMH-RL31-04	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-RL31-07	Mounting bracket including adjustment
7	OMH-R20x-Quick-Mount	Quick mounting accessory
11.	ICE2-8IOL-G65L-V1D	EtherNet/IP IO-Link master with 8 inputs/outputs
110	ICE3-8IOL-G65L-V1D	PROFINET IO IO-Link master with 8 inputs/outputs
9	ICE2-8IOL-K45S-RJ45	EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal

Accessories ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for sensor connection ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors

www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

Technical Features

Table 1: Information on Measured Value Filters

Measured value filter							
Filter	1-way	2-way	4-way	16-way	64-way	256-way	
Response time (ms)	2	4	8	32	128	512	
Repeatability (%)		< 1 %					

Commissioning

Teach-In (TI)

Use the rotary switch for switching signal Q1 or Q2 to select the relevant switching threshold A and/or B to teach in.


• The yellow LEDs indicate the current state of the selected output.

To teach in a switching threshold, press and hold the "TI" button for approximately 1 s, until the yellow and green LEDs flash in phase. Teach-in starts when the "TI" button is released.


- Teach-in successful: the yellow and green LEDs flash alternately at 2.5 Hz.
- Teach-in unsuccessful: the yellow and green LEDs quickly flash alternately at 8 Hz.
 After an unsuccessful Teach-in, the sensor continues to operate with the previous valid setting after the relevant visual fault signal is issued.

Set switching mode: you can define different switching modes by teaching in the relevant distance data for switching thresholds A and B.

1. Single point mode:



2. Window mode:



Teach in switching thresholds: you can teach in or overwrite a taught-in switching threshold at any time. To do this, press the "TI" button again.

Reset a value: you can reset a taught-in value. To do this, press the "TI" button for > 4 s, until the yellow and green LEDs go out. The reset process itself starts when the "TI" button is released.

• Reset successful: the yellow and green LEDs flash alternately at 2.5 Hz.

Resetting to Factory Settings

To revert back to factory settings, press the "TI" button for > 10 s with the rotary switch set to position "O," until the yellow and green LEDs go out at the same time. The reset process itself starts when the "TI" button is released.

Reset to factory settings successful: the yellow and green LEDs light up at the same time. The sensor then continues to
operate with factory settings.

OMT

- Factory setting for switching signal Q1:
 Switching signal is high active, window mode
- Factory setting for switching signal Q2:
 Switching signal is high active, window mode

Setting different operating modes via the IO-Link interface

The devices are equipped with an IO-Link interface as standard for diagnostics and parameterization tasks to ensure optimum adjustment of the sensors to the relevant application.

Single point mode operating mode (one switch point):

- "Detection of objects irrespective of type and color in a defined detection range. Objects in the background are suppressed.
- "The switch point corresponds exactly to the set point.




Window mode operating mode (two switch points):

- Detection of objects irrespective of type and color in a defined detection range. Reliable detection when object leaves the
 detection range.
- Window mode with two switch points.




Center window mode operating mode (one switch point):

- Detection of objects irrespective of type and color in a defined detection range. Sets a defined window around a given object.
 Objects outside this window are not detected.
- · Window mode with one switch point.



Two point mode operating mode (hysteresis operating mode):

Detection of objects irrespective of type and color between a defined switch-on and switch-off point.



Inactive operating mode:

· Evaluation of switching signals is deactivated.

The associated IODD device description file can be found in the download area at www.pepperl-fuchs.com.