




#### **Function**

The inductive safety sensors are TÜV-certified in accordance with the EU Machinery Directive, Performance Level PLd, Category 2, and SIL2. They are used to safeguard machines and plant components, as well as for reliable position detection in this environment. With their OSSD interface for reliable, redundant shutdown of electronic outputs, they enable easy connection to a safety PLC or fail-safe control interfaces. They can also be operated as standard sensors. The sensors reliably detect standard metal objects in front of the sensor face without coding or similar; there is no blind zone. High characteristic safety values allow longer testing intervals than comparable solutions with a microcontroller. 2 sensors can be connected with 2-channel redundancy and allow PLe as a Category 3 solution.

## **Dimensions**



## **Technical Data**

Release date: 2023-05-09 Date of issue: 2023-05-09 Filename: 304276-000013\_eng.pdf

General specifications		
Switching function		2 x normally open (NO)
Output type		PNP
Rated operating distance	Sn	4 mm
Installation		non-flush
Output polarity		DC
Assured operating distance	Sa	0 3.24 mm
Actuating element		Reference target according EN IEC 60947-5-2 (FE360 - ST37K) 12 mm x 12 mm x 1 mm
Reduction factor r <sub>AI</sub>		0.55
Reduction factor r <sub>Cu</sub>		0.5

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com



## NSN4-12GM50-2E2-S2D2


Technical Data		
Reduction factor r <sub>304</sub>		0.9
Reduction factor r <sub>Brass</sub>		0.6
Output type		4-wire
Nominal ratings		
Operating voltage	U <sub>B</sub>	18 30 V
Rated operating voltage	U <sub>e</sub>	24 V
Switching frequency	f	0 30 Hz
Hysteresis	Н	typ. 5%
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Overload resistance		yes
Voltage drop	$U_d$	$\leq$ 3 V at I <sub>L</sub> (sum of all outputs) max. 50 mA
Rated insulation voltage	U <sub>BIS</sub>	30 V
Operating current	ΙL	1 30 mA per output
Off-state current	l <sub>r</sub>	0 0.5 mA
No-load supply current	I <sub>0</sub>	≤ 15 mA
Time delay before availability	t <sub>v</sub>	≤ 300 ms
Switching state indicator		LED, yellow
Error indicator		LED, red
Functional safety related parameters		
Safety Integrity Level (SIL)		SIL 2
Performance level (PL)		PL d
Category		Cat. 2
MTTF <sub>d</sub>		> 7500 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		min. 60 %
Assured release distance of a PDDB	Sar	6 mm
Compliance with standards and directives		
Standard conformity		
Standards		EN IEC 60947-5-2:2007 EN IEC 60947-5-3:2013 EN ISO 13849-1:2015 EN IEC 61508:2010 EN 62061:2005+AC:2010+A1:2013+A2:2015 compatible with EN ISO 61131-2:2007 Typ 1, 2, 3
Approvals and certificates		
UL approval		cULus Listed, General Purpose, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-40 85 °C (-40 185 °F)
Altitude		≤ 2000 m above MSL
Mechanical specifications		
Connection type		cable PVC , 2 m
Core cross section		0.34 mm <sup>2</sup>
Housing material		brass, nickel-plated
Sensing face		PBT
Degree of protection		IP68 / IP69
Mass		77 g
General information		

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

2

#### Connection



# Commissioning

Note for Setting the Safety Control The sensor has a self-monitoring function for the outputs. Therefore, to avoid any malfunctions of the sensor, deactivate all test pulses of the connected safety controller to the sensor.

Access	sories	
	BF 12	Mounting flange, 12 mm

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"