
# Release date: 2023-05-09 Date of issue: 2023-05-09 Filename: 304276-000034\_eng.pdf

# Inductive sensor



## NSB10-30GM50-2E2-M1-S2D2

- No unusable area
- 10 mm flush
- Use of standard metallic actuating surfaces
- Applications up to Cat. 2, PLd/SIL 2 possible (can be used redundantly up to Cat. 3, PLe/SIL 3)
- LED for switching state and fault indication
- Safety outputs OSSD
- E1-Type approval
- Extended temperature range -40 ... +85 °C
- TÜV certified














### **Function**


The inductive safety sensors are TÜV-certified in accordance with the EU Machinery Directive, Performance Level PLd, Category 2, and SIL2. They are used to safeguard machines and plant components, as well as for reliable position detection in this environment. With their OSSD interface for reliable, redundant shutdown of electronic outputs, they enable easy connection to a safety PLC or fail-safe control interfaces. They can also be operated as standard sensors. The sensors reliably detect standard metal objects in front of the sensor face without coding or similar; there is no blind zone. High characteristic safety values allow longer testing intervals than comparable solutions with a microcontroller. 2 sensors can be connected with 2-channel redundancy and allow PLe as a Category 3 solution.

### **Dimensions**



### **Technical Data**

General specifications		
Switching function		2 x normally open (NO)
Output type		PNP
Rated operating distance	$s_n$	10 mm
Installation		flush
Output polarity		DC
Assured operating distance	sa	0 8.1 mm
Actuating element		Reference target according EN IEC 60947-5-2 (FE360 - ST37K) 30 mm x 30 mm x 1 mm
Reduction factor r <sub>Al</sub>		0.5



Technical Data		
Reduction factor r <sub>Cu</sub>		0.4
Reduction factor r <sub>304</sub>		0.8
Reduction factor r <sub>Brass</sub>		0.5
Output type		4-wire
Nominal ratings		
Operating voltage	$U_B$	18 30 V
Rated operating voltage	U <sub>e</sub>	24 V
Switching frequency	f	0 30 Hz
Hysteresis	Н	typ. 5%
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Overload resistance		yes
Voltage drop	$U_{\text{d}}$	≤ 3 V at I <sub>L</sub> (sum of all outputs) max. 50 mA
Rated insulation voltage	U <sub>BIS</sub>	30 V
Operating current	IL	1 30 mA per output
Off-state current	I <sub>r</sub>	0 0.5 mA
No-load supply current	I <sub>0</sub>	≤ 15 mA
Time delay before availability	t <sub>v</sub>	≤ 300 ms
Switching state indicator	·	LED, yellow
Error indicator		LED, red
Functional safety related parameters		,
Safety Integrity Level (SIL)		SIL 2
Performance level (PL)		PL d
Category		Cat. 2
MTTF <sub>d</sub>		> 7500 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		min. 60 %
Assured release distance of a PDDB	Sar	15 mm
Compliance with standards and directives	Oar	10 11111
Standard conformity		
Standards		EN IEC 60947-5-2:2007 EN IEC 60947-5-3:2013 EN ISO 13849-1:2015 EN IEC 61508:2010 EN 62061:2005+AC:2010+A1:2013+A2:2015
Approvals and certificates		compatible with EN ISO 61131-2:2007 Typ 1, 2, 3
UL approval		cULus Listed, General Purpose, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
E1 Type approval		10R-06
Ambient conditions		100-00
		40 05 °C / 40 405 °C\
Ambient temperature		-40 85 °C (-40 185 °F)
Storage temperature  Altitude		-40 85 °C (-40 185 °F) ≤ 2000 m above MSL
		2 2000 III above Ivige
Mechanical specifications		cable DLID 2 m
Connection type Core cross section		cable PUR , 2 m 0.5 mm <sup>2</sup>
Housing material		brass, nickel-plated
Sensing face		PBT
Degree of protection		IP68 / IP69
Mass		173 g
General information		
Scope of delivery		2 self locking nuts in scope of delivery

### BN - L+ ВK WH OSSD2/ OSSD1/ BU

# Commissioning

Note for Setting the Safety Control
The sensor has a self-monitoring function for the outputs. Therefore, to avoid any malfunctions of the sensor, deactivate all test pulses of the connected safety controller to the sensor.

### **Accessories**



**BF 30** 

Mounting flange, 30 mm