

Laser diffuse mode sensor with background evaluation





Function


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design - from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation tasks.


The entire series enables sensors to communicate via IO-Link. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor. Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.

Dimensions









Technical Data

General specifications

General specifications	
Detection range	40 600 mm
Detection range min.	40 90 mm
Detection range max.	40 600 mm
Adjustment range	90 600 mm
Reference target	standard white, 100 mm x 100 mm
Light source	laser diode
Light type	modulated visible red light
Laser nominal ratings	
Note	LASER LIGHT , DO NOT STARE INTO BEAM
Laser class	1
Wave length	680 nm
Beam divergence	> 5 mrad, d63 < 2,8 mm in the range of 350 mm 800 mm
Pulse length	3 µs
Repetition rate	approx. 13 kHz
max. pulse energy	10.4 nJ
Black-white difference (6 %/90 %)	< 5 % at 300 mm
Diameter of the light spot	approx. 2.5 mm at a distance of 600 mm
Opening angle	approx. 0.3 °
Ambient light limit	EN 60947-5-2 : 70000 Lux
Functional safety related parameters	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com



Technical Data

$\mathsf{MTTF}_{\mathsf{d}}$ 560 a 20 a Mission Time (T_M) Diagnostic Coverage (DC) 0% Indicators/operating means Operation indicator LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode Function indicator LED yellow: constantly on - background detected (object not detected) constantly off - object detected Control elements Light-on/dark-on changeover switch Control elements Sensing range adjuster **Electrical specifications** Operating voltage UB 10 ... 30 V DC Ripple max. 10 % No-load supply current < 15 mA at 24 V supply voltage I_0 Protection class Ш Interface Interface type IO-Link (via C/Q = pin 4) **IO-Link revision** 1.1 Device profile Identification and diagnosis Smart Sensor type 2.4 Device ID 0x111713 (1120019) Transfer rate COM2 (38.4 kBit/s) Min. cycle time 2.3 ms Process data input 1 Bit Process data output 2 Bit Process data width SIO mode support yes Compatible master port type А Output The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link /Q - Pin2: NPN normally closed / light-on, PNP normally open / dark-on Switching type Signal output 2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected, overvoltage protected Switching voltage max. 30 V DC Switching current max. 100 mA , resistive load DC-12 and DC-13 Usage category < 1.5 V DCVoltage drop U_{d} Switching frequency f 1650 Hz Response time 300 µs Conformity Communication interface IEC 61131-9 Product standard EN 60947-5-2 Laser safety EN 60825-1:2014 Approvals and certificates UL approval E87056, cULus Listed, class 2 power supply, type rating 1 CCC approval CCC approval / marking not required for products rated ≤36 V FDA approval IEC 60825-1:2014 Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3 as described in Laser Notice 56, dated May 8, 2019. Ambient conditions Ambient temperature -40 ... 60 °C (-40 ... 140 °F) Storage temperature -40 ... 70 °C (-40 ... 158 °F) Mechanical specifications Degree of protection IP67 / IP69 / IP69K


Refer to "General Notes Relating to Pepperl+Fuchs Product Information

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Technical Data

Connection	4-pin, M12 x 1 connector, 90° rotatable
Material	
Housing	PC (Polycarbonate)
Optical face	РММА
Mass	approx. 47 g
Dimensions	
Height	61.7 mm
Width	15 mm
Depth	41.7 mm

Connection Assignment



Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN WH	(brown) (white)
2	BU	(writte) (blue)
4	BK	(black)

Assembly

1

ģ

2

O

Release date: 2025-01-17 Date of issue: 2025-01-17 Filename: 295670-100249_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Ē

(

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

3

4

5

Sensitivity adjustment

Signal indicator

Light-on / dark-on changeover switch

Operating indicator / dark on

Operating indicator / light on

1 2

3

4

5

GN


YE

GN



Characteristic Curve

Minimum object height (typical)



Y I	Background on white 90 % / object on black 6 %
	Background on white 90 % / object on white 90 %
	— — - Background on black 6 % / object on black 6 %
	Background on black 6 % / object on white 90 %

Safety Information



CLASS 1 LASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for devlations pursuant to Laser Notice No. 50, dated June 24, 2007

CLASS 1 LASER PRODUCT

IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

5

Configuration

To unlock the adjustment functions, rotate the sensing range/sensitivity adjuster by more than 180°.

Sensing Range/Sensitivity

To increase the sensing range/sensitivity, rotate the sensing range/sensitivity adjuster clockwise.

To reduce the sensing range/sensitivity, rotate the sensing range/sensitivity adjuster counter-clockwise.

As soon as the end of the adjustment range is reached, the signal indicator flashes at 8 Hz.

Configuring Light On/Dark On

Press the light-on/dark-on changeover switch for more than 1 second (but less than 4 seconds). "Light on/dark on" mode changes and the relevant operating indicator lights up.

If you press the light-on/dark-on changeover switch for longer than 4 seconds, the "light on/dark on" mode will switch back to the original setting. The current status is activated when the light-on/dark-on changeover switch is released.

Restoring Factory Settings

Press the light-on/dark-on changeover switch for more than 10 seconds (but less than 30 seconds) until all LEDs go out. When the light-on/dark-on changeover switch is released, the signal indicator lights up. After 5 seconds, the sensor resumes operation with the factory settings.

The adjustment functions are locked after 5 minutes of inactivity. To unlock the adjustment functions, rotate the sensing range/sensitivity adjuster again by more than 180°.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information

