



Thru-beam sensor (pair) OBE25M-R201-SEP-IO-V3



- Medium design with versatile mounting options
- IO-Link interface for service and process data
- Various frequencies for avoiding mutual interference (cross-talk
- Extended temperature range -40 °C ... 60 °Ċ
- High degree of protection IP69K





Function


The optical sensors in the series are the first devices to offer an end-to-end solution in a medium-sized standard design – from the thru-beam sensor through to the measuring distance sensor. As a result of this design, the sensors are able to perform practically all standard automation

The entire series enables sensors to communicate via IO-Link.

The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Multi Pixel Technology (MPT) ensures that the standard sensors are flexible and can be adapted to the application environment.

Dimensions



Technical Data


System components	
Emitter	OBE25M-R201-S-IO-V3
Receiver	OBE25M-R201-EP-IO-V3
General specifications	
Effective detection range	0 25 m
Threshold detection range	33 m
Light source	LED
Light type	modulated visible red light
LED risk group labelling	exempt group
Alignment aid	LED red (in receiver lens) illuminated constantly: beam is interrupted, flashes: reaching switching point, off: sufficient stability control
Diameter of the light spot	approx. 850 mm at a distance of 25 m
Opening angle	approx. 2 °
Ambient light limit	EN 60947-5-2 : 40000 Lux
Functional safety related parameters	
MTTF _d	462 a


Technical Data		
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		60 %
ndicators/operating means		
Operation indicator		LED green: constantly on - power on flashing (4Hz) - short circuit flashing with short break (1 Hz) - IO-Link mode
Function indicator		Yellow LED: Permanently lit - light path clear Permanently off - object detected Flashing (4 Hz) - insufficient operating reserve
Control elements		Receiver: light/dark switch
Control elements		Receiver: sensitivity adjustment
Electrical specifications		
Operating voltage	U_B	10 30 V DC
Ripple		max. 10 %
No-load supply current	I ₀	Emitter: ≤ 15 mA Receiver: ≤ 15 mA at 24 V Operating voltage
Protection class		III
nterface		
Interface type		IO-Link (via $C/Q = pin 4$)
IO-Link revision		1.1
Device profile		Identification and diagnosis Smart Sensor: Receiver: type 2.4 Emitter: -
Device ID		Emitter: 0x1111411 (1119249) Receiver: 0x111311 (1118993)
Transfer rate		COM2 (38.4 kBit/s)
Min. cycle time		2.3 ms
Process data width		Emitter: Process data input: 0 bit Process data output: 1 bit Receiver: Process data input: 2 bit Process data output: 2 bit
SIO mode support		yes
Compatible master port type		A
nput		
Test input		emitter deactivation at +U _B
Output		
Switching type		The switching type of the sensor is adjustable. The default setting is: C/Q - Pin4: NPN normally open / dark-on, PNP normally closed / light-on, IO-Link
Signal output		1 push-pull (4 in 1) output, short-circuit protected, reverse polarity protected, overvoltage protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA , resistive load
Usage category		DC-12 and DC-13
Voltage drop	U_{d}	≤ 1.5 V DC
Switching frequency	f	1000 Hz
Response time		0.5 ms
Conformity		
Communication interface		IEC 61131-9
Product standard		EN 60947-5-2
Approvals and certificates		
UL approval		E87056 , cULus Listed , class 2 power supply , type rating 1
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-40 60 °C (-40 140 °F)

16 Date of issue: 2023-01-16 Filename: 301103 eng.pdf
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
023-01-16
8
8
8
8
8
16 Date of issue: 20
16 Date of issue:
16 Date of issu
16 Date of is:
6 Date of
l6 Date
16 Dat
<u>0</u> 9
9
Ξ
5
8
Š
8
in
æ
ಕ
ø
35
ŏ
ā
ď

Technical Data	
Storage temperature	-40 70 °C (-40 158 °F)
Mechanical specifications	
Housing width	15 mm
Housing height	61.7 mm
Housing depth	41.7 mm
Degree of protection	IP67 / IP69 / IP69K
Connection	Connector plug, M8 x 1, 3 pin, rotatable by 90°
Material	
Housing	PC (Polycarbonate)
Optical face	PMMA
Mass	Emitter: approx. 44 g receiver: approx. 44 g

Connection





Connection Assignment




Wire colors in accordance with EN 60947-5-2

BN (brown) 3 BU (blue) (black) BK




Operating indicator


Receiver



1	Sensitivity adjustment	
2	Light-on / dark-on changeover switch	
3	Operating indicator / dark on	GN
4	Signal indicator	YE
5	Operating indicator / light on	GN

Characteristic Curve





Commissioning

To unlock the adjustment functions turn the sensing range / sensitivity adjuster for more than 180 degrees.

Sensing Range / Sensitivity

Turn sensing range / sensitivity adjuster clockwise to increase sensing range / sensitivity.
Turn sensing range / sensitivity adjuster counter clockwise to decrease sensing range / sensitivity.

If the end of the adjustment range is reached, the signal indicator starts flashing with 8 Hz.

Light-on / Dark-on Configuration

Press the light-on / dark-on changeover switch for more than 1 second (less than 4 seconds). The light-on / dark-on mode changes and the operating indicators are activated accordingly.



If you press the light-on / dark-on changeover switch for more than 4 seconds, the light-on / dark-on mode changes back to the original setting. On release of the light-on / dark-on changeover switch the current state is activated.

Restore Factory Settings
Press the light-on / dark-on changeover switch for more than 10 seconds (less than 30 seconds) until all LEDs turn off. On release of the light-on / dark-on changeover switch the signal indicator turns on. After 5 seconds the sensor resumes operation with factory default settings.

After 5 minutes of inactivity the sensing range / sensitivity adjustment is locked. In order to reactivate the sensing range / sensitivity adjustment, turn the sensing range / sensitivity adjuster for more than 180 degrees.

Accessories

OMH-RL31-03 Mounting bracket narrow OMH-RL31-04 Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm OMH-RL31-07 Mounting bracket including adjustment	
OMH-RL31-04 Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm OMH RL31-07 Mounting breekst including adjustment	
OMH DI 21 07 Maunting broakst including adjustment	
OMH-RI 31-07 Mounting bracket including editestment	
OMH-RL31-07 Mounting bracket including adjustment	
OMH-RL31-08 Mounting bracket including adjustment OMH-RL31-08 Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm OMH-R20x-Quick-Mount Quick mounting accessory	
OMH-R20x-Quick-Mount Quick mounting accessory	
ICE2-8IOL-G65L-V1D EtherNet/IP IO-Link master with 8 inputs/outputs	
ICE3-8IOL-G65L-V1D PROFINET IO IO-Link master with 8 inputs/outputs	
ICE2-8IOL-K45S-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, screw terminal	
ICE3-8IOL-K45P-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, push-in terminals	
ICE3-8IOL-K45S-RJ45 PROFINET IO IO-Link master with 8 inputs/outputs, DIN rail, screw terminal	
IO-Link-Master02-USB IO-Link master, supply via USB port or separate power supply, LED indicators, M12 plug for senso connection	r
ICE1-8IOL-G30L-V1D Ethernet IO-Link module with 8 inputs/outputs	
ICE1-8IOL-G60L-V1D Ethernet IO-Link module with 8 inputs/outputs	
ICE2-8IOL-K45P-RJ45 EtherNet/IP IO-Link master with 8 inputs/outputs, DIN rail, push-in connectors	
V3-GM-2M-PUR Female cordset single-ended M8 straight A-coded, 3-pin, PUR cable grey	
V3-WM-2M-PUR Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey	