Release date: 2023-05-12 Date of issue: 2023-05-12 Filename: 305981_eng.pdf

Blancia Blancia Blancia

Photoelectric slot sensor GL5-L/43a/115a



- Miniature design
- Optimized for the detection of small parts
- High switching frequency
- Simple and fast mounting
- Clearly visible LED functional display

Miniature slot sensor for small part detection, L design, 5 mm slot width, infrared light, PNP output, with 0.2 m fixed cable and M8 plug, 4-pin



Function


The GL5 miniature slot sensor compares a high optical performance in a small housing and is optimized to the requirements in semiconductors industry for small part detection. A wide voltage range of 5 - 24 V DC and the fastest switching frequency of 5 kHz in its class stands for the quality of this sensor. The integrated aperture allows the small part detection with a minimum object size of 0.8 x 1.8 mm. The sensor offers antivalent npn or pnp outputs. Due to a variety of different housings and an optimized housing concept offers the sensor a maximum of freedom in a crowded mounting environment.

Application

- Detection of lead frames
- · Detection of cam positions
- · Detection of limit positions of moving objects
- · Position detection of wafer cases



Dimensions




Technical Data

Canaval anasifications


	IRED
	Infrared, continuous light, 940 nm
	0.8 x 1.8 mm
	5 mm
	8.5 mm
	1000 Lux
	3760 a
	20 a
	0 %
	red LED lights up when receiving the light beam
U_B	5 24 V DC , class 2
I_0	max. 20 mA
t _v	< 2 ms
	light/dark on
	2 PNP complementary , overvoltage protected
	max. 30 V DC
	max. 50 mA, resistive load
U_{d}	max. 0.2 V at 10 mA max. 0.6 V at 50 mA
f	max. 5 kHz
	I ₀ t _v

Technical Data		
Response time		40 μs Light beam is not interrupted 80 μs Light beam is interrupted
Repeat accuracy	R	0.03 mm
Compliance with standards and directives		
Directive conformity		
EMC Directive 2004/108/EC		EN 60947-5-2:2007+A1:2012
Standard conformity		
Standards		UL 60947-5-2
Approvals and certificates		
UL approval		cULus Recognized, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 55 °C (-13 131 °F)
Storage temperature		-30 80 °C (-22 176 °F)
Pollution degree		2
Mechanical specifications		
Housing width		18.5 mm
Housing height		26 mm
Degree of protection		IP50
Connection		with 0.2 m fixed cable and M8 plug, 4-pin
Material		
Housing		PBT
Mass		25 g
Tightening torque, fastening screws		0.6 Nm

Connection Assignment



- O = Light on
- = Dark on



 $\begin{tabular}{ll} \textbf{Response frequency}\\ \textbf{The response frequency is the value when the disc is rotated, see figure.} \end{tabular}$